



## Adjustable spanner, overall length: 150mm



### Order data

Order number	814001 150
GTIN	4062406072056
Item class	82A

### Description

#### Version:

Slim design with double-T-profile shank (chromium plated). Jaw angle 22°. Drop-forged and hardened. With **scale** on the jaw.

Adjustable spanner, chrome-plated.  
 maximum width across flats: 19 mm  
 overall length: 6 in

### Technical description

maximum width across flats	19 mm
overall length	150 mm
overall length	6 in
Jaw position	22°
Manufacturing process	drop-forged and hardened
non-sparking	no
Scaling	yes
Grips	no
Type of product	Adjustable spanners

