



## Adjustable spanner, overall length: 250mm



### Order data

Order number	814001 250
GTIN	4062406072070
Item class	82A

### Description

#### Version:

Slim design with double-T-profile shank (chromium plated). Jaw angle 22°. Drop-forged and hardened. With **scale** on the jaw.

Adjustable spanner, chrome-plated.

maximum width across flats: 30 mm

overall length: 10 in

### Technical description

overall length	10 in
maximum width across flats	30 mm
overall length	250 mm
Jaw position	22°
Manufacturing process	drop-forged and hardened
non-sparking	no
Scaling	yes
Grips	no
Type of product	Adjustable spanners

