


DATE	REV	ECN	DESCRIPTION
10/30/2015	D		SPECIFICATION UPDATED

PRODUCT SPECIFICATION

Parent Number: F18041-

Description: 18 16/30 TC AWM 1569 or 1007 TR-64 or AWM I A/B

DIAMETER: 0.079
TOLERANCE ± : 0.003



MIN AVG WALL: 0.015
MINIMUM WALL: 0.013

Stranding: 16/30 TC LHL

Style: UL: AWM 1007 OR 1569 CSA: TR-64 or AWM I A/B

Insulation: PVC

Print Legend: 18 AWG (0.823mm²) E57498 (PLANT ID CODE) (AWM LOGO) AWM 1569 105C OR 1007 80C 300V VW-1 --- 156205 CSA TR-64 90C FT1 OR AWM I A/B 105C 300V FT1

Voltage: 300V

Temperature: 1569=105C, 1007=80C, TR64=90C, AWM I A/B=105C

Notes: 1. Min Temp Rating: -15C

This product complies with European Directive 2011/65/EU (RoHS 2)

The information presented here is, to the best of our knowledge, true and accurate. Since conditions of use are beyond Southwire's control all product data presented is for informational purposes only and does not create a binding obligation or liability on Southwire or confer any rights on any customer. The sale of product(s) is conditioned upon acceptance of a purchase order subject to Southwire's standard terms and conditions contained therein, including without limitation Southwire's standard warranty. Southwire disclaims all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Southwire Company, LLC. Any information contained herein shall not be disclosed to any party without written consent of Southwire Company, LLC.

Customer Approval:

Customer Part Nbr(s): _____

Approved By: _____ **Date:** _____

Title: _____ **Company Name:** _____



Copperfield[®]
 1115 W. North Street
 Bremen, IN 46506
 Phone: 1-574-546-5115

