



ATTN:

IN RESPONSE TO YOUR REQUEST FOR SPECS ON 6 GA UL CABLE, PLEASE FIND THE FOLLOWING:

- 1) PART #: TBD**
- 2) GA: 6**
- 3) STRANDING: 19 BC**
- 4) NOMINAL O.D: .325**
- 5) WALL THICKNESS: .060**
- 6) VOLTAGE: 1000 VOLT**
- 7) JACKET TYPE: 105C DEGREE PVC**
- 8) PRINT LEGEND: E315270 6 AWG (UL) MTW OR THHW OR BC-5W2 OR AWM 1232/1283/1015/1346 600V OR 1032/10269 1000V, VW-1---240954 CSA TEW 105C 600V FT1 OR AWM I A/B 105C W75C O 600/1000V FT1---SAE J1127 TYPE SGT**

THIS IS TO CONFIRM THAT THE 6 GA UL CABLE LISTED MEETS THE ABOVE SPECS.

**ANDY HARWOOD
VICE PRESIDENT OF SALES**