



ATTN:

IN RESPONSE TO YOUR REQUEST FOR SPECS ON 1 GA UL CABLE, PLEASE FIND THE FOLLOWING:

- 1) GA: 1**
- 2) STRANDING: 7X19/.0243 BC**
- 3) NOMINAL O.D: .510 OD**
- 4) WALL THICKNESS: .080**
- 5) VOLTAGE: 1000 VOLT**
- 6) JACKET TYPE: 105C DEGREE PVC**
- 7) PRINT LEGEND: E315270 1 AWG (UL) MTW OR THHW OR BC-5W2 OR AWM 1011/1015/1232/1284/1338 600V OR 1032/10269 1000V, VW-1---240954 CSA 105C TEW 600V FT1 OR AWM I A/B 105C W75C O 600/1000V FT1---SAE J1127 TYPE SGT**

THIS IS TO CONFIRM THAT THE 1 GA UL CABLE LISTED MEETS THE ABOVE SPECS.

**ANDY HARWOOD
VICE PRESIDENT OF SALES**