



**ATTN:**

**IN RESPONSE TO YOUR REQUEST FOR SPECS ON 3/0 GA UL CABLE, PLEASE FIND THE FOLLOWING:**

- 1) PART #: TBD**
- 2) GA: 3/0**
- 3) STRANDING: 19X88/30 BC**
- 4) NOMINAL O.D: .680 OD**
- 5) WALL THICKNESS: .085**
- 6) VOLTAGE: 1000 VOLT**
- 7) JACKET TYPE: 105C DEGREE PVC**
- 8) RATED FOR CT USE**
- 9) PRINT LEGEND: E315270 3/0 AWG (UL) MTW OR THHW OR BC-5W2 OR AWM 1011/1015/1232/1284/1338 600V OR 1032/10269 1000V, VW-1---240954 CSA 105C TEW 600V FT1 OR AWM I A/B 105C W75C O 600/1000V FT1---SAE J1127 TYPE SGT**

**THIS IS TO CONFIRM THAT THE 3/0 GA UL CABLE LISTED MEETS THE ABOVE SPECS.**

---

**ANDY HARWOOD  
VICE PRESIDENT OF SALES**