

PRODUCT SPECIFICATION



DESCRIPTION: 16 AWM 3173/3237

DIAMETER: 0.114

TOLERANCE +/-: 0.003

PRODUCT NUMBER: 1643A4T

GAUGE: 16

STRANDING: 26/30 TC

INSULATION: XLPE

VOLTAGE: 600V DC/1000V DC

TEMPERATURE: 125C

STYLE: AWM/3173/3237



NOM WALL: 0.030

MINIMUM WALL: 0.027

PRINT LEGEND: E511593 16 AWG (1.31mm²) UR AWM
3173 125C 600V or 3237 1000V -- 301259
CSA CL1251 125C 600V or AWM I A/B 125C
600V FT2 Suitable for Switchboard Wire

NOTES: 1. Min Temp Rating: -40C

Tolerances unless otherwise noted: FRACTIONS +/- 1/32, DECIMALS +/- 0.03 (2PL) +/-0.005 (3PL)

Confidential: This drawing and its information are the exclusive and confidential property of Sequel Wire and Cable, LLC and are not to be disclosed, duplicated, distributed, or otherwise used without the written consent of Sequel Wire and Cable, LLC. All rights reserved.

Date	Revision	ECN	Description
12/09/2021	1		