


PRODUCT SPECIFICATION

<i>DATE</i>	<i>REV</i>	<i>ECN</i>	<i>DESCRIPTION</i>
6/30/2009	B	20972	SPECIFICATION UPDATED

Parent Number: F22030-

Description: 22 7/.0096 TC AWM 3173 CL 1251 AWM I A/B

DIAMETER: 0.090
TOLERANCE ± : 0.003



MIN AVERAGE WALL: 0.030

MINIMUM WALL: 0.027

Stranding: 7/.0096 TC LHL

Style: UL: AWM 3173 CSA: CL1251 AWM I A/B

Insulation: XLPE

Print Legend: 22 AWG (0.324mm²) E96824 (PLANT ID CODE) (AWM LOGO) AWM 3173 125C 600V -- 156016 CSA CL1251 125C 600V OR AWM I A/B 125C 600V FT2 -- SUITABLE FOR "SWITCHBOARD WIRE" -- MADE IN USA

Voltage: UL: AWM 3173 = 600V CSA: AWM/CL1251 = 600V, AWM = 1000V

Temperature: UL: AWM 3173 = 125C CSA: AWM = 105C, CL1251 or AWM = 125C

Notes:

This product complies with European Directive 2011/65/EU (RoHS 2)

The information presented here is, to the best of our knowledge, true and accurate. Since conditions of use are beyond Coleman Cable's control all product data presented is for informational purposes only and does not create a binding obligation or liability on Coleman Cable or confer any rights on any customer. The sale of product(s) is conditioned upon acceptance of a purchase order subject to Coleman Cable's standard terms and conditions contained therein, including without limitation Coleman Cable's standard warranty. Coleman cable disclaims all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Coleman Cable. Any information contained herein shall not be disclosed to any party without written consent of Coleman Cable.

Customer Approval:

Customer Part Nbr(s): _____

Approved By: _____ **Date:** _____

Title: _____ **Company Name:** _____

COLEMAN CABLE, INC

1530 Shields Drive
Waukegan, IL 60085

Phone: 1-800-323-9355

www.colemancable.com

