			DATE	REV	ECN	DESCRIPTION
<u>PRODUCT</u>	<u>SPECIFICATION</u>		7/6/2009	D	20977	SPECIFICATION UPDATED
Parent Number:	F04029-					
<b>Description:</b>	4 7x19/25 TC AWM 3196 UL SIS CL 1251	DIAMETER: (				
	<u>AWM I A/B</u>	$TOLERANCE \pm : \ \underline{C}$	<u>).010</u>		000	
~ .				$\downarrow$	/ 1888	8
	7x19/25 TC Unilay				<i>M</i>	IIN AVERAGE WALL: <u>0.060</u>
<u>Style:</u>	UL: AWM 3196 UL SIS CSA: CL 1251 AWM I	<u>A/B</u>				<i>MINIMUM WALL:</i> <u>0.054</u>
In and at any	VI DE					
Insulation:						
<u>Print Legend:</u>	E137925 (PLANT ID CODE) 4 AWG SIS (UL) 600V AND AV MADE IN USA	<u>NM STYLE 3196 156</u>	6016 CSA CI	_1251 125	C 600V OF	<u>RAWM I A/B 125C 600V FT2</u>
Voltage:	<u>600V</u>					
_						
<u>Temperature:</u>	<u>SIS = 90C, AWM 3196 = 125C</u>					
Notes:						
	This product complies with European Directive 2011/65/EU (RoHS	,				
	ented here is, to the best of our knowledge, true and accurate. Since es not create a binding obligation or liability on Coleman Cable or co					
order subject to Colen	nan Cable's standard terms and conditions contained therein, includi se of information contained herein or otherwise.					
This specification is p without written conser	roprietary intellectual property of Coleman Cable. Any information cont of Coleman Cable.	ntained herein shall not be	e disclosed to	any party	CO	LEMAN CABLE, INC
<u>Customer Appro</u>	oval:				1530 SI	hields Drive
Customer Part	t Nbr(s):				Wauke	gan, IL 60085
Approved By:_	Date:				Phone:	1-800-323-9355
Title:_	Company l	Name:			www.col	lemancable.com