


DATE	REV	ECN	DESCRIPTION
10/31/2016	C		Updated voltage ratings.

PRODUCT SPECIFICATION

Parent Number: F04033-

Description: 4 7x19/25 TC AWM 3556 or 3321 CL 1503 or AWM I A/B

DIAMETER: 0.392
TOLERANCE ±: 0.010



MIN AVG WALL: 0.060
MINIMUM WALL: 0.054

Stranding: 7x19/25 TC LHL

Style: UL: AWM 3556 or 3321 CSA: CL 1503 or AWM I A/B

Insulation: POE

Print Legend: 4 AWG (21.15mm²) E57498 (PLANT ID CODE) (AWM LOGO) AWM STYLE 3556 OR 3321 150C 600V EP -- 156205 CSA CL1503 150C 600V OR AWM I A/B 150C 600V FT2 -- MADE IN USA

Voltage: UL: 600V AC or 750V DC CSA: 600V

Temperature: 150C

Notes:

This product complies with European Directive 2011/65/EU (RoHS 2)

The information presented here is, to the best of our knowledge, true and accurate. Since conditions of use are beyond Southwire's control all product data presented is for informational purposes only and does not create a binding obligation or liability on Southwire or confer any rights on any customer. The sale of product(s) is conditioned upon acceptance of a purchase order subject to Southwire's standard terms and conditions contained therein, including without limitation Southwire's standard warranty. Southwire disclaims all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Southwire Company, LLC. Any information contained herein shall not be disclosed to any party without written consent of Southwire Company, LLC.

Customer Approval:

Customer Part Nbr(s): _____

Approved By: _____ **Date:** _____

Title: _____ **Company Name:** _____



Southwire
Copperfield[®]
 1115 W. North Street
 Bremen, IN 46506
 Phone: 1-574-546-5115