

CAROLPRENE SJOOW

Rubber cord that performs in heat & cold, Resistant to oil/chemicals



GENERAL INFO

Thermoset rubber cord products have evolved over the last 50 years from simple and unsophisticated to a product line where specialized, technologically advanced products are in demand for exacting commercial and industrial applications. No longer are rubber cord products used only in applications where flexibility is needed; today typical applications require cord to perform well in environments of extreme heat and cold and on job sites and factory floors where resistance to oil, chemicals and abrasion is mandatory. General Cable's role, as the producer of the premiere Carol® Brand rubber cord products, is to ensure that new product development, product innovation and quality not only keep pace with industry requirements but also set the trends. Our rubber cord products carry a full range of listings and certifications with Underwriters Laboratories, Inc. and the Canadian Standard Association. In addition, many products meet or exceed the requirements of OSHA, MSHA and other relevant industry standards. Carol Brand is simply the most accepted in the industry, having proven itself on the job time after time. Our rubber cord line is the most comprehensive in the industry, ensuring that the proper Carol product can always be specified.

CONSTRUCTION/DESIGN

Nominal outer diameter [inch]	Conductor strand count	Cable marking	Conductor category	AWG size
0.56	104/30	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Class 2 = stranded	10
0.58	104/30	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Class 2 = stranded	10
0.58	104/30	CAROL (SIZE) (mm ²) TYPE SJ 60°C (UL) --- CSA TYPE SJ-FT2 300 VOLT ROHS MADE IN USA	Class 2 = stranded	10
0.58	104/30	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Class 2 = stranded	10
0.58	104/30	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Class 2 = stranded	10
0.655	104/30	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Class 2 = stranded	10
0.655	104/30	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Class 2 = stranded	10
0.41	65/30	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Class 2 = stranded	12
0.41	65/30	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Class 2 = stranded	12
0.41	65/30	CAROL (SIZE) (mm ²) TYPE SJ 60°C (UL) --- CSA TYPE SJ-FT2 300 VOLT ROHS MADE IN USA	Class 2 = stranded	12
0.41	65/30	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Class 2 = stranded	12
0.43	65/30	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Class 2 = stranded	12
0.43	65/30	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Class 2 = stranded	12

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
01382.99.01	10/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White	2	Black
01382.44.01	10/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White	2	Black
01382.XX.01	10/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White	2	Black
01483.XX.05	10/3C SJOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Yellow
01483.35T.05	10/3C SJOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Yellow
01377.41T.01	10/3C SJ BLK	CAROL (SIZE) (mm2) TYPE SJ 60°C (UL) --- CSA TYPE SJ-FT2 300 VOLT ROHS MADE IN USA	10	Black, White, Green	3	Black
01383.99.01M	10/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Black
01383.41T.01M	10/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Black
01383.46.01M	10/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Black
01383.35T.01M	10/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
01383.99.01	10/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Black
01383.41T.01	10/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Black
01383.44.01	10/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Black
01383.46.01	10/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Black
01383.XX.01	10/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Black
01383.35T.01	10/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Black
01383.85.01	10/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Black
01384.41T.01M	10/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Red, Green	4	Black
01384.35T.01M	10/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Red, Green	4	Black
01384.85.01M	10/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Red, Green	4	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
01384.41T.01	10/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Red, Green	4	Black
01384.44.01	10/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Red, Green	4	Black
01384.XX.01	10/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Red, Green	4	Black
01384.35.01	10/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Red, Green	4	Black
01384.35T.01	10/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Red, Green	4	Black
01384.38.01	10/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Red, Green	4	Black
01384.85.01	10/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Red, Green	4	Black
01379.99.01	12/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White	2	Black
01379.41T.01	12/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White	2	Black
01379.XX.01	12/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White	2	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
01379.35T.01	12/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White	2	Black
01379.38T.01	12/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White	2	Black
01379.41T.01M	12/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White	2	Black
01379.35T.01M	12/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White	2	Black
01368.41T.01	12/2C SJ BLK	CAROL (SIZE) (mm2) TYPE SJ 60°C (UL) --- CSA TYPE SJ-FT2 300 VOLT ROHS MADE IN USA	12	Black, White	2	Black
01379.99.07	12/2C SJOOW CAROLPRENE BLUE	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White	2	Blue
01380.99.01	12/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Black
01380.41T.01	12/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Black
01380.44.01	12/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Black
01380.46.01	12/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
01380.XX.01	12/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Black
01380.15T.01	12/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Black
01380.35.01	12/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Black
01380.35T.01	12/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Black
01380.38T.01	12/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Black
01380.82.01	12/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Black
01480.41T.05M	12/3C SJOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Yellow
01480.35T.05M	12/3C SJOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Yellow
01380.41T.04	12/3C SJOOW CAROLPRENE ORG	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Orange
01380.35.04	12/3C SJOOW CAROLPRENE ORG	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Orange

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
01480.41T.05	12/3C SJOOW CAROLPRENE YLW	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Yellow
01480.46.05	12/3C SJOOW CAROLPRENE YLW	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Yellow
01480.XX.05	12/3C SJOOW CAROLPRENE YLW	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Yellow
01480.35T.05	12/3C SJOOW CAROLPRENE YLW	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Yellow
01380.41T.01M	12/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Black
01380.46.01M	12/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Black
01380.XX.01M	12/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Black
01380.35T.01M	12/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Black
01380.38T.01M	12/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Black
01380.41T.02	12/3C SJOOW CAROLPRENE WHT	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	White

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
01380.XX.02	12/3C SJOOW CAROLPRENE WHT	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	White
01381.99.01	12/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Black
01381.41T.01	12/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Black
01381.46.01	12/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Black
01381.XX.01	12/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Black
01381.35T.01	12/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Black
01381.38T.01	12/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Black
01381.85.01	12/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Black
01381.99.01M	12/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Black
01381.41T.01M	12/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
01381.46.01M	12/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Black
01381.35T.01M	12/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Black
01381.38T.01M	12/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Black
01381.85.01M	12/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Black
01481.35T.05	12/4C SJOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Yellow
01481.35T.05M	12/4C SJOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Yellow
01312.41T.01M	16/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White	2	Black
01312.35T.01M	16/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White	2	Black
01312.38.01M	16/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White	2	Black
01312.99.01	16/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White	2	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
01312.41.01	16/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White	2	Black
01312.41T.01	16/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White	2	Black
01312.44.01	16/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White	2	Black
01312.46.01	16/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White	2	Black
01312.L2.01	16/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White	2	Black
01312.35.01	16/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White	2	Black
01312.35T.01	16/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White	2	Black
01312.38.01	16/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White	2	Black
01312.38T.01	16/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White	2	Black
01312.82.01	16/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White	2	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
01312.L1.01	16/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White	2	Black
01342.44.02M	16/3C SJOOW CAROLPRENE WHT	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	White
01442.35T.05M	16/3C SJOOW CAROLPRENE YLW	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Yellow
01442.35T.05	16/3C SJOOW CAROLPRENE YLW	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Yellow
01342R.46.01	16/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black
01342.44.02	16/3C SJOOW CAROLPRENE WHT	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	White
01306.41T.01	16/3C SJ BLK	CAROL (SIZE) (mm ²) TYPE SJ 60°C (UL) --- CSA TYPE SJ-FT2 300 VOLT ROHS MADE IN USA	16	Black, White, Green	3	Black
01306.46.01	16/3C SJ BLK	CAROL (SIZE) (mm ²) TYPE SJ 60°C (UL) --- CSA TYPE SJ-FT2 300 VOLT ROHS MADE IN USA	16	Black, White, Green	3	Black
01342.99.01M	16/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black
01342.41T.01M	16/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
01342.44.01M	16/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black
01342.46.01M	16/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black
01342.XX.01M	16/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black
01342.35.01M	16/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black
01342.35T.01M	16/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black
01342.99.01	16/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black
01342.41.01	16/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black
01342.41T.01	16/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black
01342.44.01	16/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black
01342.46.01	16/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
01342.35.01	16/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black
01342.35T.01	16/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black
01342.38.01	16/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black
01342.38T.01	16/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black
01342.82.01	16/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black
01343.99.01	16/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Red, Green	4	Black
01343.41T.01	16/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Red, Green	4	Black
01343.44.01	16/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Red, Green	4	Black
01343.46.01	16/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Red, Green	4	Black
01343.35.01	16/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Red, Green	4	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
01343.35T.01	16/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Red, Green	4	Black
01343.38.01	16/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Red, Green	4	Black
01343.41T.01M	16/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Red, Green	4	Black
01343.46.01M	16/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Red, Green	4	Black
01343.35T.01M	16/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Red, Green	4	Black
01310.99.01	18/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White	2	Black
01310.41T.01	18/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White	2	Black
01310.46.01	18/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White	2	Black
01310.L2.01	18/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White	2	Black
01310.35.01	18/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White	2	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
01310.35T.01	18/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White	2	Black
01310.38T.01	18/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White	2	Black
01310.L1.01	18/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White	2	Black
01310.99.01M	18/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White	2	Black
01310.41T.01M	18/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White	2	Black
01310.46.01M	18/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White	2	Black
01310.XX.01M	18/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White	2	Black
01310.35.01M	18/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White	2	Black
01310.35T.01M	18/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White	2	Black
01310.38T.01M	18/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White	2	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
01311.99.01M	18/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Green	3	Black
01311.41T.01M	18/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Green	3	Black
01311.44.01M	18/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Green	3	Black
01311.46.01M	18/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Green	3	Black
01311.35T.01M	18/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Green	3	Black
01311.38T.01M	18/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Green	3	Black
01311.99.01	18/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Green	3	Black
01311.41.01	18/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Green	3	Black
01311.41T.01	18/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Green	3	Black
01311.44.01	18/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Green	3	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
01311.46.01	18/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Green	3	Black
01311.L2.01	18/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Green	3	Black
01311.35.01	18/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Green	3	Black
01311.35T.01	18/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Green	3	Black
01311.38T.01	18/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Green	3	Black
01304.41.01	18/4C SJ BLK	CAROL (SIZE) (mm2) TYPE SJ 60°C (UL) --- CSA TYPE SJ-FT2 300 VOLT ROHS MADE IN USA	18	Black, White, Red, Green	4	Black
01344.99.01	18/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Red, Green	4	Black
01344.41T.01	18/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Red, Green	4	Black
01344.44.01	18/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Red, Green	4	Black
01344.46.01	18/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Red, Green	4	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
01344.35.01	18/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Red, Green	4	Black
01344.35T.01	18/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Red, Green	4	Black
01344.38T.01	18/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Red, Green	4	Black
01444.41T.05	18/4C SJOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Red, Green	4	Yellow
01444.35T.05	18/4C SJOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Red, Green	4	Yellow
01444.99.05	18/4C SJOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Red, Green	4	Yellow
01344.99.01M	18/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Red, Green	4	Black
01344.41T.01M	18/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Red, Green	4	Black
01344.44.01M	18/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Red, Green	4	Black
01344.35T.01M	18/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Red, Green	4	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
01444.35T.05M	18/4C SJOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Red, Green	4	Yellow
01358R.46.01	14/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White	2	Black
01358.41T.01M	14/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White	2	Black
01358.46.01M	14/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White	2	Black
01358.35T.01M	14/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White	2	Black
01312R.46.01	16/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White	2	Black
01358.99.01	14/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White	2	Black
01358.41T.01	14/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White	2	Black
01358.44.01	14/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White	2	Black
01358.46.01	14/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White	2	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
01358.35.01	14/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White	2	Black
01358.35T.01	14/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White	2	Black
01358.38.01	14/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White	2	Black
01358.82.01	14/2C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White	2	Black
01360.41T.04	14/3C SJOOW SUPER VUTRON III ORG	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Orange
01380R.44.01	12/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	NA	3	Black
01383R.41T.01	10/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
01362.41T.01	14/3C SJ BLK	CAROL (SIZE) (mm2) TYPE SJ 60°C (UL) --- CSA TYPE SJ-FT2 300 VOLT ROHS MADE IN USA	Other	Black, White, Green	3	Black
01460.41T.05M	14/3C SJOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Yellow
01460.35T.05M	14/3C SJOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Yellow

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
01460.41T.05	14/3C SJOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Yellow
01460.46.05	14/3C SJOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Yellow
01460.XX.05	14/3C SJOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Yellow
01460.35.05	14/3C SJOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Yellow
01460.35T.05	14/3C SJOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Yellow
01460.99.05	14/3C SJOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Yellow
01360.99.01	14/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
01360.41.01	14/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
01360.41T.01	14/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
01360.44.01	14/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
01360.46.01	14/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
01360.XX.01	14/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
01360.35.01	14/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
01360.35T.01	14/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
01360.38T.01	14/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
01360.82.01	14/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
01360.41T.01M	14/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
01360.44.01M	14/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
01360.XX.01M	14/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
01360.35T.01M	14/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
01360.38T.01M	14/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
01311R.46.01	18/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
01360R.44.01	14/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
01360R.46.01	14/3C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
01364.41T.02	14/4C SJOOW CAROLPRENE WHT	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Red, Green	4	White
01364.41T.01M	14/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	4	Black
01364.35T.01M	14/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	4	Black
01364.99.01	14/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Red, Green	4	Black
01364.41T.01	14/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Red, Green	4	Black
01364.46.01	14/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Red, Green	4	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
01364.L2.01	14/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Red, Green	4	Black
01364.35.01	14/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Red, Green	4	Black
01364.35T.01	14/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Red, Green	4	Black
01364.38T.01	14/4C SJOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Red, Green	4	Black
01464.15T.05	14/4C SJOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Red, Green	4	Yellow
01464.99.05	14/4C SJOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SJOOW CSA (-40°C) FT2 P-7K-123033 MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Red, Green	4	Yellow

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
01382.99.01	10/2C SJOOW CAROLPRENE BLK		0.045	0.56			1.14	14.22
01382.44.01	10/2C SJOOW CAROLPRENE BLK		0.045	0.56			1.14	14.22
01382.XX.01	10/2C SJOOW CAROLPRENE BLK		0.045	0.56			1.14	14.22
01483.XX.05	10/3C SJOOW CAROLPRENE YLW		0.045	0.58			1.14	14.73
01483.35T.05	10/3C SJOOW CAROLPRENE YLW		0.045	0.58			1.14	14.73
01377.41T.01	10/3C SJ BLK		0.045	0.58			1.14	14.73
01383.99.01M	10/3C SJOOW CAROLPRENE BLK		0.045	0.58			1.14	14.73
01383.41T.01M	10/3C SJOOW CAROLPRENE BLK		0.045	0.58			1.14	14.73
01383.46.01M	10/3C SJOOW CAROLPRENE BLK		0.045	0.58			1.14	14.73
01383.35T.01M	10/3C SJOOW CAROLPRENE BLK		0.045	0.58			1.14	14.73

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
01383.99.01	10/3C SJOOW CAROLPRENE BLK		0.045	0.58			1.14	14.73
01383.41T.01	10/3C SJOOW CAROLPRENE BLK		0.045	0.58			1.14	14.73
01383.44.01	10/3C SJOOW CAROLPRENE BLK		0.045	0.58			1.14	14.73
01383.46.01	10/3C SJOOW CAROLPRENE BLK		0.045	0.58			1.14	14.73
01383.XX.01	10/3C SJOOW CAROLPRENE BLK		0.045	0.58			1.14	14.73
01383.35T.01	10/3C SJOOW CAROLPRENE BLK		0.045	0.58			1.14	14.73
01383.85.01	10/3C SJOOW CAROLPRENE BLK		0.045	0.58			1.14	14.73
01384.41T.01M	10/4C SJOOW CAROLPRENE BLK		0.045	0.655			1.14	16.64
01384.35T.01M	10/4C SJOOW CAROLPRENE BLK		0.045	0.655			1.14	16.64
01384.85.01M	10/4C SJOOW CAROLPRENE BLK		0.045	0.655			1.14	16.64

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
01384.41T.01	10/4C SJOOW CAROLPRENE BLK		0.045	0.655			1.14	16.64
01384.44.01	10/4C SJOOW CAROLPRENE BLK		0.045	0.655			1.14	16.64
01384.XX.01	10/4C SJOOW CAROLPRENE BLK		0.045	0.655			1.14	16.64
01384.35.01	10/4C SJOOW CAROLPRENE BLK		0.045	0.655			1.14	16.64
01384.35T.01	10/4C SJOOW CAROLPRENE BLK		0.045	0.655			1.14	16.64
01384.38.01	10/4C SJOOW CAROLPRENE BLK		0.045	0.655			1.14	16.64
01384.85.01	10/4C SJOOW CAROLPRENE BLK		0.045	0.655			1.14	16.64
01379.99.01	12/2C SJOOW CAROLPRENE BLK		0.03	0.41			0.76	10.41
01379.41T.01	12/2C SJOOW CAROLPRENE BLK		0.03	0.41			0.76	10.41
01379.XX.01	12/2C SJOOW CAROLPRENE BLK		0.03	0.41			0.76	10.41

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
01379.35T.01	12/2C SJOOW CAROLPRENE BLK		0.03	0.41			0.76	10.41
01379.38T.01	12/2C SJOOW CAROLPRENE BLK		0.03	0.41			0.76	10.41
01379.41T.01M	12/2C SJOOW CAROLPRENE BLK		0.03	0.41			0.76	10.41
01379.35T.01M	12/2C SJOOW CAROLPRENE BLK		0.03	0.41			0.76	10.41
01368.41T.01	12/2C SJ BLK		0.03	0.41			0.76	10.41
01379.99.07	12/2C SJOOW CAROLPRENE BLUE		0.03	0.41			0.76	10.41
01380.99.01	12/3C SJOOW CAROLPRENE BLK		0.03	0.43			0.76	10.92
01380.41T.01	12/3C SJOOW CAROLPRENE BLK		0.03	0.43			0.76	10.92
01380.44.01	12/3C SJOOW CAROLPRENE BLK		0.03	0.43			0.76	10.92
01380.46.01	12/3C SJOOW CAROLPRENE BLK		0.03	0.43			0.76	10.92

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
01380.XX.01	12/3C SJOOW CAROLPRENE BLK		0.03	0.43			0.76	10.92
01380.15T.01	12/3C SJOOW CAROLPRENE BLK		0.03	0.43			0.76	10.92
01380.35.01	12/3C SJOOW CAROLPRENE BLK		0.03	0.43			0.76	10.92
01380.35T.01	12/3C SJOOW CAROLPRENE BLK		0.03	0.43			0.76	10.92
01380.38T.01	12/3C SJOOW CAROLPRENE BLK		0.03	0.43			0.76	10.92
01380.82.01	12/3C SJOOW CAROLPRENE BLK		0.03	0.43			0.76	10.92
01480.41T.05M	12/3C SJOOW CAROLPRENE YLW		0.03	0.43			0.76	10.92
01480.35T.05M	12/3C SJOOW CAROLPRENE YLW		0.03	0.43			0.76	10.92
01380.41T.04	12/3C SJOOW CAROLPRENE ORG		0.03	0.43			0.76	10.92
01380.35.04	12/3C SJOOW CAROLPRENE ORG		0.03	0.43			0.76	10.92

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
01480.41T.05	12/3C SJOOW CAROLPRENE YLW		0.03	0.43			0.76	10.92
01480.46.05	12/3C SJOOW CAROLPRENE YLW		0.03	0.43			0.76	10.92
01480.XX.05	12/3C SJOOW CAROLPRENE YLW		0.03	0.43			0.76	10.92
01480.35T.05	12/3C SJOOW CAROLPRENE YLW		0.03	0.43			0.76	10.92
01380.41T.01M	12/3C SJOOW CAROLPRENE BLK		0.03	0.43			0.76	10.92
01380.46.01M	12/3C SJOOW CAROLPRENE BLK		0.03	0.43			0.76	10.92
01380.XX.01M	12/3C SJOOW CAROLPRENE BLK		0.03	0.43			0.76	10.92
01380.35T.01M	12/3C SJOOW CAROLPRENE BLK		0.03	0.43			0.76	10.92
01380.38T.01M	12/3C SJOOW CAROLPRENE BLK		0.03	0.43			0.76	10.92
01380.41T.02	12/3C SJOOW CAROLPRENE WHT		0.03	0.43			0.76	10.92

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
01380.XX.02	12/3C SJOOW CAROLPRENE WHT		0.03	0.43			0.76	10.92
01381.99.01	12/4C SJOOW CAROLPRENE BLK		0.03	0.475			0.76	12.07
01381.41T.01	12/4C SJOOW CAROLPRENE BLK		0.03	0.475			0.76	12.07
01381.46.01	12/4C SJOOW CAROLPRENE BLK		0.03	0.475			0.76	12.07
01381.XX.01	12/4C SJOOW CAROLPRENE BLK		0.03	0.475			0.76	12.07
01381.35T.01	12/4C SJOOW CAROLPRENE BLK		0.03	0.475			0.76	12.07
01381.38T.01	12/4C SJOOW CAROLPRENE BLK		0.03	0.475			0.76	12.07
01381.85.01	12/4C SJOOW CAROLPRENE BLK		0.03	0.475			0.76	12.07
01381.99.01M	12/4C SJOOW CAROLPRENE BLK		0.03	0.475			0.76	12.07
01381.41T.01M	12/4C SJOOW CAROLPRENE BLK		0.03	0.475			0.76	12.07

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
01381.46.01M	12/4C SJOOW CAROLPRENE BLK		0.03	0.475			0.76	12.07
01381.35T.01M	12/4C SJOOW CAROLPRENE BLK		0.03	0.475			0.76	12.07
01381.38T.01M	12/4C SJOOW CAROLPRENE BLK		0.03	0.475			0.76	12.07
01381.85.01M	12/4C SJOOW CAROLPRENE BLK		0.03	0.475			0.76	12.07
01481.35T.05	12/4C SJOOW CAROLPRENE YLW		0.03	0.475			0.76	12.07
01481.35T.05M	12/4C SJOOW CAROLPRENE YLW		0.03	0.475			0.76	12.07
01312.41T.01M	16/2C SJOOW CAROLPRENE BLK		0.03	0.31			0.76	7.87
01312.35T.01M	16/2C SJOOW CAROLPRENE BLK		0.03	0.31			0.76	7.87
01312.38.01M	16/2C SJOOW CAROLPRENE BLK		0.03	0.31			0.76	7.87
01312.99.01	16/2C SJOOW CAROLPRENE BLK		0.03	0.31			0.76	7.87

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
01312.41.01	16/2C SJOOW CAROLPRENE BLK		0.03	0.31			0.76	7.87
01312.41T.01	16/2C SJOOW CAROLPRENE BLK		0.03	0.31			0.76	7.87
01312.44.01	16/2C SJOOW CAROLPRENE BLK		0.03	0.31			0.76	7.87
01312.46.01	16/2C SJOOW CAROLPRENE BLK		0.03	0.31			0.76	7.87
01312.L2.01	16/2C SJOOW CAROLPRENE BLK		0.03	0.31			0.76	7.87
01312.35.01	16/2C SJOOW CAROLPRENE BLK		0.03	0.31			0.76	7.87
01312.35T.01	16/2C SJOOW CAROLPRENE BLK		0.03	0.31			0.76	7.87
01312.38.01	16/2C SJOOW CAROLPRENE BLK		0.03	0.31			0.76	7.87
01312.38T.01	16/2C SJOOW CAROLPRENE BLK		0.03	0.31			0.76	7.87
01312.82.01	16/2C SJOOW CAROLPRENE BLK		0.03	0.31			0.76	7.87

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
01312.L1.01	16/2C SJOOW CAROLPRENE BLK		0.03	0.31			0.76	7.87
01342.44.02M	16/3C SJOOW CAROLPRENE WHT		0.03	0.33			0.76	8.38
01442.35T.05M	16/3C SJOOW CAROLPRENE YLW		0.03	0.33			0.76	8.38
01442.35T.05	16/3C SJOOW CAROLPRENE YLW		0.03	0.33			0.76	8.38
01342R.46.01	16/3C SJOOW CAROLPRENE BLK		0.03	0.33			0.76	8.38
01342.44.02	16/3C SJOOW CAROLPRENE WHT		0.03	0.33			0.76	8.38
01306.41T.01	16/3C SJ BLK		0.03	0.33			0.76	8.38
01306.46.01	16/3C SJ BLK		0.03	0.33			0.76	8.38
01342.99.01M	16/3C SJOOW CAROLPRENE BLK		0.03	0.33			0.76	8.38
01342.41T.01M	16/3C SJOOW CAROLPRENE BLK		0.03	0.33			0.76	8.38

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
01342.44.01M	16/3C SJOOW CAROLPRENE BLK		0.03	0.33			0.76	8.38
01342.46.01M	16/3C SJOOW CAROLPRENE BLK		0.03	0.33			0.76	8.38
01342.XX.01M	16/3C SJOOW CAROLPRENE BLK		0.03	0.33			0.76	8.38
01342.35.01M	16/3C SJOOW CAROLPRENE BLK		0.03	0.33			0.76	8.38
01342.35T.01M	16/3C SJOOW CAROLPRENE BLK		0.03	0.33			0.76	8.38
01342.99.01	16/3C SJOOW CAROLPRENE BLK		0.03	0.33			0.76	8.38
01342.41.01	16/3C SJOOW CAROLPRENE BLK		0.03	0.33			0.76	8.38
01342.41T.01	16/3C SJOOW CAROLPRENE BLK		0.03	0.33			0.76	8.38
01342.44.01	16/3C SJOOW CAROLPRENE BLK		0.03	0.33			0.76	8.38
01342.46.01	16/3C SJOOW CAROLPRENE BLK		0.03	0.33			0.76	8.38

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
01342.35.01	16/3C SJOOW CAROLPRENE BLK		0.03	0.33			0.76	8.38
01342.35T.01	16/3C SJOOW CAROLPRENE BLK		0.03	0.33			0.76	8.38
01342.38.01	16/3C SJOOW CAROLPRENE BLK		0.03	0.33			0.76	8.38
01342.38T.01	16/3C SJOOW CAROLPRENE BLK		0.03	0.33			0.76	8.38
01342.82.01	16/3C SJOOW CAROLPRENE BLK		0.03	0.33			0.76	8.38
01343.99.01	16/4C SJOOW CAROLPRENE BLK		0.03	0.365			0.76	9.27
01343.41T.01	16/4C SJOOW CAROLPRENE BLK		0.03	0.365			0.76	9.27
01343.44.01	16/4C SJOOW CAROLPRENE BLK		0.03	0.365			0.76	9.27
01343.46.01	16/4C SJOOW CAROLPRENE BLK		0.03	0.365			0.76	9.27
01343.35.01	16/4C SJOOW CAROLPRENE BLK		0.03	0.365			0.76	9.27

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
01343.35T.01	16/4C SJOOW CAROLPRENE BLK		0.03	0.365			0.76	9.27
01343.38.01	16/4C SJOOW CAROLPRENE BLK		0.03	0.365			0.76	9.27
01343.41T.01M	16/4C SJOOW CAROLPRENE BLK		0.03	0.365			0.76	9.27
01343.46.01M	16/4C SJOOW CAROLPRENE BLK		0.03	0.365			0.76	9.27
01343.35T.01M	16/4C SJOOW CAROLPRENE BLK		0.03	0.365			0.76	9.27
01310.99.01	18/2C SJOOW CAROLPRENE BLK		0.03	0.285			0.76	7.24
01310.41T.01	18/2C SJOOW CAROLPRENE BLK		0.03	0.285			0.76	7.24
01310.46.01	18/2C SJOOW CAROLPRENE BLK		0.03	0.285			0.76	7.24
01310.L2.01	18/2C SJOOW CAROLPRENE BLK		0.03	0.285			0.76	7.24
01310.35.01	18/2C SJOOW CAROLPRENE BLK		0.03	0.285			0.76	7.24

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
01310.35T.01	18/2C SJOOW CAROLPRENE BLK		0.03	0.285			0.76	7.24
01310.38T.01	18/2C SJOOW CAROLPRENE BLK		0.03	0.285			0.76	7.24
01310.L1.01	18/2C SJOOW CAROLPRENE BLK		0.03	0.285			0.76	7.24
01310.99.01M	18/2C SJOOW CAROLPRENE BLK		0.03	0.285			0.76	7.24
01310.41T.01M	18/2C SJOOW CAROLPRENE BLK		0.03	0.285			0.76	7.24
01310.46.01M	18/2C SJOOW CAROLPRENE BLK		0.03	0.285			0.76	7.24
01310.XX.01M	18/2C SJOOW CAROLPRENE BLK		0.03	0.285			0.76	7.24
01310.35.01M	18/2C SJOOW CAROLPRENE BLK		0.03	0.285			0.76	7.24
01310.35T.01M	18/2C SJOOW CAROLPRENE BLK		0.03	0.285			0.76	7.24
01310.38T.01M	18/2C SJOOW CAROLPRENE BLK		0.03	0.285			0.76	7.24

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
01311.99.01M	18/3C SJOOW CAROLPRENE BLK		0.03	0.305			0.76	7.75
01311.41T.01M	18/3C SJOOW CAROLPRENE BLK		0.03	0.305			0.76	7.75
01311.44.01M	18/3C SJOOW CAROLPRENE BLK		0.03	0.305			0.76	7.75
01311.46.01M	18/3C SJOOW CAROLPRENE BLK		0.03	0.305			0.76	7.75
01311.35T.01M	18/3C SJOOW CAROLPRENE BLK		0.03	0.305			0.76	7.75
01311.38T.01M	18/3C SJOOW CAROLPRENE BLK		0.03	0.305			0.76	7.75
01311.99.01	18/3C SJOOW CAROLPRENE BLK		0.03	0.305			0.76	7.75
01311.41.01	18/3C SJOOW CAROLPRENE BLK		0.03	0.305			0.76	7.75
01311.41T.01	18/3C SJOOW CAROLPRENE BLK		0.03	0.305			0.76	7.75
01311.44.01	18/3C SJOOW CAROLPRENE BLK		0.03	0.305			0.76	7.75

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
01311.46.01	18/3C SJOOW CAROLPRENE BLK		0.03	0.305			0.76	7.75
01311.L2.01	18/3C SJOOW CAROLPRENE BLK		0.03	0.305			0.76	7.75
01311.35.01	18/3C SJOOW CAROLPRENE BLK		0.03	0.305			0.76	7.75
01311.35T.01	18/3C SJOOW CAROLPRENE BLK		0.03	0.305			0.76	7.75
01311.38T.01	18/3C SJOOW CAROLPRENE BLK		0.03	0.305			0.76	7.75
01304.41.01	18/4C SJ BLK		0.03	0.33			0.76	8.38
01344.99.01	18/4C SJOOW CAROLPRENE BLK		0.03	0.33			0.76	8.38
01344.41T.01	18/4C SJOOW CAROLPRENE BLK		0.03	0.33			0.76	8.38
01344.44.01	18/4C SJOOW CAROLPRENE BLK		0.03	0.33			0.76	8.38
01344.46.01	18/4C SJOOW CAROLPRENE BLK		0.03	0.33			0.76	8.38

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
01344.35.01	18/4C SJOOW CAROLPRENE BLK		0.03	0.33			0.76	8.38
01344.35T.01	18/4C SJOOW CAROLPRENE BLK		0.03	0.33			0.76	8.38
01344.38T.01	18/4C SJOOW CAROLPRENE BLK		0.03	0.33			0.76	8.38
01444.41T.05	18/4C SJOOW CAROLPRENE YLW		0.03	0.33			0.76	8.38
01444.35T.05	18/4C SJOOW CAROLPRENE YLW		0.03	0.33			0.76	8.38
01444.99.05	18/4C SJOOW CAROLPRENE YLW		0.03	0.33			0.76	8.38
01344.99.01M	18/4C SJOOW CAROLPRENE BLK		0.03	0.33			0.76	8.38
01344.41T.01M	18/4C SJOOW CAROLPRENE BLK		0.03	0.33			0.76	8.38
01344.44.01M	18/4C SJOOW CAROLPRENE BLK		0.03	0.33			0.76	8.38
01344.35T.01M	18/4C SJOOW CAROLPRENE BLK		0.03	0.33			0.76	8.38

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
01444.35T.05M	18/4C SJOOW CAROLPRENE YLW		0.03	0.33			0.76	8.38
01358R.46.01	14/3C SJOOW CAROLPRENE BLK							
01358.41T.01M	14/2C SJOOW CAROLPRENE BLK		0.03	0.34			0.76	8.64
01358.46.01M	14/2C SJOOW CAROLPRENE BLK		0.03	0.34			0.76	8.64
01358.35T.01M	14/2C SJOOW CAROLPRENE BLK		0.03	0.34			0.76	8.64
01312R.46.01	16/2C SJOOW CAROLPRENE BLK							
01358.99.01	14/2C SJOOW CAROLPRENE BLK		0.03	0.34			0.76	8.64
01358.41T.01	14/2C SJOOW CAROLPRENE BLK		0.03	0.34			0.76	8.64
01358.44.01	14/2C SJOOW CAROLPRENE BLK		0.03	0.34			0.76	8.64
01358.46.01	14/2C SJOOW CAROLPRENE BLK		0.03	0.34			0.76	8.64

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
01358.35.01	14/2C SJOOW CAROLPRENE BLK		0.03	0.34			0.76	8.64
01358.35T.01	14/2C SJOOW CAROLPRENE BLK		0.03	0.34			0.76	8.64
01358.38.01	14/2C SJOOW CAROLPRENE BLK		0.03	0.34			0.76	8.64
01358.82.01	14/2C SJOOW CAROLPRENE BLK		0.03	0.34			0.76	8.64
01360.41T.04	14/3C SJOOW SUPER VUTRON III ORG		0.03	0.37			0.76	9.4
01380R.44.01	12/3C SJOOW CAROLPRENE BLK							
01383R.41T.01	10/3C SJOOW CAROLPRENE BLK							
01362.41T.01	14/3C SJ BLK		0.03	0.37			0.76	9.4
01460.41T.05M	14/3C SJOOW CAROLPRENE YLW		0.03	0.37			0.76	9.4
01460.35T.05M	14/3C SJOOW CAROLPRENE YLW		0.03	0.37			0.76	9.4

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
01460.41T.05	14/3C SJOOW CAROLPRENE YLW		0.03	0.37			0.76	9.4
01460.46.05	14/3C SJOOW CAROLPRENE YLW		0.03	0.37			0.76	9.4
01460.XX.05	14/3C SJOOW CAROLPRENE YLW		0.03	0.37			0.76	9.4
01460.35.05	14/3C SJOOW CAROLPRENE YLW		0.03	0.37			0.76	9.4
01460.35T.05	14/3C SJOOW CAROLPRENE YLW		0.03	0.37			0.76	9.4
01460.99.05	14/3C SJOOW CAROLPRENE YLW		0.03	0.37			0.76	9.4
01360.99.01	14/3C SJOOW CAROLPRENE BLK		0.03	0.37			0.76	9.4
01360.41.01	14/3C SJOOW CAROLPRENE BLK		0.03	0.37			0.76	9.4
01360.41T.01	14/3C SJOOW CAROLPRENE BLK		0.03	0.37			0.76	9.4
01360.44.01	14/3C SJOOW CAROLPRENE BLK		0.03	0.37			0.76	9.4

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
01360.46.01	14/3C SJOOW CAROLPRENE BLK		0.03	0.37			0.76	9.4
01360.XX.01	14/3C SJOOW CAROLPRENE BLK		0.03	0.37			0.76	9.4
01360.35.01	14/3C SJOOW CAROLPRENE BLK		0.03	0.37			0.76	9.4
01360.35T.01	14/3C SJOOW CAROLPRENE BLK		0.03	0.37			0.76	9.4
01360.38T.01	14/3C SJOOW CAROLPRENE BLK		0.03	0.37			0.76	9.4
01360.82.01	14/3C SJOOW CAROLPRENE BLK		0.03	0.37			0.76	9.4
01360.41T.01M	14/3C SJOOW CAROLPRENE BLK		0.03	0.37			0.76	9.4
01360.44.01M	14/3C SJOOW CAROLPRENE BLK		0.03	0.37			0.76	9.4
01360.XX.01M	14/3C SJOOW CAROLPRENE BLK		0.03	0.37			0.76	9.4
01360.35T.01M	14/3C SJOOW CAROLPRENE BLK		0.03	0.37			0.76	9.4

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
01360.38T.01M	14/3C SJOOW CAROLPRENE BLK		0.03	0.37			0.76	9.4
01311R.46.01	18/3C SJOOW CAROLPRENE BLK							
01360R.44.01	14/3C SJOOW CAROLPRENE BLK							
01360R.46.01	14/3C SJOOW CAROLPRENE BLK							
01364.41T.02	14/4C SJOOW CAROLPRENE WHT		0.03	0.41			0.76	10.41
01364.41T.01M	14/4C SJOOW CAROLPRENE BLK		0.03	0.41			0.76	10.41
01364.35T.01M	14/4C SJOOW CAROLPRENE BLK		0.03	0.41			0.76	10.41
01364.99.01	14/4C SJOOW CAROLPRENE BLK		0.03	0.41			0.76	10.41
01364.41T.01	14/4C SJOOW CAROLPRENE BLK		0.03	0.41			0.76	10.41
01364.46.01	14/4C SJOOW CAROLPRENE BLK		0.03	0.41			0.76	10.41

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
01364.L2.01	14/4C SJOOW CAROLPRENE BLK		0.03	0.41			0.76	10.41
01364.35.01	14/4C SJOOW CAROLPRENE BLK		0.03	0.41			0.76	10.41
01364.35T.01	14/4C SJOOW CAROLPRENE BLK		0.03	0.41			0.76	10.41
01364.38T.01	14/4C SJOOW CAROLPRENE BLK		0.03	0.41			0.76	10.41
01464.15T.05	14/4C SJOOW CAROLPRENE YLW		0.03	0.41			0.76	10.41
01464.99.05	14/4C SJOOW CAROLPRENE YLW		0.03	0.41			0.76	10.41

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	01382.99.01	10/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	190	LBS
	01382.44.01	10/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	190	LBS
	01382.XX.01	10/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	190	LBS
	01483.XX.05	10/3C SJOOW CAROLPRENE YLW	US	Distribution products	MTO	242	LBS
	01483.35T.05	10/3C SJOOW CAROLPRENE YLW	US	Distribution products	MTO	242	LBS
	01377.41T.01	10/3C SJ BLK	US	Distribution products	MTO	243	LBS
	01383.99.01M	10/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	236	LBS
	01383.41T.01M	10/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	236	LBS
	01383.46.01M	10/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	236	LBS
	01383.35T.01M	10/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	236	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	01383.99.01	10/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	236	LBS
	01383.41T.01	10/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	236	LBS
	01383.44.01	10/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	236	LBS
	01383.46.01	10/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	236	LBS
	01383.XX.01	10/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	236	LBS
	01383.35T.01	10/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	236	LBS
	01383.85.01	10/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	236	LBS
	01384.41T.01M	10/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	296	LBS
	01384.35T.01M	10/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	296	LBS
	01384.85.01M	10/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	296	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	01384.41T.01	10/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	296	LBS
	01384.44.01	10/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	296	LBS
	01384.XX.01	10/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	296	LBS
	01384.35.01	10/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	296	LBS
	01384.35T.01	10/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	296	LBS
	01384.38.01	10/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	296	LBS
	01384.85.01	10/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	296	LBS
	01379.99.01	12/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	108	LBS
	01379.41T.01	12/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	108	LBS
	01379.XX.01	12/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	108	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	01379.35T.01	12/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	108	LBS
	01379.38T.01	12/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	108	LBS
	01379.41T.01M	12/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	108	LBS
	01379.35T.01M	12/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	108	LBS
	01368.41T.01	12/2C SJ BLK	US	Distribution products	MTO	117	LBS
	01379.99.07	12/2C SJOOW CAROLPRENE BLUE	US	Distribution products	MTO	108	LBS
	01380.99.01	12/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	136	LBS
	01380.41T.01	12/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	136	LBS
	01380.44.01	12/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	136	LBS
	01380.46.01	12/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	136	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	01380.XX.01	12/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	136	LBS
	01380.15T.01	12/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	136	LBS
	01380.35.01	12/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	136	LBS
	01380.35T.01	12/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	136	LBS
	01380.38T.01	12/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	136	LBS
	01380.82.01	12/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	136	LBS
	01480.41T.05M	12/3C SJOOW CAROLPRENE YLW	US	Distribution products	MTO	146	LBS
	01480.35T.05M	12/3C SJOOW CAROLPRENE YLW	US	Distribution products	MTO	146	LBS
	01380.41T.04	12/3C SJOOW CAROLPRENE ORG	US	Distribution products	MTO	136	LBS
	01380.35.04	12/3C SJOOW CAROLPRENE ORG	US	Distribution products	MTO	136	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	01480.41T.05	12/3C SJOOW CAROLPRENE YLW	US	Distribution products	MTO	146	LBS
	01480.46.05	12/3C SJOOW CAROLPRENE YLW	US	Distribution products	MTO	146	LBS
	01480.XX.05	12/3C SJOOW CAROLPRENE YLW	US	Distribution products	MTO	146	LBS
	01480.35T.05	12/3C SJOOW CAROLPRENE YLW	US	Distribution products	MTS	146	LBS
	01380.41T.01M	12/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	136	LBS
	01380.46.01M	12/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	136	LBS
	01380.XX.01M	12/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	136	LBS
	01380.35T.01M	12/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	136	LBS
	01380.38T.01M	12/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	136	LBS
	01380.41T.02	12/3C SJOOW CAROLPRENE WHT	US	Distribution products	MTO	136	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	01380.XX.02	12/3C SJOOW CAROLPRENE WHT	US	Distribution products	MTO	136	LBS
	01381.99.01	12/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	177	LBS
	01381.41T.01	12/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	177	LBS
	01381.46.01	12/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	177	LBS
	01381.XX.01	12/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	177	LBS
	01381.35T.01	12/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	177	LBS
	01381.38T.01	12/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	177	LBS
	01381.85.01	12/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	177	LBS
	01381.99.01M	12/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	177	LBS
	01381.41T.01M	12/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	177	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	01381.46.01M	12/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	177	LBS
	01381.35T.01M	12/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	177	LBS
	01381.38T.01M	12/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	177	LBS
	01381.85.01M	12/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	177	LBS
	01481.35T.05	12/4C SJOOW CAROLPRENE YLW	US	Distribution products	MTO	185	LBS
	01481.35T.05M	12/4C SJOOW CAROLPRENE YLW	US	Distribution products	MTO	185	LBS
	01312.41T.01M	16/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	56	LBS
	01312.35T.01M	16/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	56	LBS
	01312.38.01M	16/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	56	LBS
	01312.99.01	16/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	56	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	01312.41.01	16/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	56	LBS
	01312.41T.01	16/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	56	LBS
	01312.44.01	16/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	56	LBS
	01312.46.01	16/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	56	LBS
	01312.L2.01	16/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	56	LBS
	01312.35.01	16/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	56	LBS
	01312.35T.01	16/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	56	LBS
	01312.38.01	16/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	56	LBS
	01312.38T.01	16/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	56	LBS
	01312.82.01	16/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	56	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	01312.L1.01	16/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	56	LBS
	01342.44.02M	16/3C SJOOW CAROLPRENE WHT	US	Distribution products	MTO	72	LBS
	01442.35T.05M	16/3C SJOOW CAROLPRENE YLW	US	Distribution products	MTO	76	LBS
	01442.35T.05	16/3C SJOOW CAROLPRENE YLW	US	Distribution products	MTS	76	LBS
	01342R.46.01	16/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	72	LBS
	01342.44.02	16/3C SJOOW CAROLPRENE WHT	US	Distribution products	MTO	72	LBS
	01306.41T.01	16/3C SJ BLK	US	Distribution products	MTO	76	LBS
	01306.46.01	16/3C SJ BLK	US	Distribution products	MTO	76	LBS
	01342.99.01M	16/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	72	LBS
	01342.41T.01M	16/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	72	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	01342.44.01M	16/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	72	LBS
	01342.46.01M	16/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	72	LBS
	01342.XX.01M	16/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	72	LBS
	01342.35.01M	16/3C SJOOW CAROLPRENE BLK	US	Distribution products		72	LBS
	01342.35T.01M	16/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	72	LBS
	01342.99.01	16/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	72	LBS
	01342.41.01	16/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	72	LBS
	01342.41T.01	16/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	72	LBS
	01342.44.01	16/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	72	LBS
	01342.46.01	16/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	72	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	01342.35.01	16/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	72	LBS
	01342.35T.01	16/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	72	LBS
	01342.38.01	16/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	72	LBS
	01342.38T.01	16/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	72	LBS
	01342.82.01	16/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	72	LBS
	01343.99.01	16/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	89	LBS
	01343.41T.01	16/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	89	LBS
	01343.44.01	16/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	89	LBS
	01343.46.01	16/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	89	LBS
	01343.35.01	16/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	89	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	01343.35T.01	16/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	89	LBS
	01343.38.01	16/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	89	LBS
	01343.41T.01M	16/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	89	LBS
	01343.46.01M	16/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	89	LBS
	01343.35T.01M	16/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	89	LBS
	01310.99.01	18/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	46	LBS
	01310.41T.01	18/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	46	LBS
	01310.46.01	18/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	46	LBS
	01310.L2.01	18/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	46	LBS
	01310.35.01	18/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	46	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	01310.35T.01	18/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	46	LBS
	01310.38T.01	18/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	46	LBS
	01310.L1.01	18/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	46	LBS
	01310.99.01M	18/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	46	LBS
	01310.41T.01M	18/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	46	LBS
	01310.46.01M	18/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	46	LBS
	01310.XX.01M	18/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	46	LBS
	01310.35.01M	18/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	46	LBS
	01310.35T.01M	18/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	46	LBS
	01310.38T.01M	18/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	46	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	01311.99.01M	18/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	60	LBS
	01311.41T.01M	18/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	60	LBS
	01311.44.01M	18/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	60	LBS
	01311.46.01M	18/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	60	LBS
	01311.35T.01M	18/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	60	LBS
	01311.38T.01M	18/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	60	LBS
	01311.99.01	18/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	60	LBS
	01311.41.01	18/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	60	LBS
	01311.41T.01	18/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	60	LBS
	01311.44.01	18/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	60	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	01311.46.01	18/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	60	LBS
	01311.L2.01	18/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	60	LBS
	01311.35.01	18/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	60	LBS
	01311.35T.01	18/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	60	LBS
	01311.38T.01	18/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	60	LBS
	01304.41.01	18/4C SJ BLK	US	Distribution products	MTO	76	LBS
	01344.99.01	18/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	72	LBS
	01344.41T.01	18/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	72	LBS
	01344.44.01	18/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	72	LBS
	01344.46.01	18/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	72	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	01344.35.01	18/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	72	LBS
	01344.35T.01	18/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	72	LBS
	01344.38T.01	18/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	72	LBS
	01444.41T.05	18/4C SJOOW CAROLPRENE YLW	US	Distribution products	MTO	76	LBS
	01444.35T.05	18/4C SJOOW CAROLPRENE YLW	US	Distribution products	MTS	76	LBS
	01444.99.05	18/4C SJOOW CAROLPRENE YLW	US	Distribution products	MTO	76	LBS
	01344.99.01M	18/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	72	LBS
	01344.41T.01M	18/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	72	LBS
	01344.44.01M	18/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	72	LBS
	01344.35T.01M	18/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	72	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	01444.35T.05M	18/4C SJOOW CAROLPRENE YLW	US	Distribution products	MTO	76	LBS
	01358R.46.01	14/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO		LBS
	01358.41T.01M	14/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	75	LBS
	01358.46.01M	14/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	75	LBS
	01358.35T.01M	14/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	75	LBS
	01312R.46.01	16/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO		LBS
	01358.99.01	14/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	75	LBS
	01358.41T.01	14/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	75	LBS
	01358.44.01	14/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	75	LBS
	01358.46.01	14/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	75	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	01358.35.01	14/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	75	LBS
	01358.35T.01	14/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	75	LBS
	01358.38.01	14/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	75	LBS
	01358.82.01	14/2C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	75	LBS
	01360.41T.04	14/3C SJOOW SUPER VUTRON III ORG	US	Distribution products	MTO	100	LBS
	01380R.44.01	12/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO		LBS
	01383R.41T.01	10/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO		LBS
	01362.41T.01	14/3C SJ BLK	US	Distribution products	MTO	106	LBS
	01460.41T.05M	14/3C SJOOW CAROLPRENE YLW	US	Distribution products	MTS	106	LBS
	01460.35T.05M	14/3C SJOOW CAROLPRENE YLW	US	Distribution products	MTO	106	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	01460.41T.05	14/3C SJOOW CAROLPRENE YLW	US	Distribution products	MTS	106	LBS
	01460.46.05	14/3C SJOOW CAROLPRENE YLW	US	Distribution products	MTO	106	LBS
	01460.XX.05	14/3C SJOOW CAROLPRENE YLW	US	Distribution products	MTO	106	LBS
	01460.35.05	14/3C SJOOW CAROLPRENE YLW	US	Distribution products	MTO	106	LBS
	01460.35T.05	14/3C SJOOW CAROLPRENE YLW	US	Distribution products	MTS	106	LBS
	01460.99.05	14/3C SJOOW CAROLPRENE YLW	US	Distribution products	MTO	106	LBS
	01360.99.01	14/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	100	LBS
	01360.41.01	14/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	100	LBS
	01360.41T.01	14/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	100	LBS
	01360.44.01	14/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	100	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	01360.46.01	14/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	100	LBS
	01360.XX.01	14/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	100	LBS
	01360.35.01	14/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	100	LBS
	01360.35T.01	14/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	100	LBS
	01360.38T.01	14/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	100	LBS
	01360.82.01	14/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	100	LBS
	01360.41T.01M	14/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	100	LBS
	01360.44.01M	14/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	100	LBS
	01360.XX.01M	14/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	100	LBS
	01360.35T.01M	14/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	100	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	01360.38T.01M	14/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	100	LBS
	01311R.46.01	18/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO		LBS
	01360R.44.01	14/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO		LBS
	01360R.46.01	14/3C SJOOW CAROLPRENE BLK	US	Distribution products	MTO		LBS
	01364.41T.02	14/4C SJOOW CAROLPRENE WHT	US	Distribution products	MTO	128	LBS
	01364.41T.01M	14/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	128	LBS
	01364.35T.01M	14/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	128	LBS
	01364.99.01	14/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	128	LBS
	01364.41T.01	14/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	128	LBS
	01364.46.01	14/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	128	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	01364.L2.01	14/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	128	LBS
	01364.35.01	14/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	128	LBS
	01364.35T.01	14/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTS	128	LBS
	01364.38T.01	14/4C SJOOW CAROLPRENE BLK	US	Distribution products	MTO	128	LBS
	01464.15T.05	14/4C SJOOW CAROLPRENE YLW	US	Distribution products	MTO	121	LBS
	01464.99.05	14/4C SJOOW CAROLPRENE YLW	US	Distribution products	MTO	121	LBS

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
01382.99.01	10/2C SJOOW CAROLPRENE BLK	FOOT	22	20	18	Factory Reel
01382.44.01	10/2C SJOOW CAROLPRENE BLK	FOOT	22	20	1	2500 FT Reel
01382.XX.01	10/2C SJOOW CAROLPRENE BLK	FOOT	22	20	1	Various Lengths
01483.XX.05	10/3C SJOOW CAROLPRENE YLW	FOOT	48	42	1	Various Lengths
01483.35T.05	10/3C SJOOW CAROLPRENE YLW	FOOT	14	14	12	250 FT Reel
01377.41T.01	10/3C SJ BLK	FOOT	24	22	24	1000 FT Reel
01383.99.01M	10/3C SJOOW CAROLPRENE BLK	FOOT	48	42	1	Factory Reel
01383.41T.01M	10/3C SJOOW CAROLPRENE BLK	FOOT	22	20	1	1000 FT Reel
01383.46.01M	10/3C SJOOW CAROLPRENE BLK	FOOT	22	20	1	5000 FT Reel
01383.35T.01M	10/3C SJOOW CAROLPRENE BLK	FOOT	14	13	14	250 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
01383.99.01	10/3C SJOOW CAROLPRENE BLK	FOOT	48	42	48	Factory Reel
01383.41T.01	10/3C SJOOW CAROLPRENE BLK	FOOT	24	22	24	1000 FT Reel
01383.44.01	10/3C SJOOW CAROLPRENE BLK	FOOT	32	26	32	2500 FT Reel
01383.46.01	10/3C SJOOW CAROLPRENE BLK	FOOT	32	26	32	5000 FT Reel
01383.XX.01	10/3C SJOOW CAROLPRENE BLK	FOOT	48	42	48	Various Lengths
01383.35T.01	10/3C SJOOW CAROLPRENE BLK	FOOT	14	13	14	250 FT Reel
01383.85.01	10/3C SJOOW CAROLPRENE BLK	FOOT	20	21	14	250 FT Coil
01384.41T.01M	10/4C SJOOW CAROLPRENE BLK	FOOT	22	20	1	1000 FT Reel
01384.35T.01M	10/4C SJOOW CAROLPRENE BLK	FOOT	22	20	1	250 FT Reel
01384.85.01M	10/4C SJOOW CAROLPRENE BLK	FOOT	21	21	9	250 FT Coil

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
01384.41T.01	10/4C SJOOW CAROLPRENE BLK	FOOT	24	22	24	1000 FT Reel
01384.44.01	10/4C SJOOW CAROLPRENE BLK	FOOT	22	20	1	2500 FT Reel
01384.XX.01	10/4C SJOOW CAROLPRENE BLK	FOOT	48	42	1	Various Lengths
01384.35.01	10/4C SJOOW CAROLPRENE BLK	FOOT	16	13	16	250 FT Reel
01384.35T.01	10/4C SJOOW CAROLPRENE BLK	FOOT	16	13	16	250 FT Reel
01384.38.01	10/4C SJOOW CAROLPRENE BLK	FOOT	22	20	18	500 FT Reel
01384.85.01	10/4C SJOOW CAROLPRENE BLK	FOOT	20	21	7	250 FT Coil
01379.99.01	12/2C SJOOW CAROLPRENE BLK	FOOT	48	42	1	Factory Reel
01379.41T.01	12/2C SJOOW CAROLPRENE BLK	FOOT	20	13	20	1000 FT Reel
01379.XX.01	12/2C SJOOW CAROLPRENE BLK	FOOT	48	42	1	Various Lengths

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
01379.35T.01	12/2C SJOOW CAROLPRENE BLK	FOOT	11	11	11	250 FT Reel
01379.38T.01	12/2C SJOOW CAROLPRENE BLK	FOOT	22	20	1	500 FT Reel
01379.41T.01M	12/2C SJOOW CAROLPRENE BLK	FOOT	22	20	1	1000 FT Reel
01379.35T.01M	12/2C SJOOW CAROLPRENE BLK	FOOT	11	11	11	250 FT Reel
01368.41T.01	12/2C SJ BLK	FOOT	20	13	20	1000 FT Reel
01379.99.07	12/2C SJOOW CAROLPRENE BLUE	FOOT	20	13	20	Factory Reel
01380.99.01	12/3C SJOOW CAROLPRENE BLK	FOOT	48	42	1	Factory Reel
01380.41T.01	12/3C SJOOW CAROLPRENE BLK	FOOT	18	13	18	1000 FT Reel
01380.44.01	12/3C SJOOW CAROLPRENE BLK	FOOT	30	22	30	2500 FT Reel
01380.46.01	12/3C SJOOW CAROLPRENE BLK	FOOT	30	22	30	5000 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
01380.XX.01	12/3C SJOOW CAROLPRENE BLK	FOOT	48	42	1	Various Lengths
01380.15T.01	12/3C SJOOW CAROLPRENE BLK	FOOT	11	11	11	250 FT Spool
01380.35.01	12/3C SJOOW CAROLPRENE BLK	FOOT	11	11	11	250 FT Reel
01380.35T.01	12/3C SJOOW CAROLPRENE BLK	FOOT	11	11	11	250 FT Reel
01380.38T.01	12/3C SJOOW CAROLPRENE BLK	FOOT	16	13	16	500 FT Reel
01380.82.01	12/3C SJOOW CAROLPRENE BLK	FOOT	11	11	8	50 FT Hanging Cuff
01480.41T.05M	12/3C SJOOW CAROLPRENE YLW	FOOT	18	18	12	1000 FT Reel
01480.35T.05M	12/3C SJOOW CAROLPRENE YLW	FOOT	1	1	1	250 FT Reel
01380.41T.04	12/3C SJOOW CAROLPRENE ORG	FOOT	18	13	18	1000 FT Reel
01380.35.04	12/3C SJOOW CAROLPRENE ORG	FOOT	11	11	11	250 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
01480.41T.05	12/3C SJOOW CAROLPRENE YLW	FOOT	18	18	12	1000 FT Reel
01480.46.05	12/3C SJOOW CAROLPRENE YLW	FOOT	18	18	12	5000 FT Reel
01480.XX.05	12/3C SJOOW CAROLPRENE YLW	FOOT	48	42	1	Various Lengths
01480.35T.05	12/3C SJOOW CAROLPRENE YLW	FOOT	12	12	12	250 FT Reel
01380.41T.01M	12/3C SJOOW CAROLPRENE BLK	FOOT	18	13	18	1000 FT Reel
01380.46.01M	12/3C SJOOW CAROLPRENE BLK	FOOT	30	22	30	5000 FT Reel
01380.XX.01M	12/3C SJOOW CAROLPRENE BLK	FOOT	48	42	1	Various Lengths
01380.35T.01M	12/3C SJOOW CAROLPRENE BLK	FOOT	11	11	11	250 FT Reel
01380.38T.01M	12/3C SJOOW CAROLPRENE BLK	FOOT	22	20	1	500 FT Reel
01380.41T.02	12/3C SJOOW CAROLPRENE WHT	FOOT	22	20	18	1000 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
01380.XX.02	12/3C SJOOW CAROLPRENE WHT	FOOT	22	20	18	Various Lengths
01381.99.01	12/4C SJOOW CAROLPRENE BLK	FOOT	48	42	48	Factory Reel
01381.41T.01	12/4C SJOOW CAROLPRENE BLK	FOOT	20	20	16	1000 FT Reel
01381.46.01	12/4C SJOOW CAROLPRENE BLK	FOOT	20	20	20	5000 FT Reel
01381.XX.01	12/4C SJOOW CAROLPRENE BLK	FOOT	20	20	20	Various Lengths
01381.35T.01	12/4C SJOOW CAROLPRENE BLK	FOOT	12	13	12	250 FT Reel
01381.38T.01	12/4C SJOOW CAROLPRENE BLK	FOOT	22	20	1	500 FT Reel
01381.85.01	12/4C SJOOW CAROLPRENE BLK	FOOT	20	21	14	250 FT Coil
01381.99.01M	12/4C SJOOW CAROLPRENE BLK	FOOT	48	42	1	Factory Reel
01381.41T.01M	12/4C SJOOW CAROLPRENE BLK	FOOT	20	20	16	1000 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
01381.46.01M	12/4C SJOOW CAROLPRENE BLK	FOOT	22	20	1	5000 FT Reel
01381.35T.01M	12/4C SJOOW CAROLPRENE BLK	FOOT	22	20	1	250 FT Reel
01381.38T.01M	12/4C SJOOW CAROLPRENE BLK	FOOT	22	20	1	500 FT Reel
01381.85.01M	12/4C SJOOW CAROLPRENE BLK	FOOT	21	21	6	250 FT Coil
01481.35T.05	12/4C SJOOW CAROLPRENE YLW	FOOT	12	12	12	250 FT Reel
01481.35T.05M	12/4C SJOOW CAROLPRENE YLW	FOOT	12	12	12	250 FT Reel
01312.41T.01M	16/2C SJOOW CAROLPRENE BLK	FOOT	14	13	14	1000 FT Reel
01312.35T.01M	16/2C SJOOW CAROLPRENE BLK	FOOT	7	7	10	250 FT Reel
01312.38.01M	16/2C SJOOW CAROLPRENE BLK	FOOT	22	20	1	500 FT Reel
01312.99.01	16/2C SJOOW CAROLPRENE BLK	FOOT	48	42	1	Factory Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
01312.41.01	16/2C SJOOW CAROLPRENE BLK	FOOT	14	13	14	1000 FT Reel
01312.41T.01	16/2C SJOOW CAROLPRENE BLK	FOOT	14	13	14	1000 FT Reel
01312.44.01	16/2C SJOOW CAROLPRENE BLK	FOOT	14	14	12	2500 FT Reel
01312.46.01	16/2C SJOOW CAROLPRENE BLK	FOOT	27	22	27	5000 FT Reel
01312.L2.01	16/2C SJOOW CAROLPRENE BLK	FOOT	14	14	12	Long Length Reel
01312.35.01	16/2C SJOOW CAROLPRENE BLK	FOOT	7	7	10	250 FT Reel
01312.35T.01	16/2C SJOOW CAROLPRENE BLK	FOOT	7	7	10	250 FT Reel
01312.38.01	16/2C SJOOW CAROLPRENE BLK	FOOT	22	20	1	500 FT Reel
01312.38T.01	16/2C SJOOW CAROLPRENE BLK	FOOT	22	20	1	500 FT Reel
01312.82.01	16/2C SJOOW CAROLPRENE BLK	FOOT	11	11	8	50 FT Hanging Cuff

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
01312.L1.01	16/2C SJOOW CAROLPRENE BLK	FOOT	14	14	12	Long Length Reel
01342.44.02M	16/3C SJOOW CAROLPRENE WHT	FOOT	22	20	1	2500 FT Reel
01442.35T.05M	16/3C SJOOW CAROLPRENE YLW	FOOT	11	11	9	250 FT Reel
01442.35T.05	16/3C SJOOW CAROLPRENE YLW	FOOT	11	11	9	250 FT Reel
01342R.46.01	16/3C SJOOW CAROLPRENE BLK	FOOT	22	20	1	5000 FT Reel
01342.44.02	16/3C SJOOW CAROLPRENE WHT	FOOT	14	14	12	2500 FT Reel
01306.41T.01	16/3C SJ BLK	FOOT	16	13	16	1000 FT Reel
01306.46.01	16/3C SJ BLK	FOOT	30	22	30	5000 FT Reel
01342.99.01M	16/3C SJOOW CAROLPRENE BLK	FOOT	48	42	1	Factory Reel
01342.41T.01M	16/3C SJOOW CAROLPRENE BLK	FOOT	16	13	16	1000 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
01342.44.01M	16/3C SJOOW CAROLPRENE BLK	FOOT	22	20	1	2500 FT Reel
01342.46.01M	16/3C SJOOW CAROLPRENE BLK	FOOT	30	30	21	5000 FT Reel
01342.XX.01M	16/3C SJOOW CAROLPRENE BLK	FOOT	48	42	1	Various Lengths
01342.35.01M	16/3C SJOOW CAROLPRENE BLK	FOOT	16	16	13	250 FT Reel
01342.35T.01M	16/3C SJOOW CAROLPRENE BLK	FOOT	11	11	9	250 FT Reel
01342.99.01	16/3C SJOOW CAROLPRENE BLK	FOOT	48	42	48	Factory Reel
01342.41.01	16/3C SJOOW CAROLPRENE BLK	FOOT	16	13	16	1000 FT Reel
01342.41T.01	16/3C SJOOW CAROLPRENE BLK	FOOT	16	13	16	1000 FT Reel
01342.44.01	16/3C SJOOW CAROLPRENE BLK	FOOT	20	20	20	2500 FT Reel
01342.46.01	16/3C SJOOW CAROLPRENE BLK	FOOT	30	22	30	5000 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
01342.35.01	16/3C SJOOW CAROLPRENE BLK	FOOT	11	11	9	250 FT Reel
01342.35T.01	16/3C SJOOW CAROLPRENE BLK	FOOT	11	11	9	250 FT Reel
01342.38.01	16/3C SJOOW CAROLPRENE BLK	FOOT	22	20	1	500 FT Reel
01342.38T.01	16/3C SJOOW CAROLPRENE BLK	FOOT	22	20	1	500 FT Reel
01342.82.01	16/3C SJOOW CAROLPRENE BLK	FOOT	11	11	8	50 FT Hanging Cuff
01343.99.01	16/4C SJOOW CAROLPRENE BLK	FOOT	48	42	1	Factory Reel
01343.41T.01	16/4C SJOOW CAROLPRENE BLK	FOOT	16	13	16	1000 FT Reel
01343.44.01	16/4C SJOOW CAROLPRENE BLK	FOOT	14	14	12	2500 FT Reel
01343.46.01	16/4C SJOOW CAROLPRENE BLK	FOOT	30	22	30	5000 FT Reel
01343.35.01	16/4C SJOOW CAROLPRENE BLK	FOOT	11	11	9	250 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
01343.35T.01	16/4C SJOOW CAROLPRENE BLK	FOOT	11	11	9	250 FT Reel
01343.38.01	16/4C SJOOW CAROLPRENE BLK	FOOT	16	13	16	500 FT Reel
01343.41T.01M	16/4C SJOOW CAROLPRENE BLK	FOOT	16	13	16	1000 FT Reel
01343.46.01M	16/4C SJOOW CAROLPRENE BLK	FOOT	22	20	1	5000 FT Reel
01343.35T.01M	16/4C SJOOW CAROLPRENE BLK	FOOT	11	11	9	250 FT Reel
01310.99.01	18/2C SJOOW CAROLPRENE BLK	FOOT	42	48	42	Factory Reel
01310.41T.01	18/2C SJOOW CAROLPRENE BLK	FOOT	14	13	14	1000 FT Reel
01310.46.01	18/2C SJOOW CAROLPRENE BLK	FOOT	24	22	24	5000 FT Reel
01310.L2.01	18/2C SJOOW CAROLPRENE BLK	FOOT	14	14	12	Long Length Reel
01310.35.01	18/2C SJOOW CAROLPRENE BLK	FOOT	14	14	10	250 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
01310.35T.01	18/2C SJOOW CAROLPRENE BLK	FOOT	14	14	10	250 FT Reel
01310.38T.01	18/2C SJOOW CAROLPRENE BLK	FOOT	12	13	12	500 FT Reel
01310.L1.01	18/2C SJOOW CAROLPRENE BLK	FOOT	14	14	12	Long Length Reel
01310.99.01M	18/2C SJOOW CAROLPRENE BLK	FOOT	42	48	42	Factory Reel
01310.41T.01M	18/2C SJOOW CAROLPRENE BLK	FOOT	14	13	14	1000 FT Reel
01310.46.01M	18/2C SJOOW CAROLPRENE BLK	FOOT	24	24	21	5000 FT Reel
01310.XX.01M	18/2C SJOOW CAROLPRENE BLK	FOOT	42	48	42	Various Lengths
01310.35.01M	18/2C SJOOW CAROLPRENE BLK	FOOT	22	20	1	250 FT Reel
01310.35T.01M	18/2C SJOOW CAROLPRENE BLK	FOOT	22	20	1	250 FT Reel
01310.38T.01M	18/2C SJOOW CAROLPRENE BLK	FOOT	22	20	1	500 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
01311.99.01M	18/3C SJOOW CAROLPRENE BLK	FOOT	48	42	1	Factory Reel
01311.41T.01M	18/3C SJOOW CAROLPRENE BLK	FOOT	14	13	14	1000 FT Reel
01311.44.01M	18/3C SJOOW CAROLPRENE BLK	FOOT	22	20	1	2500 FT Reel
01311.46.01M	18/3C SJOOW CAROLPRENE BLK	FOOT	34	34	18	5000 FT Reel
01311.35T.01M	18/3C SJOOW CAROLPRENE BLK	FOOT	7	7	10	250 FT Reel
01311.38T.01M	18/3C SJOOW CAROLPRENE BLK	FOOT	22	20	1	500 FT Reel
01311.99.01	18/3C SJOOW CAROLPRENE BLK	FOOT	48	42	1	Factory Reel
01311.41.01	18/3C SJOOW CAROLPRENE BLK	FOOT	14	13	14	1000 FT Reel
01311.41T.01	18/3C SJOOW CAROLPRENE BLK	FOOT	14	13	14	1000 FT Reel
01311.44.01	18/3C SJOOW CAROLPRENE BLK	FOOT	27	22	27	2500 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
01311.46.01	18/3C SJOOW CAROLPRENE BLK	FOOT	27	22	27	5000 FT Reel
01311.L2.01	18/3C SJOOW CAROLPRENE BLK	FOOT	14	14	12	Long Length Reel
01311.35.01	18/3C SJOOW CAROLPRENE BLK	FOOT	14	14	10	250 FT Reel
01311.35T.01	18/3C SJOOW CAROLPRENE BLK	FOOT	14	14	10	250 FT Reel
01311.38T.01	18/3C SJOOW CAROLPRENE BLK	FOOT	12	13	12	500 FT Reel
01304.41.01	18/4C SJ BLK	FOOT	16	13	16	1000 FT Reel
01344.99.01	18/4C SJOOW CAROLPRENE BLK	FOOT	48	42	1	Factory Reel
01344.41T.01	18/4C SJOOW CAROLPRENE BLK	FOOT	16	13	16	1000 FT Reel
01344.44.01	18/4C SJOOW CAROLPRENE BLK	FOOT	24	22	24	2500 FT Reel
01344.46.01	18/4C SJOOW CAROLPRENE BLK	FOOT	30	22	30	5000 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
01344.35.01	18/4C SJOOW CAROLPRENE BLK	FOOT	11	11	9	250 FT Reel
01344.35T.01	18/4C SJOOW CAROLPRENE BLK	FOOT	11	11	9	250 FT Reel
01344.38T.01	18/4C SJOOW CAROLPRENE BLK	FOOT	12	13	12	500 FT Reel
01444.41T.05	18/4C SJOOW CAROLPRENE YLW	FOOT	14	14	12	1000 FT Reel
01444.35T.05	18/4C SJOOW CAROLPRENE YLW	FOOT	14	14	10	250 FT Reel
01444.99.05	18/4C SJOOW CAROLPRENE YLW	FOOT	22	20	1	Factory Reel
01344.99.01M	18/4C SJOOW CAROLPRENE BLK	FOOT	48	42	1	Factory Reel
01344.41T.01M	18/4C SJOOW CAROLPRENE BLK	FOOT	16	13	16	1000 FT Reel
01344.44.01M	18/4C SJOOW CAROLPRENE BLK	FOOT	22	20	1	2500 FT Reel
01344.35T.01M	18/4C SJOOW CAROLPRENE BLK	FOOT	11	11	11	250 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
01444.35T.05M	18/4C SJOOW CAROLPRENE YLW	FOOT	16	15	12	250 FT Reel
01358R.46.01	14/3C SJOOW CAROLPRENE BLK	FOOT	22	20	1	5000 FT Reel
01358.41T.01M	14/2C SJOOW CAROLPRENE BLK	FOOT	16	13	16	1000 FT Reel
01358.46.01M	14/2C SJOOW CAROLPRENE BLK	FOOT	22	20	1	5000 FT Reel
01358.35T.01M	14/2C SJOOW CAROLPRENE BLK	FOOT	11	11	9	250 FT Reel
01312R.46.01	16/2C SJOOW CAROLPRENE BLK	FOOT	22	20	1	5000 FT Reel
01358.99.01	14/2C SJOOW CAROLPRENE BLK	FOOT	48	42	1	Factory Reel
01358.41T.01	14/2C SJOOW CAROLPRENE BLK	FOOT	16	13	16	1000 FT Reel
01358.44.01	14/2C SJOOW CAROLPRENE BLK	FOOT	14	14	12	2500 FT Reel
01358.46.01	14/2C SJOOW CAROLPRENE BLK	FOOT	30	22	30	5000 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
01358.35.01	14/2C SJOOW CAROLPRENE BLK	FOOT	11	11	9	250 FT Reel
01358.35T.01	14/2C SJOOW CAROLPRENE BLK	FOOT	11	11	9	250 FT Reel
01358.38.01	14/2C SJOOW CAROLPRENE BLK	FOOT	22	20	1	500 FT Reel
01358.82.01	14/2C SJOOW CAROLPRENE BLK	FOOT	11	11	8	50 FT Hanging Cuff
01360.41T.04	14/3C SJOOW SUPER VUTRON III ORG	FOOT	18	13	12	1000 FT Reel
01380R.44.01	12/3C SJOOW CAROLPRENE BLK	FOOT	22	20	1	2500 FT Reel
01383R.41T.01	10/3C SJOOW CAROLPRENE BLK	FOOT	22	20	1	1000 FT Reel
01362.41T.01	14/3C SJ BLK	FOOT	18	13	18	1000 FT Reel
01460.41T.05M	14/3C SJOOW CAROLPRENE YLW	FOOT	18	18	12	1000 FT Reel
01460.35T.05M	14/3C SJOOW CAROLPRENE YLW	FOOT	11	11	9	250 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
01460.41T.05	14/3C SJOOW CAROLPRENE YLW	FOOT	18	18	12	1000 FT Reel
01460.46.05	14/3C SJOOW CAROLPRENE YLW	FOOT	18	18	12	5000 FT Reel
01460.XX.05	14/3C SJOOW CAROLPRENE YLW	FOOT	48	42	1	Various Lengths
01460.35.05	14/3C SJOOW CAROLPRENE YLW	FOOT	11	11	9	250 FT Reel
01460.35T.05	14/3C SJOOW CAROLPRENE YLW	FOOT	11	11	9	250 FT Reel
01460.99.05	14/3C SJOOW CAROLPRENE YLW	FOOT	22	20	1	Factory Reel
01360.99.01	14/3C SJOOW CAROLPRENE BLK	FOOT	48	42	1	Factory Reel
01360.41.01	14/3C SJOOW CAROLPRENE BLK	FOOT	18	13	12	1000 FT Reel
01360.41T.01	14/3C SJOOW CAROLPRENE BLK	FOOT	18	13	12	1000 FT Reel
01360.44.01	14/3C SJOOW CAROLPRENE BLK	FOOT	24	22	24	2500 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
01360.46.01	14/3C SJOOW CAROLPRENE BLK	FOOT	34	20	34	5000 FT Reel
01360.XX.01	14/3C SJOOW CAROLPRENE BLK	FOOT	48	42	1	Various Lengths
01360.35.01	14/3C SJOOW CAROLPRENE BLK	FOOT	11	11	9	250 FT Reel
01360.35T.01	14/3C SJOOW CAROLPRENE BLK	FOOT	11	11	9	250 FT Reel
01360.38T.01	14/3C SJOOW CAROLPRENE BLK	FOOT	22	20	1	500 FT Reel
01360.82.01	14/3C SJOOW CAROLPRENE BLK	FOOT	11	11	8	50 FT Hanging Cuff
01360.41T.01M	14/3C SJOOW CAROLPRENE BLK	FOOT	18	13	12	1000 FT Reel
01360.44.01M	14/3C SJOOW CAROLPRENE BLK	FOOT	25	25	21	2500 FT Reel
01360.XX.01M	14/3C SJOOW CAROLPRENE BLK	FOOT	48	42	1	Various Lengths
01360.35T.01M	14/3C SJOOW CAROLPRENE BLK	FOOT	11	11	9	250 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
01360.38T.01M	14/3C SJOOW CAROLPRENE BLK	FOOT	22	20	1	500 FT Reel
01311R.46.01	18/3C SJOOW CAROLPRENE BLK	FOOT	22	20	1	5000 FT Reel
01360R.44.01	14/3C SJOOW CAROLPRENE BLK	FOOT	22	20	1	2500 FT Reel
01360R.46.01	14/3C SJOOW CAROLPRENE BLK	FOOT	22	20	1	5000 FT Reel
01364.41T.02	14/4C SJOOW CAROLPRENE WHT	FOOT	22	20	1	1000 FT Reel
01364.41T.01M	14/4C SJOOW CAROLPRENE BLK	FOOT	18	13	18	1000 FT Reel
01364.35T.01M	14/4C SJOOW CAROLPRENE BLK	FOOT	11	11	11	250 FT Reel
01364.99.01	14/4C SJOOW CAROLPRENE BLK	FOOT	48	42	48	Factory Reel
01364.41T.01	14/4C SJOOW CAROLPRENE BLK	FOOT	18	13	18	1000 FT Reel
01364.46.01	14/4C SJOOW CAROLPRENE BLK	FOOT	22	20	1	5000 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
01364.L2.01	14/4C SJOOW CAROLPRENE BLK	FOOT	14	14	12	Long Length Reel
01364.35.01	14/4C SJOOW CAROLPRENE BLK	FOOT	11	11	11	250 FT Reel
01364.35T.01	14/4C SJOOW CAROLPRENE BLK	FOOT	11	11	11	250 FT Reel
01364.38T.01	14/4C SJOOW CAROLPRENE BLK	FOOT	14	13	14	500 FT Reel
01464.15T.05	14/4C SJOOW CAROLPRENE YLW	FOOT	11	11	11	250 FT Spool
01464.99.05	14/4C SJOOW CAROLPRENE YLW	FOOT	22	20	1	Factory Reel