

SUPER VUTRON SOOW

Rubber cord that performs in heat & cold, Resistant to oil/chemicals



GENERAL INFO

Thermoset rubber cord products have evolved over the last 50 years from simple and unsophisticated to a product line where specialized, technologically advanced products are in demand for exacting commercial and industrial applications. No longer are rubber cord products used only in applications where flexibility is needed; today typical applications require cord to perform well in environments of extreme heat and cold and on job sites and factory floors where resistance to oil, chemicals and abrasion is mandatory. General Cable's role, as the producer of the premiere Carol® Brand rubber cord products, is to ensure that new product development, product innovation and quality not only keep pace with industry requirements but also set the trends. Our rubber cord products carry a full range of listings and certifications with Underwriters Laboratories, Inc. and the Canadian Standard Association. In addition, many products meet or exceed the requirements of OSHA, MSHA and other relevant industry standards. Carol Brand is simply the most accepted in the industry, having proven itself on the job time after time. Our rubber cord line is the most comprehensive in the industry, ensuring that the proper Carol product can always be specified.

CONSTRUCTION/DESIGN

Conductor material	Copper	Shield construction	Not applicable
Conductor surface	Bare	Shield material	Not applicable
Core insulation material	EPDM rubber	Material outer jacket	Rubber
Drain wire	No	Cable shape	Round
Longitudinal water blocking cable		Silicon free	Not applicable
Radial water blocking cable		Lead free	Not applicable
Rip cord	Yes	Permitted cable outer temperature during assembling/handling (min) [°C]	
Armoring/reinforcement		Permitted cable outer temperature during assembling/handling (max) [°C]	
Armoring/reinforcement material			

APPLICATION PROPERTIES

Nominal voltage U [V]	600	Resistant to UV	Yes
Flame retardant	Yes	Moisture resistance	Yes
Halogen free	No	Outdoor installation	Yes
Low smoke	No	Underground installation	No
Oil resistant	Yes		

STANDARDS AND APPROVALS



PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
09005.41.01M	10/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	10	Black, White, Red, Green, Orange	5	Black
09005.43.01M	10/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	10	Black, White, Red, Green, Orange	5	Black
09005.46.01M	10/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	10	Black, White, Red, Green, Orange	5	Black
09005.35.01M	10/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	10	Black, White, Red, Green, Orange	5	Black
09005.99.01M	10/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	10	Black, White, Red, Green, Orange	5	Black
09005.41.01	10/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	10	Black, White, Red, Green, Orange	5	Black
09005.43.01	10/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	10	Black, White, Red, Green, Orange	5	Black
09005.46.01	10/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	10	Black, White, Red, Green, Orange	5	Black
09005.XX.01	10/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	10	Black, White, Red, Green, Orange	5	Black
09005.35.01	10/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	10	Black, White, Red, Green, Orange	5	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
09005.38.01	10/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	10	Black, White, Red, Green, Orange	5	Black
09005.99.01	10/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	10	Black, White, Red, Green, Orange	5	Black
09006.XX.01	10/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	10	Black, White, Red, Green, Orange, Blue	6	Black
09006.99.01	10/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	10	Black, White, Red, Green, Orange, Blue	6	Black
09007.XX.01	10/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	10	Black, White, Red, Green, Orange, Blue, White/Black	7	Black
09007.99.01	10/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	10	Black, White, Red, Green, Orange, Blue, White/Black	7	Black
09008.44.01	10/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	10	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black
09008.XX.01	10/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	10	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black
09008.99.01	10/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	10	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black
09010.XX.01	10/10C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	10	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black	10	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
09010.99.01	10/10C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	10	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black	10	Black
09010.99.01M	10/10C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	10	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black	10	Black
09012.99.01M	10/12C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	10	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White	12	Black
09012.99.01	10/12C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	10	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White	12	Black
09016.99.01M	10/16C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	10	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red	16	Black
09016.99.01	10/16C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	10	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red	16	Black
09020.99.01M	10/20C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	10	Black, White, Red, Green, Orange, Blue, White/Black, Red/black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green	20	Black
09020.99.01	10/20C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	10	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green	20	Black
02623.35.01	12/5C SOOW VUTRON BLK	SUPER VU-TRON® SUPREME SOOW - CAROL SUPER VU-TRON® SUPREME FEATURING GENCLEAN® JACKET (SIZE) (mm2) 105°C (UL) WATER RESISTANT SOOW CSA (-50°C) FT1 --- P-07-KA120015-MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green/Yellow, Orange	5	Black
US00_SUPERVUTRON SOOW 12/03/2022	12/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-	12	Black, White, Red, Green, Orange,	5	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
09205.44.01M	12/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green Orange	5	Black
09205.35.01M	12/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green Orange	5	Black
02623.35.05	12/5C SOOW VUTRON YLW	SUPER VU-TRON® SUPREME SOOW - CAROL SUPER VU-TRON® SUPREME FEATURING GENCLEAN® JACKET (SIZE) (mm2) 105°C (UL) WATER RESISTANT SOOW CSA (-50°C) FT1 --- P-07-KA120015-MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green/Yellow, Orange	5	Yellow
09205.41.01	12/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange	5	Black
09205.44.01	12/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange	5	Black
09205.XX.01	12/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange	5	Black
09205.35.01	12/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange	5	Black
09205.38.01	12/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange	5	Black
09205.99.01	12/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange	5	Black
09206.41.01	12/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue	6	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
09206.XX.01	12/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue	6	Black
09206.35.01	12/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue	6	Black
09206.99.01	12/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue	6	Black
09206.41.01M	12/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue	6	Black
09207.41.01M	12/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black	7	Black
09207.35.01M	12/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black	7	Black
09207.41.01	12/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black	7	Black
09207.XX.01	12/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black	7	Black
09207.35.01	12/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black	7	Black
09207.99.01	12/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black	7	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
09208.41.01	12/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black
09208.XX.01	12/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black
09208.35.01	12/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black
09208.38.01	12/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black
09208.99.01	12/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black
09208.41.01M	12/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black
09208.99.01M	12/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black
09209.XX.01	12/9C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black	9	Black
09209.99.01	12/9C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black	9	Black
09210.99.01M	12/10C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black	10	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
09210.41.01	12/10C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (- 40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black	10	Black
09210.XX.01	12/10C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (- 40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black	10	Black
09210.99.01	12/10C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (- 40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black	10	Black
09212.99.01M	12/12C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (- 40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Blue, Black/White	12	Black
09212.XX.01	12/12C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (- 40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White	12	Black
09212.99.01	12/12C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (- 40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White	12	Black
09214.99.01M	12/14C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (- 40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White	14	Black
09214.XX.01	12/14C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (- 40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Blue/Black, Black/White, Red/White, Green/White	14	Black
09214.99.01	12/14C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (- 40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Blue/Black, Black/White, Red/White, Green/White	14	Black
09216.99.01	12/16C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (- 40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red	16	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
09216.99.01M	12/16C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red	16	Black
09220.99.01M	12/20C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green	20	Black
09220.99.01	12/20C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green Orange, Blue, White/Black, Red/black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green	20	Black
09224.99.01M	12/24C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green, Orange/Green, Black, White, Red	24	Black
09224.XX.01	12/24C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green, Orange/Green, Black, White, Red	24	Black
09224.99.01	12/24C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green, Orange/Green, Black, White, Red	24	Black
09226.XX.01	12/26C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green, Orange/Green, Black, White, Red, Green, Orange	26	Black
09226.99.01	12/26C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green, Orange/Green, Black, White, Red, Green, Orange	26	Black
09230.XX.01	12/30C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green, Orange/Green, Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green	30	Black
US00_SUPERVUTRON SOOW SUPER	12/30C SOOW SUPER	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C)	12	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green, Orange/Green, Black, White, Red, Green, Orange	30	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
09230.99.01M	12/30C SOOW SUPER VU- TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	12	Black, White, Red, Green, Orange, Blue, White/black, Red/Black, Green/Black, Orange/black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green, Orange/Green, Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/black	30	Black
09605.41.01	16/5C SOOW SUPER VU- TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange	5	Black
09605.44.01	16/5C SOOW SUPER VU- TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange	5	Black
09605.46.01	16/5C SOOW SUPER VU- TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange	5	Black
09605.XX.01	16/5C SOOW SUPER VU- TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange	5	Black
09605.35.01	16/5C SOOW SUPER VU- TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange	5	Black
09605.38.01	16/5C SOOW SUPER VU- TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange	5	Black
09605.99.01	16/5C SOOW SUPER VU- TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange	5	Black
09605.41.01M	16/5C SOOW SUPER VU- TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange	5	Black
US00_SUPERVUTRON SOOW 16/03/2019	16/5C SOOW SUPER VU- TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C)	16	P 10 Black, White, Red, Green, Orange	5	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
09605.46.01M	16/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange	5	Black
09605.35.01M	16/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange	5	Black
09606.41.01M	16/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Blue, White/Black	6	Black
09606.44.01M	16/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Blue, White/Black	6	Black
09606.46.01M	16/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Blue, White/Black	6	Black
09606.35.01M	16/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Blue, White/Black	6	Black
09606.41.01	16/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue	6	Black
09606.44.01	16/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue	6	Black
09606.46.01	16/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue	6	Black
09606.XX.01	16/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue	6	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
09606.35.01	16/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue	6	Black
09606.38.01	16/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue	6	Black
09606.99.01	16/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue	6	Black
09607.41.01M	16/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black	7	Black
09607.35.01M	16/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black	7	Black
09607.99.01M	16/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black	7	Black
09607.41.01	16/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black	7	Black
09607.44.01	16/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black	7	Black
09607.46.01	16/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black	7	Black
09607.XX.01	16/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black	7	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
09607.35.01	16/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black	7	Black
09607.38.01	16/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black	7	Black
09607.99.01	16/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black	7	Black
09608.41.01M	16/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black
09608.44.01M	16/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black
09608.35.01M	16/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black
09608.XX.01M	16/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black
09608.41.01	16/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black
09608.44.01	16/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black
09608.XX.01	16/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
09608.35.01	16/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black
09608.38.01	16/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black
09608.99.01	16/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black
09609.99.01M	16/9C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black	9	Black
09609.41.01	16/9C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black	9	Black
09609.XX.01	16/9C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black	9	Black
09609.99.01	16/9C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black	9	Black
09610.XX.01	16/10C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black	10	Black
09610.35.01	16/10C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black	10	Black
09610.99.01	16/10C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black	10	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
09610.99.01M	16/10C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (- 40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black	10	Black
09612.99.01M	16/12C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (- 40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White	12	Black
09612.XX.01	16/12C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (- 40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White	12	Black
09612.35.01	16/12C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (- 40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White	12	Black
09612.99.01	16/12C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (- 40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White	12	Black
09614.99.01M	16/14C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (- 40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/black, Blue/Black, Black/White, Red/White, Green/White	14	Black
09614.41.01	16/14C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (- 40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/black, Blue/Black, Black/White, Red/White, Green/White	14	Black
09614.XX.01	16/14C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (- 40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/black, Blue/Black, Black/White, Red/White, Green/White	14	Black
09614.99.01	16/14C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (- 40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/black, Blue/Black, Black/White, Red/White, Green/White	14	Black
09616.XX.01M	16/16C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (- 40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red	16	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
09616.99.01M	16/16C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red	16	Black
09616.XX.01	16/16C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red	16	Black
09616.35.01	16/16C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red	16	Black
09616.99.01	16/16C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red	16	Black
09620.99.01M	16/20C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green	20	Black
09620.XX.01	16/20C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green	20	Black
09620.99.01	16/20C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green	20	Black
09624.99.01M	16/24C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green, Orange/Green, Black, White, Red	24	Black
09624.XX.01	16/24C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green, Orange/Green, Black, White, Red	24	Black
US00_SUPERVUTRON SOOW SUPER	16/24C SOOW SUPER	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green, Orange/Green, Black, White, Red	24	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
09630.99.01M	16/30C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green, Orange/Green, Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/black	30	Black
09630.XX.01	16/30C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green, Orange/Green, Black, White, Red, Green, Orange, Blue, White/Black, Red/Black Green/Black	30	Black
09630.99.01	16/30C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	16	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green, Orange/Green, Black, White, Red, Green, Orange, Blue, White/Black, Red/Black Green/Black	30	Black
09805.41.01M	18/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange	5	Black
09805.44.01M	18/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange	5	Black
09805.38.01M	18/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange	5	Black
09805.41.01	18/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange	5	Black
09805.44.01	18/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange	5	Black
09805.XX.01	18/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange	5	Black
US00_SUPERVUTRON SOOW SUPER VU-TRON BLK	18/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange	5	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
09805.38.01	18/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange	5	Black
09805.99.01	18/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange	5	Black
09806.41.01M	18/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue	6	Black
09806.44.01M	18/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue	6	Black
09806.46.01M	18/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue	6	Black
09806.99.01M	18/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue	6	Black
09806.41.01	18/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue	6	Black
09806.46.01	18/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue	6	Black
09806.XX.01	18/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue	6	Black
09806.35.01	18/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue	6	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
09806.38.01	18/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue	6	Black
09806.99.01	18/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue	6	Black
09807.41.01M	18/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black	7	Black
09807.35.01M	18/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black	7	Black
09807.XX.01M	18/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black	7	Black
09807.41.01	18/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black	7	Black
09807.44.01	18/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black	7	Black
09807.35.01	18/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black	7	Black
09807.99.01	18/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black	7	Black
09808.41.01	18/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
09808.44.01	18/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black
09808.XX.01	18/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black
09808.35.01	18/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black
09808.38.01	18/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black
09808.99.01	18/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black
09808.41.01M	18/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black
09808.44.01M	18/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black
09808.99.01M	18/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black
09810.99.01M	18/10C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black	10	Black
09810.41.01	18/10C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black	10	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
09810.38.01	18/10C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black	10	Black
09810.XX.01	18/10C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black	10	Black
09810.99.01	18/10C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black	10	Black
09812.35.01	18/12C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White	12	Black
09812.XX.01	18/12C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White	12	Black
09812.99.01	18/12C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White	12	Black
09812.99.01M	18/12C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White	12	Black
09814.99.01M	18/14C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White	14	Black
09814.XX.01	18/14C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White	14	Black
09814.99.01	18/14C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White	14	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
09816.XX.01	18/16C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red	16	Black
09816.99.01	18/16C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red	16	Black
09816.99.01M	18/16C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red	16	Black
09820.99.01M	18/20C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green	20	Black
09820.XX.01	18/20C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green	20	Black
09820.99.01	18/20C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green	20	Black
09824.99.01M	18/24C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green, Orange/Green, Black, White, Red	24	Black
09824.41.01	18/24C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green, Orange/Green, Black, White, Red	24	Black
09824.XX.01	18/24C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green, Orange/Green, Black, White, Red	24	Black
US00_SUPERVUTRON SOOW SUPER	18/24C SOOW SUPER	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green, Orange/Green, Black, White, Red	24	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
09824.99.01	18/24C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green, Orange/Green, Black, White, Red	24	Black
09830.99.01M	18/30C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green, Orange/Green, Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black	30	Black
09830.99.01	18/30C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	18	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green, Orange/Green, Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black	30	Black
09405.41.01	14/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange	5	Black
09405.44.01	14/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange	5	Black
09405.XX.01	14/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange	5	Black
09405.35.01	14/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange	5	Black
09405.38.01	14/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange	5	Black
09405.99.01	14/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange	5	Black
US00_SUPERVUTRON SOOW SUPER VU-TRON BLK 09405.41.01M	14/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange	5	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
09405.44.01M	14/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange	5	Black
09405.35.01M	14/5C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange	5	Black
09406.41.01	14/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue	6	Black
09406.44.01	14/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue	6	Black
09406.XX.01	14/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue	6	Black
09406.35.01	14/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue	6	Black
09406.38.01	14/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue	6	Black
09406.99.01	14/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue	6	Black
09406.41.01M	14/6C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue	6	Black
09407.41.01	14/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black	7	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
09407.44.01	14/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black	7	Black
09407.XX.01	14/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black	7	Black
09407.35.01	14/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black	7	Black
09407.99.01	14/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black	7	Black
09407.41.01M	14/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black	7	Black
09407.35.01M	14/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black	7	Black
09407.99.01M	14/7C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black	7	Black
09408.41.01M	14/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black
09408.41.01	14/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black
09408.XX.01	14/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
09408.35.01	14/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black
09408.38.01	14/8C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black	8	Black
09410.XX.01M	14/10C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black	10	Black
09410.99.01M	14/10C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black	10	Black
09410.XX.01	14/10C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black	10	Black
09410.99.01	14/10C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black	10	Black
09412.XX.01	14/12C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White	12	Black
09412.99.01	14/12C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White	12	Black
09412.99.01M	14/12C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White	12	Black
09414.99.01	14/14C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White	14	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
09416.99.01M	14/16C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red	16	Black
09416.XX.01	14/16C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red	16	Black
09416.99.01	14/16C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red	16	Black
09420.99.01M	14/20C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green	20	Black
09420.XX.01	14/20C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green	20	Black
09420.99.01	14/20C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green	20	Black
09424.99.01	14/24C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green, Orange/Green, Black, White, Red	24	Black
09424.99.01M	14/24C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green, Orange/Green, Black, White, Red	24	Black
09428.99.01	14/28C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green, Orange/Green, Black, White, Red, Green, Orange, Blue, White/Black	28	Black
US00_SUPERVUTRON SOOW SUPER VU-TRON BLK 09430.XX.01	14/30C SOOW SUPER VU-TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green, Orange/Green, Black, White, Red	30	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
09430.99.01	14/30C SOOW SUPER VU- TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green, Orange/Green, Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black	30	Black
09430.99.01M	14/30C SOOW SUPER VU- TRON BLK	CAROL SUPER VU-TRON® (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green, Orange/Green, Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black	30	Black

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
09005.41.01M	10/5C SOOW SUPER VU-TRON BLK		0.045	0.77			1.14	19.56
09005.43.01M	10/5C SOOW SUPER VU-TRON BLK		0.045	0.77			1.14	19.56
09005.46.01M	10/5C SOOW SUPER VU-TRON BLK		0.045	0.77			1.14	19.56
09005.35.01M	10/5C SOOW SUPER VU-TRON BLK		0.045	0.77			1.14	19.56
09005.99.01M	10/5C SOOW SUPER VU-TRON BLK		0.045	0.77			1.14	19.56
09005.41.01	10/5C SOOW SUPER VU-TRON BLK		0.045	0.77			1.14	19.56
09005.43.01	10/5C SOOW SUPER VU-TRON BLK		0.045	0.77			1.14	19.56
09005.46.01	10/5C SOOW SUPER VU-TRON BLK		0.045	0.77			1.14	19.56
09005.XX.01	10/5C SOOW SUPER VU-TRON BLK		0.045	0.77			1.14	19.56
09005.35.01	10/5C SOOW SUPER VU-TRON BLK		0.045	0.77			1.14	19.56

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
09005.38.01	10/5C SOOW SUPER VU- TRON BLK		0.045	0.77			1.14	19.56
09005.99.01	10/5C SOOW SUPER VU- TRON BLK		0.045	0.77			1.14	19.56
09006.XX.01	10/6C SOOW SUPER VU- TRON BLK		0.045	0.875			1.14	22.23
09006.99.01	10/6C SOOW SUPER VU- TRON BLK		0.045	0.875			1.14	22.23
09007.XX.01	10/7C SOOW SUPER VU- TRON BLK		0.045	0.9			1.14	22.86
09007.99.01	10/7C SOOW SUPER VU- TRON BLK		0.045	0.9			1.14	22.86
09008.44.01	10/8C SOOW SUPER VU- TRON BLK		0.045	0.935			1.14	23.75
09008.XX.01	10/8C SOOW SUPER VU- TRON BLK		0.045	0.935			1.14	23.75
09008.99.01	10/8C SOOW SUPER VU- TRON BLK		0.045	0.935			1.14	23.75
09010.XX.01	10/10C SOOW SUPER VU- TRON BLK		0.045	1.02			1.14	25.91

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
09010.99.01	10/10C SOOW SUPER VU-TRON BLK		0.045	1.02			1.14	25.91
09010.99.01M	10/10C SOOW SUPER VU-TRON BLK		0.045	1.02			1.14	25.91
09012.99.01M	10/12C SOOW SUPER VU-TRON BLK		0.045	1.07			1.14	27.18
09012.99.01	10/12C SOOW SUPER VU-TRON BLK		0.045	1.07			1.14	27.18
09016.99.01M	10/16C SOOW SUPER VU-TRON BLK		0.045	1.23			1.14	31.24
09016.99.01	10/16C SOOW SUPER VU-TRON BLK		0.045	1.23			1.14	31.24
09020.99.01M	10/20C SOOW SUPER VU-TRON BLK		0.045	1.325			1.14	33.66
09020.99.01	10/20C SOOW SUPER VU-TRON BLK		0.045	1.325			1.14	33.66
02623.35.01	12/5C SOOW VUTRON BLK		0.045	0.73			1.14	18.54
09205.41.01M	12/5C SOOW SUPER VU-TRON BLK		0.045	0.715			1.14	18.16

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
09205.44.01M	12/5C SOOW SUPER VUTRON BLK		0.045	0.715			1.14	18.16
09205.35.01M	12/5C SOOW SUPER VUTRON BLK		0.045	0.715			1.14	18.16
02623.35.05	12/5C SOOW VUTRON YLW		0.045	0.73			1.14	18.54
09205.41.01	12/5C SOOW SUPER VUTRON BLK		0.045	0.715			1.14	18.16
09205.44.01	12/5C SOOW SUPER VUTRON BLK		0.045	0.715			1.14	18.16
09205.XX.01	12/5C SOOW SUPER VUTRON BLK		0.045	0.715			1.14	18.16
09205.35.01	12/5C SOOW SUPER VUTRON BLK		0.045	0.715			1.14	18.16
09205.38.01	12/5C SOOW SUPER VUTRON BLK		0.045	0.715			1.14	18.16
09205.99.01	12/5C SOOW SUPER VUTRON BLK		0.045	0.715			1.14	18.16
09206.41.01	12/6C SOOW SUPER VUTRON BLK		0.045	0.74			1.14	18.8

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
09206.XX.01	12/6C SOOW SUPER VU-TRON BLK		0.045	0.74			1.14	18.8
09206.35.01	12/6C SOOW SUPER VU-TRON BLK		0.045	0.74			1.14	18.8
09206.99.01	12/6C SOOW SUPER VU-TRON BLK		0.045	0.74			1.14	18.8
09206.41.01M	12/6C SOOW SUPER VU-TRON BLK		0.045	0.74			1.14	18.8
09207.41.01M	12/7C SOOW SUPER VU-TRON BLK		0.045	0.79			1.14	20.07
09207.35.01M	12/7C SOOW SUPER VU-TRON BLK		0.045	0.79			1.14	20.07
09207.41.01	12/7C SOOW SUPER VU-TRON BLK		0.045	0.79			1.14	20.07
09207.XX.01	12/7C SOOW SUPER VU-TRON BLK		0.045	0.79			1.14	20.07
09207.35.01	12/7C SOOW SUPER VU-TRON BLK		0.045	0.79			1.14	20.07
09207.99.01	12/7C SOOW SUPER VU-TRON BLK		0.045	0.79			1.14	20.07

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
09208.41.01	12/8C SOOW SUPER VU-TRON BLK		0.045	0.825			1.14	20.96
09208.XX.01	12/8C SOOW SUPER VU-TRON BLK		0.045	0.825			1.14	20.96
09208.35.01	12/8C SOOW SUPER VU-TRON BLK		0.045	0.825			1.14	20.96
09208.38.01	12/8C SOOW SUPER VU-TRON BLK		0.045	0.825			1.14	20.96
09208.99.01	12/8C SOOW SUPER VU-TRON BLK		0.045	0.825			1.14	20.96
09208.41.01M	12/8C SOOW SUPER VU-TRON BLK		0.045	0.825			1.14	20.96
09208.99.01M	12/8C SOOW SUPER VU-TRON BLK		0.045	0.825			1.14	20.96
09209.XX.01	12/9C SOOW SUPER VU-TRON BLK		0.045	0.9			1.14	22.86
09209.99.01	12/9C SOOW SUPER VU-TRON BLK		0.045	0.9			1.14	22.86
09210.99.01M	12/10C SOOW SUPER VU-TRON BLK		0.045	0.95			1.14	24.13

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
09210.41.01	12/10C SOOW SUPER VU- TRON BLK		0.045	0.95			1.14	24.13
09210.XX.01	12/10C SOOW SUPER VU- TRON BLK		0.045	0.95			1.14	24.13
09210.99.01	12/10C SOOW SUPER VU- TRON BLK		0.045	0.95			1.14	24.13
09212.99.01M	12/12C SOOW SUPER VU- TRON BLK		0.045	1.01			1.14	25.65
09212.XX.01	12/12C SOOW SUPER VU- TRON BLK		0.045	1.01			1.14	25.65
09212.99.01	12/12C SOOW SUPER VU- TRON BLK		0.045	1.01			1.14	25.65
09214.99.01M	12/14C SOOW SUPER VU- TRON BLK		0.045	1.02			1.14	25.91
09214.XX.01	12/14C SOOW SUPER VU- TRON BLK		0.045	1.02			1.14	25.91
09214.99.01	12/14C SOOW SUPER VU- TRON BLK		0.045	1.02			1.14	25.91
09216.99.01	12/16C SOOW SUPER VU- TRON BLK		0.045	1.135			1.14	28.83

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
09216.99.01M	12/16C SOOW SUPER VU- TRON BLK		0.045	1.135			1.14	28.83
09220.99.01M	12/20C SOOW SUPER VU- TRON BLK		0.045	1.175			1.14	29.84
09220.99.01	12/20C SOOW SUPER VU- TRON BLK		0.045	1.175			1.14	29.84
09224.99.01M	12/24C SOOW SUPER VU- TRON BLK		0.045	1.36			1.14	34.54
09224.XX.01	12/24C SOOW SUPER VU- TRON BLK		0.045	1.36			1.14	34.54
09224.99.01	12/24C SOOW SUPER VU- TRON BLK		0.045	1.36			1.14	34.54
09226.XX.01	12/26C SOOW SUPER VU- TRON BLK		0.045	1.38			1.14	35.05
09226.99.01	12/26C SOOW SUPER VU- TRON BLK		0.045	1.38			1.14	35.05
09230.XX.01	12/30C SOOW SUPER VU- TRON BLK		0.045	1.455			1.14	36.96
09230.99.01	12/30C SOOW SUPER VU- TRON BLK		0.045	1.455			1.14	36.96

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
09230.99.01M	12/30C SOOW SUPER VU-TRON BLK		0.045	1.455			1.14	36.96
09605.41.01	16/5C SOOW SUPER VU-TRON BLK		0.03	0.495			0.76	12.57
09605.44.01	16/5C SOOW SUPER VU-TRON BLK		0.03	0.495			0.76	12.57
09605.46.01	16/5C SOOW SUPER VU-TRON BLK		0.03	0.495			0.76	12.57
09605.XX.01	16/5C SOOW SUPER VU-TRON BLK		0.03	0.495			0.76	12.57
09605.35.01	16/5C SOOW SUPER VU-TRON BLK		0.03	0.495			0.76	12.57
09605.38.01	16/5C SOOW SUPER VU-TRON BLK		0.03	0.495			0.76	12.57
09605.99.01	16/5C SOOW SUPER VU-TRON BLK		0.03	0.495			0.76	12.57
09605.41.01M	16/5C SOOW SUPER VU-TRON BLK		0.03	0.495			0.76	12.57
09605.44.01M	16/5C SOOW SUPER VU-TRON BLK		0.03	0.495			0.76	12.57

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
09605.46.01M	16/5C SOOW SUPER VU-TRON BLK		0.03	0.495			0.76	12.57
09605.35.01M	16/5C SOOW SUPER VU-TRON BLK		0.03	0.495			0.76	12.57
09606.41.01M	16/6C SOOW SUPER VU-TRON BLK		0.03	0.52			0.76	13.21
09606.44.01M	16/6C SOOW SUPER VU-TRON BLK		0.03	0.52			0.76	13.21
09606.46.01M	16/6C SOOW SUPER VU-TRON BLK		0.03	0.52			0.76	13.21
09606.35.01M	16/6C SOOW SUPER VU-TRON BLK		0.03	0.52			0.76	13.21
09606.41.01	16/6C SOOW SUPER VU-TRON BLK		0.03	0.52			0.76	13.21
09606.44.01	16/6C SOOW SUPER VU-TRON BLK		0.03	0.52			0.76	13.21
09606.46.01	16/6C SOOW SUPER VU-TRON BLK		0.03	0.52			0.76	13.21
09606.XX.01	16/6C SOOW SUPER VU-TRON BLK		0.03	0.52			0.76	13.21

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
09606.35.01	16/6C SOOW SUPER VU-TRON BLK		0.03	0.52			0.76	13.21
09606.38.01	16/6C SOOW SUPER VU-TRON BLK		0.03	0.52			0.76	13.21
09606.99.01	16/6C SOOW SUPER VU-TRON BLK		0.03	0.52			0.76	13.21
09607.41.01M	16/7C SOOW SUPER VU-TRON BLK		0.03	0.54			0.76	13.72
09607.35.01M	16/7C SOOW SUPER VU-TRON BLK		0.03	0.54			0.76	13.72
09607.99.01M	16/7C SOOW SUPER VU-TRON BLK		0.03	0.54			0.76	13.72
09607.41.01	16/7C SOOW SUPER VU-TRON BLK		0.03	0.54			0.76	13.72
09607.44.01	16/7C SOOW SUPER VU-TRON BLK		0.03	0.54			0.76	13.72
09607.46.01	16/7C SOOW SUPER VU-TRON BLK		0.03	0.54			0.76	13.72
09607.XX.01	16/7C SOOW SUPER VU-TRON BLK		0.03	0.54			0.76	13.72

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
09607.35.01	16/7C SOOW SUPER VU-TRON BLK		0.03	0.54			0.76	13.72
09607.38.01	16/7C SOOW SUPER VU-TRON BLK		0.03	0.54			0.76	13.72
09607.99.01	16/7C SOOW SUPER VU-TRON BLK		0.03	0.54			0.76	13.72
09608.41.01M	16/8C SOOW SUPER VU-TRON BLK		0.03	0.575			0.76	14.61
09608.44.01M	16/8C SOOW SUPER VU-TRON BLK		0.03	0.575			0.76	14.61
09608.35.01M	16/8C SOOW SUPER VU-TRON BLK		0.03	0.575			0.76	14.61
09608.XX.01M	16/8C SOOW SUPER VU-TRON BLK		0.03	0.575			0.76	14.61
09608.41.01	16/8C SOOW SUPER VU-TRON BLK		0.03	0.575			0.76	14.61
09608.44.01	16/8C SOOW SUPER VU-TRON BLK		0.03	0.575			0.76	14.61
09608.XX.01	16/8C SOOW SUPER VU-TRON BLK		0.03	0.575			0.76	14.61

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
09608.35.01	16/8C SOOW SUPER VU-TRON BLK		0.03	0.575			0.76	14.61
09608.38.01	16/8C SOOW SUPER VU-TRON BLK		0.03	0.575			0.76	14.61
09608.99.01	16/8C SOOW SUPER VU-TRON BLK		0.03	0.575			0.76	14.61
09609.99.01M	16/9C SOOW SUPER VU-TRON BLK		0.03	0.6			0.76	15.24
09609.41.01	16/9C SOOW SUPER VU-TRON BLK		0.03	0.6			0.76	15.24
09609.XX.01	16/9C SOOW SUPER VU-TRON BLK		0.03	0.6			0.76	15.24
09609.99.01	16/9C SOOW SUPER VU-TRON BLK		0.03	0.6			0.76	15.24
09610.XX.01	16/10C SOOW SUPER VU-TRON BLK		0.03	0.62			0.76	15.75
09610.35.01	16/10C SOOW SUPER VU-TRON BLK		0.03	0.62			0.76	15.75
09610.99.01	16/10C SOOW SUPER VU-TRON BLK		0.03	0.62			0.76	15.75

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
09610.99.01M	16/10C SOOW SUPER VU-TRON BLK		0.03	0.62			0.76	15.75
09612.99.01M	16/12C SOOW SUPER VU-TRON BLK		0.03	0.66			0.76	16.76
09612.XX.01	16/12C SOOW SUPER VU-TRON BLK		0.03	0.66			0.76	16.76
09612.35.01	16/12C SOOW SUPER VU-TRON BLK		0.03	0.66			0.76	16.76
09612.99.01	16/12C SOOW SUPER VU-TRON BLK		0.03	0.66			0.76	16.76
09614.99.01M	16/14C SOOW SUPER VU-TRON BLK		0.03	0.73			0.76	18.54
09614.41.01	16/14C SOOW SUPER VU-TRON BLK		0.03	0.73			0.76	18.54
09614.XX.01	16/14C SOOW SUPER VU-TRON BLK		0.03	0.73			0.76	18.54
09614.99.01	16/14C SOOW SUPER VU-TRON BLK		0.03	0.73			0.76	18.54
09616.XX.01M	16/16C SOOW SUPER VU-TRON BLK		0.03	0.74			0.76	18.8

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
09616.99.01M	16/16C SOOW SUPER VU- TRON BLK		0.03	0.74			0.76	18.8
09616.XX.01	16/16C SOOW SUPER VU- TRON BLK		0.03	0.74			0.76	18.8
09616.35.01	16/16C SOOW SUPER VU- TRON BLK		0.03	0.74			0.76	18.8
09616.99.01	16/16C SOOW SUPER VU- TRON BLK		0.03	0.74			0.76	18.8
09620.99.01M	16/20C SOOW SUPER VU- TRON BLK		0.03	0.81			0.76	20.57
09620.XX.01	16/20C SOOW SUPER VU- TRON BLK		0.03	0.81			0.76	20.57
09620.99.01	16/20C SOOW SUPER VU- TRON BLK		0.03	0.81			0.76	20.57
09624.99.01M	16/24C SOOW SUPER VU- TRON BLK		0.03	0.925			0.76	23.5
09624.XX.01	16/24C SOOW SUPER VU- TRON BLK		0.03	0.925			0.76	23.5
09624.99.01	16/24C SOOW SUPER VU- TRON BLK		0.03	0.925			0.76	23.5

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
09630.99.01M	16/30C SOOW SUPER VU-TRON BLK		0.03	1.01			0.76	25.65
09630.XX.01	16/30C SOOW SUPER VU-TRON BLK		0.03	1.01			0.76	25.65
09630.99.01	16/30C SOOW SUPER VU-TRON BLK		0.03	1.01			0.76	25.65
09805.41.01M	18/5C SOOW SUPER VU-TRON BLK		0.03	0.465			0.76	11.81
09805.44.01M	18/5C SOOW SUPER VU-TRON BLK		0.03	0.465			0.76	11.81
09805.38.01M	18/5C SOOW SUPER VU-TRON BLK		0.03	0.465			0.76	11.81
09805.41.01	18/5C SOOW SUPER VU-TRON BLK		0.03	0.465			0.76	11.81
09805.44.01	18/5C SOOW SUPER VU-TRON BLK		0.03	0.465			0.76	11.81
09805.XX.01	18/5C SOOW SUPER VU-TRON BLK		0.03	0.465			0.76	11.81
09805.35.01	18/5C SOOW SUPER VU-TRON BLK		0.03	0.465			0.76	11.81

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
09805.38.01	18/5C SOOW SUPER VU-TRON BLK		0.03	0.465			0.76	11.81
09805.99.01	18/5C SOOW SUPER VU-TRON BLK		0.03	0.465			0.76	11.81
09806.41.01M	18/6C SOOW SUPER VU-TRON BLK		0.03	0.495			0.76	12.57
09806.44.01M	18/6C SOOW SUPER VU-TRON BLK		0.03	0.495			0.76	12.57
09806.46.01M	18/6C SOOW SUPER VU-TRON BLK		0.03	0.495			0.76	12.57
09806.99.01M	18/6C SOOW SUPER VU-TRON BLK		0.03	0.495			0.76	12.57
09806.41.01	18/6C SOOW SUPER VU-TRON BLK		0.03	0.495			0.76	12.57
09806.46.01	18/6C SOOW SUPER VU-TRON BLK		0.03	0.495			0.76	12.57
09806.XX.01	18/6C SOOW SUPER VU-TRON BLK		0.03	0.495			0.76	12.57
09806.35.01	18/6C SOOW SUPER VU-TRON BLK		0.03	0.495			0.76	12.57

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
09806.38.01	18/6C SOOW SUPER VU-TRON BLK		0.03	0.495			0.76	12.57
09806.99.01	18/6C SOOW SUPER VU-TRON BLK		0.03	0.495			0.76	12.57
09807.41.01M	18/7C SOOW SUPER VU-TRON BLK		0.03	0.52			0.76	13.21
09807.35.01M	18/7C SOOW SUPER VU-TRON BLK		0.03	0.52			0.76	13.21
09807.XX.01M	18/7C SOOW SUPER VU-TRON BLK		0.03	0.52			0.76	13.21
09807.41.01	18/7C SOOW SUPER VU-TRON BLK		0.03	0.52			0.76	13.21
09807.44.01	18/7C SOOW SUPER VU-TRON BLK		0.03	0.52			0.76	13.21
09807.35.01	18/7C SOOW SUPER VU-TRON BLK		0.03	0.52			0.76	13.21
09807.99.01	18/7C SOOW SUPER VU-TRON BLK		0.03	0.52			0.76	13.21
09808.41.01	18/8C SOOW SUPER VU-TRON BLK		0.03	0.53			0.76	13.46

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
09808.44.01	18/8C SOOW SUPER VU-TRON BLK		0.03	0.53			0.76	13.46
09808.XX.01	18/8C SOOW SUPER VU-TRON BLK		0.03	0.53			0.76	13.46
09808.35.01	18/8C SOOW SUPER VU-TRON BLK		0.03	0.53			0.76	13.46
09808.38.01	18/8C SOOW SUPER VU-TRON BLK		0.03	0.53			0.76	13.46
09808.99.01	18/8C SOOW SUPER VU-TRON BLK		0.03	0.53			0.76	13.46
09808.41.01M	18/8C SOOW SUPER VU-TRON BLK		0.03	0.53			0.76	13.46
09808.44.01M	18/8C SOOW SUPER VU-TRON BLK		0.03	0.53			0.76	13.46
09808.99.01M	18/8C SOOW SUPER VU-TRON BLK		0.03	0.53			0.76	13.46
09810.99.01M	18/10C SOOW SUPER VU-TRON BLK		0.03	0.595			0.76	15.11
09810.41.01	18/10C SOOW SUPER VU-TRON BLK		0.03	0.595			0.76	15.11

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
09810.38.01	18/10C SOOW SUPER VU-TRON BLK		0.03	0.595			0.76	15.11
09810.XX.01	18/10C SOOW SUPER VU-TRON BLK		0.03	0.595			0.76	15.11
09810.99.01	18/10C SOOW SUPER VU-TRON BLK		0.03	0.595			0.76	15.11
09812.35.01	18/12C SOOW SUPER VU-TRON BLK		0.03	0.6			0.76	15.24
09812.XX.01	18/12C SOOW SUPER VU-TRON BLK		0.03	0.6			0.76	15.24
09812.99.01	18/12C SOOW SUPER VU-TRON BLK		0.03	0.6			0.76	15.24
09812.99.01M	18/12C SOOW SUPER VU-TRON BLK		0.03	0.6			0.76	15.24
09814.99.01M	18/14C SOOW SUPER VU-TRON BLK		0.03	0.63			0.76	16
09814.XX.01	18/14C SOOW SUPER VU-TRON BLK		0.03	0.63			0.76	16
09814.99.01	18/14C SOOW SUPER VU-TRON BLK		0.03	0.63			0.76	16

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
09816.XX.01	18/16C SOOW SUPER VU-TRON BLK		0.03	0.7			0.76	17.78
09816.99.01	18/16C SOOW SUPER VU-TRON BLK		0.03	0.7			0.76	17.78
09816.99.01M	18/16C SOOW SUPER VU-TRON BLK		0.03	0.7			0.76	17.78
09820.99.01M	18/20C SOOW SUPER VU-TRON BLK		0.03	0.795			0.76	20.19
09820.XX.01	18/20C SOOW SUPER VU-TRON BLK		0.03	0.795			0.76	20.19
09820.99.01	18/20C SOOW SUPER VU-TRON BLK		0.03	0.795			0.76	20.19
09824.99.01M	18/24C SOOW SUPER VU-TRON BLK		0.03	0.85			0.76	21.59
09824.41.01	18/24C SOOW SUPER VU-TRON BLK		0.03	0.85			0.76	21.59
09824.XX.01	18/24C SOOW SUPER VU-TRON BLK		0.03	0.85			0.76	21.59
09824.38.01	18/24C SOOW SUPER VU-TRON BLK		0.03	0.85			0.76	21.59

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
09824.99.01	18/24C SOOW SUPER VU-TRON BLK		0.03	0.85			0.76	21.59
09830.99.01M	18/30C SOOW SUPER VU-TRON BLK		0.03	0.915			0.76	23.24
09830.99.01	18/30C SOOW SUPER VU-TRON BLK		0.03	0.915			0.76	23.24
09405.41.01	14/5C SOOW SUPER VU-TRON BLK		0.045	0.645			1.14	16.26
09405.44.01	14/5C SOOW SUPER VU-TRON BLK		0.045	0.645			1.14	16.26
09405.XX.01	14/5C SOOW SUPER VU-TRON BLK		0.045	0.645			1.14	16.26
09405.35.01	14/5C SOOW SUPER VU-TRON BLK		0.045	0.645			1.14	16.26
09405.38.01	14/5C SOOW SUPER VU-TRON BLK		0.045	0.645			1.14	16.26
09405.99.01	14/5C SOOW SUPER VU-TRON BLK		0.045	0.645			1.14	16.26
09405.41.01M	14/5C SOOW SUPER VU-TRON BLK		0.045	0.645			1.14	16.26

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
09405.44.01M	14/5C SOOW SUPER VU-TRON BLK		0.045	0.645			1.14	16.26
09405.35.01M	14/5C SOOW SUPER VU-TRON BLK		0.045	0.645			1.14	16.26
09406.41.01	14/6C SOOW SUPER VU-TRON BLK		0.045	0.71			1.14	18.03
09406.44.01	14/6C SOOW SUPER VU-TRON BLK		0.045	0.71			1.14	18.03
09406.XX.01	14/6C SOOW SUPER VU-TRON BLK		0.045	0.71			1.14	18.03
09406.35.01	14/6C SOOW SUPER VU-TRON BLK		0.045	0.71			1.14	18.03
09406.38.01	14/6C SOOW SUPER VU-TRON BLK		0.045	0.71			1.14	18.03
09406.99.01	14/6C SOOW SUPER VU-TRON BLK		0.045	0.71			1.14	18.03
09406.41.01M	14/6C SOOW SUPER VU-TRON BLK		0.045	0.71			1.14	18.03
09407.41.01	14/7C SOOW SUPER VU-TRON BLK		0.045	0.755			1.14	19.18

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
09407.44.01	14/7C SOOW SUPER VU-TRON BLK		0.045	0.755			1.14	19.18
09407.XX.01	14/7C SOOW SUPER VU-TRON BLK		0.045	0.755			1.14	19.18
09407.35.01	14/7C SOOW SUPER VU-TRON BLK		0.045	0.755			1.14	19.18
09407.99.01	14/7C SOOW SUPER VU-TRON BLK		0.045	0.755			1.14	19.18
09407.41.01M	14/7C SOOW SUPER VU-TRON BLK		0.045	0.755			1.14	19.18
09407.35.01M	14/7C SOOW SUPER VU-TRON BLK		0.045	0.755			1.14	19.18
09407.99.01M	14/7C SOOW SUPER VU-TRON BLK		0.045	0.755			1.14	19.18
09408.41.01M	14/8C SOOW SUPER VU-TRON BLK		0.045	0.81			1.14	20.57
09408.41.01	14/8C SOOW SUPER VU-TRON BLK		0.045	0.81			1.14	20.57
09408.XX.01	14/8C SOOW SUPER VU-TRON BLK		0.045	0.81			1.14	20.57

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
09408.35.01	14/8C SOOW SUPER VU- TRON BLK		0.045	0.81			1.14	20.57
09408.38.01	14/8C SOOW SUPER VU- TRON BLK		0.045	0.81			1.14	20.57
09410.XX.01M	14/10C SOOW SUPER VU- TRON BLK		0.045	0.875			1.14	22.23
09410.99.01M	14/10C SOOW SUPER VU- TRON BLK		0.045	0.875			1.14	22.23
09410.XX.01	14/10C SOOW SUPER VU- TRON BLK		0.045	0.875			1.14	22.23
09410.99.01	14/10C SOOW SUPER VU- TRON BLK		0.045	0.875			1.14	22.23
09412.XX.01	14/12C SOOW SUPER VU- TRON BLK		0.045	0.9			1.14	22.86
09412.99.01	14/12C SOOW SUPER VU- TRON BLK		0.045	0.9			1.14	22.86
09412.99.01M	14/12C SOOW SUPER VU- TRON BLK		0.045	0.9			1.14	22.86
09414.99.01	14/14C SOOW SUPER VU- TRON BLK		0.045	1			1.14	25.4

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
09416.99.01M	14/16C SOOW SUPER VU-TRON BLK		0.045	1.03			1.14	26.16
09416.XX.01	14/16C SOOW SUPER VU-TRON BLK		0.045	1.03			1.14	26.16
09416.99.01	14/16C SOOW SUPER VU-TRON BLK		0.045	1.03			1.14	26.16
09420.99.01M	14/20C SOOW SUPER VU-TRON BLK		0.045	1.155			1.14	29.34
09420.XX.01	14/20C SOOW SUPER VU-TRON BLK		0.045	1.155			1.14	29.34
09420.99.01	14/20C SOOW SUPER VU-TRON BLK		0.045	1.155			1.14	29.34
09424.99.01	14/24C SOOW SUPER VU-TRON BLK		0.045	1.26			1.14	32
09424.99.01M	14/24C SOOW SUPER VU-TRON BLK		0.045	1.26			1.14	32
09428.99.01	14/28C SOOW SUPER VU-TRON BLK		0.045	1.33			1.14	33.78
09430.XX.01	14/30C SOOW SUPER VU-TRON BLK		0.045	1.335			1.14	33.97

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
09430.99.01	14/30C SOOW SUPER VU- TRON BLK		0.045	1.335			1.14	33.97
09430.99.01M	14/30C SOOW SUPER VU- TRON BLK		0.045	1.335			1.14	33.97

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	09005.41.01M	10/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	423	LBS
	09005.43.01M	10/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	423	LBS
	09005.46.01M	10/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	423	LBS
	09005.35.01M	10/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	423	LBS
	09005.99.01M	10/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	423	LBS
	09005.41.01	10/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	423	LBS
	09005.43.01	10/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	423	LBS
	09005.46.01	10/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	423	LBS
	09005.XX.01	10/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	423	LBS
	09005.35.01	10/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	423	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	09005.38.01	10/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	423	LBS
	09005.99.01	10/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	423	LBS
	09006.XX.01	10/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	508	LBS
	09006.99.01	10/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	508	LBS
	09007.XX.01	10/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	549	LBS
	09007.99.01	10/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	549	LBS
	09008.44.01	10/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	625	LBS
	09008.XX.01	10/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	625	LBS
	09008.99.01	10/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	625	LBS
	09010.XX.01	10/10C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	755	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	09010.99.01	10/10C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	755	LBS
	09010.99.01M	10/10C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	755	LBS
	09012.99.01M	10/12C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	867	LBS
	09012.99.01	10/12C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	867	LBS
	09016.99.01M	10/16C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	1,142	LBS
	09016.99.01	10/16C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	1,142	LBS
	09020.99.01M	10/20C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	1,445	LBS
	09020.99.01	10/20C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	1,445	LBS
	02623.35.01	12/5C SOOW VUTRON BLK	US	Distribution products	MTO	308	LBS
	09205.41.01M	12/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	326	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	09205.44.01M	12/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	326	LBS
	09205.35.01M	12/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	326	LBS
	02623.35.05	12/5C SOOW VUTRON YLW	US	Distribution products	MTO	308	LBS
	09205.41.01	12/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	326	LBS
	09205.44.01	12/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	326	LBS
	09205.XX.01	12/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	326	LBS
	09205.35.01	12/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	326	LBS
	09205.38.01	12/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	326	LBS
	09205.99.01	12/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	326	LBS
	09206.41.01	12/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	362	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	09206.XX.01	12/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	362	LBS
	09206.35.01	12/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	362	LBS
	09206.99.01	12/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	362	LBS
	09206.41.01M	12/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	362	LBS
	09207.41.01M	12/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	415	LBS
	09207.35.01M	12/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	415	LBS
	09207.41.01	12/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	415	LBS
	09207.XX.01	12/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	415	LBS
	09207.35.01	12/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	415	LBS
	09207.99.01	12/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	415	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	09208.41.01	12/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	464	LBS
	09208.XX.01	12/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	464	LBS
	09208.35.01	12/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	464	LBS
	09208.38.01	12/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	464	LBS
	09208.99.01	12/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	464	LBS
	09208.41.01M	12/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	464	LBS
	09208.99.01M	12/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	464	LBS
	09209.XX.01	12/9C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	510	LBS
	09209.99.01	12/9C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	510	LBS
	09210.99.01M	12/10C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	602	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	09210.41.01	12/10C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	602	LBS
	09210.XX.01	12/10C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	602	LBS
	09210.99.01	12/10C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	602	LBS
	09212.99.01M	12/12C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	662	LBS
	09212.XX.01	12/12C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	662	LBS
	09212.99.01	12/12C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	662	LBS
	09214.99.01M	12/14C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	724	LBS
	09214.XX.01	12/14C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	724	LBS
	09214.99.01	12/14C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	724	LBS
	09216.99.01	12/16C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	869	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	09216.99.01M	12/16C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	869	LBS
	09220.99.01M	12/20C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	977	LBS
	09220.99.01	12/20C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	977	LBS
	09224.99.01M	12/24C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	1,236	LBS
	09224.XX.01	12/24C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	1,236	LBS
	09224.99.01	12/24C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	1,236	LBS
	09226.XX.01	12/26C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	1,309	LBS
	09226.99.01	12/26C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	1,309	LBS
	09230.XX.01	12/30C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	1,512	LBS
	09230.99.01	12/30C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	1,512	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	09230.99.01M	12/30C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	1,512	LBS
	09605.41.01	16/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	152	LBS
	09605.44.01	16/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	152	LBS
	09605.46.01	16/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	152	LBS
	09605.XX.01	16/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	152	LBS
	09605.35.01	16/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	152	LBS
	09605.38.01	16/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	152	LBS
	09605.99.01	16/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	152	LBS
	09605.41.01M	16/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	152	LBS
	09605.44.01M	16/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	152	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	09605.46.01M	16/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	152	LBS
	09605.35.01M	16/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	152	LBS
	09606.41.01M	16/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	184	LBS
	09606.44.01M	16/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	184	LBS
	09606.46.01M	16/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	184	LBS
	09606.35.01M	16/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	184	LBS
	09606.41.01	16/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	184	LBS
	09606.44.01	16/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	184	LBS
	09606.46.01	16/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	184	LBS
	09606.XX.01	16/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	184	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	09606.35.01	16/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	184	LBS
	09606.38.01	16/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	184	LBS
	09606.99.01	16/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	184	LBS
	09607.41.01M	16/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	210	LBS
	09607.35.01M	16/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	210	LBS
	09607.99.01M	16/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	210	LBS
	09607.41.01	16/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	210	LBS
	09607.44.01	16/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	210	LBS
	09607.46.01	16/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	210	LBS
	09607.XX.01	16/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	210	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	09607.35.01	16/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	210	LBS
	09607.38.01	16/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	210	LBS
	09607.99.01	16/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	210	LBS
	09608.41.01M	16/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	228	LBS
	09608.44.01M	16/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	228	LBS
	09608.35.01M	16/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	228	LBS
	09608.XX.01M	16/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	228	LBS
	09608.41.01	16/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	228	LBS
	09608.44.01	16/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	228	LBS
	09608.XX.01	16/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	228	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	09608.35.01	16/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	228	LBS
	09608.38.01	16/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	228	LBS
	09608.99.01	16/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	228	LBS
	09609.99.01M	16/9C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	255	LBS
	09609.41.01	16/9C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	255	LBS
	09609.XX.01	16/9C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	255	LBS
	09609.99.01	16/9C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	255	LBS
	09610.XX.01	16/10C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	260	LBS
	09610.35.01	16/10C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	260	LBS
	09610.99.01	16/10C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	260	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	09610.99.01M	16/10C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	260	LBS
	09612.99.01M	16/12C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	319	LBS
	09612.XX.01	16/12C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	319	LBS
	09612.35.01	16/12C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	319	LBS
	09612.99.01	16/12C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	319	LBS
	09614.99.01M	16/14C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	343	LBS
	09614.41.01	16/14C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	343	LBS
	09614.XX.01	16/14C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	343	LBS
	09614.99.01	16/14C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	343	LBS
	09616.XX.01M	16/16C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	367	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	09616.99.01M	16/16C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	367	LBS
	09616.XX.01	16/16C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	367	LBS
	09616.35.01	16/16C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	367	LBS
	09616.99.01	16/16C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	367	LBS
	09620.99.01M	16/20C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	444	LBS
	09620.XX.01	16/20C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	444	LBS
	09620.99.01	16/20C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	444	LBS
	09624.99.01M	16/24C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	547	LBS
	09624.XX.01	16/24C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	547	LBS
	09624.99.01	16/24C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	547	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	09630.99.01M	16/30C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	685	LBS
	09630.XX.01	16/30C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	685	LBS
	09630.99.01	16/30C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	685	LBS
	09805.41.01M	18/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	131	LBS
	09805.44.01M	18/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	131	LBS
	09805.38.01M	18/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	131	LBS
	09805.41.01	18/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	131	LBS
	09805.44.01	18/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	131	LBS
	09805.XX.01	18/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	131	LBS
	09805.35.01	18/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	131	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	09805.38.01	18/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	131	LBS
	09805.99.01	18/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	131	LBS
	09806.41.01M	18/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	142	LBS
	09806.44.01M	18/6C SOOW SUPER VU-TRON BLK	US	Distribution products		142	LBS
	09806.46.01M	18/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	142	LBS
	09806.99.01M	18/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	142	LBS
	09806.41.01	18/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	142	LBS
	09806.46.01	18/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	142	LBS
	09806.XX.01	18/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	142	LBS
	09806.35.01	18/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	142	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	09806.38.01	18/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	142	LBS
	09806.99.01	18/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	142	LBS
	09807.41.01M	18/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	161	LBS
	09807.35.01M	18/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	161	LBS
	09807.XX.01M	18/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	161	LBS
	09807.41.01	18/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	161	LBS
	09807.44.01	18/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	161	LBS
	09807.35.01	18/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	161	LBS
	09807.99.01	18/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	161	LBS
	09808.41.01	18/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	173	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	09808.44.01	18/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	173	LBS
	09808.XX.01	18/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	173	LBS
	09808.35.01	18/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	173	LBS
	09808.38.01	18/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	173	LBS
	09808.99.01	18/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	173	LBS
	09808.41.01M	18/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	173	LBS
	09808.44.01M	18/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	173	LBS
	09808.99.01M	18/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	173	LBS
	09810.99.01M	18/10C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	221	LBS
	09810.41.01	18/10C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	221	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	09810.38.01	18/10C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	221	LBS
	09810.XX.01	18/10C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	221	LBS
	09810.99.01	18/10C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	221	LBS
	09812.35.01	18/12C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	235	LBS
	09812.XX.01	18/12C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	235	LBS
	09812.99.01	18/12C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	235	LBS
	09812.99.01M	18/12C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	235	LBS
	09814.99.01M	18/14C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	262	LBS
	09814.XX.01	18/14C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	262	LBS
	09814.99.01	18/14C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	262	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	09816.XX.01	18/16C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	306	LBS
	09816.99.01	18/16C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	306	LBS
	09816.99.01M	18/16C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	306	LBS
	09820.99.01M	18/20C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	377	LBS
	09820.XX.01	18/20C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	377	LBS
	09820.99.01	18/20C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	377	LBS
	09824.99.01M	18/24C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	453	LBS
	09824.41.01	18/24C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	453	LBS
	09824.XX.01	18/24C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	453	LBS
	09824.38.01	18/24C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	453	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	09824.99.01	18/24C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	453	LBS
	09830.99.01M	18/30C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	524	LBS
	09830.99.01	18/30C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	524	LBS
	09405.41.01	14/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	266	LBS
	09405.44.01	14/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	266	LBS
	09405.XX.01	14/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	266	LBS
	09405.35.01	14/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	266	LBS
	09405.38.01	14/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	266	LBS
	09405.99.01	14/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	266	LBS
	09405.41.01M	14/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	266	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	09405.44.01M	14/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	266	LBS
	09405.35.01M	14/5C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	266	LBS
	09406.41.01	14/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	313	LBS
	09406.44.01	14/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	313	LBS
	09406.XX.01	14/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	313	LBS
	09406.35.01	14/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	313	LBS
	09406.38.01	14/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	313	LBS
	09406.99.01	14/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	313	LBS
	09406.41.01M	14/6C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	313	LBS
	09407.41.01	14/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	326	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	09407.44.01	14/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	326	LBS
	09407.XX.01	14/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	326	LBS
	09407.35.01	14/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	326	LBS
	09407.99.01	14/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	326	LBS
	09407.41.01M	14/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	326	LBS
	09407.35.01M	14/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	326	LBS
	09407.99.01M	14/7C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	326	LBS
	09408.41.01M	14/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	366	LBS
	09408.41.01	14/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTS	366	LBS
	09408.XX.01	14/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	366	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	09408.35.01	14/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	366	LBS
	09408.38.01	14/8C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	366	LBS
	09410.XX.01M	14/10C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	436	LBS
	09410.99.01M	14/10C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	436	LBS
	09410.XX.01	14/10C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	436	LBS
	09410.99.01	14/10C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	436	LBS
	09412.XX.01	14/12C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	516	LBS
	09412.99.01	14/12C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	516	LBS
	09412.99.01M	14/12C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	516	LBS
	09414.99.01	14/14C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	597	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	09416.99.01M	14/16C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	658	LBS
	09416.XX.01	14/16C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	658	LBS
	09416.99.01	14/16C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	658	LBS
	09420.99.01M	14/20C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	799	LBS
	09420.XX.01	14/20C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	799	LBS
	09420.99.01	14/20C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	799	LBS
	09424.99.01	14/24C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	998	LBS
	09424.99.01M	14/24C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	998	LBS
	09428.99.01	14/28C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	1,080	LBS
	09430.XX.01	14/30C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	1,146	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	09430.99.01	14/30C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	1,146	LBS
	09430.99.01M	14/30C SOOW SUPER VU-TRON BLK	US	Distribution products	MTO	1,146	LBS

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
09005.41.01M	10/5C SOOW SUPER VU-TRON BLK	FOOT	30	30	21	1000 FT Reel
09005.43.01M	10/5C SOOW SUPER VU-TRON BLK	FOOT	36	36	28	2000 FT Reel
09005.46.01M	10/5C SOOW SUPER VU-TRON BLK	FOOT	30	22	30	5000 FT Reel
09005.35.01M	10/5C SOOW SUPER VU-TRON BLK	FOOT	18	13	18	250 FT Reel
09005.99.01M	10/5C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09005.41.01	10/5C SOOW SUPER VU-TRON BLK	FOOT	30	22	30	1000 FT Reel
09005.43.01	10/5C SOOW SUPER VU-TRON BLK	FOOT	36	25	36	2000 FT Reel
09005.46.01	10/5C SOOW SUPER VU-TRON BLK	FOOT	30	22	30	5000 FT Reel
09005.XX.01	10/5C SOOW SUPER VU-TRON BLK	FOOT	18	13	18	Various Lengths
09005.35.01	10/5C SOOW SUPER VU-TRON BLK	FOOT	18	13	18	250 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
09005.38.01	10/5C SOOW SUPER VU-TRON BLK	FOOT	24	22	24	500 FT Reel
09005.99.01	10/5C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09006.XX.01	10/6C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Various Lengths
09006.99.01	10/6C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09007.XX.01	10/7C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Various Lengths
09007.99.01	10/7C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel
09008.44.01	10/8C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	2500 FT Reel
09008.XX.01	10/8C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Various Lengths
09008.99.01	10/8C SOOW SUPER VU-TRON BLK	FOOT	30	22	30	Factory Reel
09010.XX.01	10/10C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Various Lengths

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
09010.99.01	10/10C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel
09010.99.01M	10/10C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09012.99.01M	10/12C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09012.99.01	10/12C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09016.99.01M	10/16C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09016.99.01	10/16C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09020.99.01M	10/20C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09020.99.01	10/20C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
02623.35.01	12/5C SOOW VUTRON BLK	FOOT	30	22	30	250 FT Reel
09205.41.01M	12/5C SOOW SUPER VU-TRON BLK	FOOT	27	27	21	1000 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
09205.44.01M	12/5C SOOW SUPER VU-TRON BLK	FOOT	22	20	1	2500 FT Reel
09205.35.01M	12/5C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	250 FT Reel
02623.35.05	12/5C SOOW VUTRON YLW	FOOT	30	22	30	250 FT Reel
09205.41.01	12/5C SOOW SUPER VU-TRON BLK	FOOT	27	22	27	1000 FT Reel
09205.44.01	12/5C SOOW SUPER VU-TRON BLK	FOOT	36	25	36	2500 FT Reel
09205.XX.01	12/5C SOOW SUPER VU-TRON BLK	FOOT	16	13	16	Various Lengths
09205.35.01	12/5C SOOW SUPER VU-TRON BLK	FOOT	16	13	16	250 FT Reel
09205.38.01	12/5C SOOW SUPER VU-TRON BLK	FOOT	20	20	20	500 FT Reel
09205.99.01	12/5C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09206.41.01	12/6C SOOW SUPER VU-TRON BLK	FOOT	30	22	30	1000 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
09206.XX.01	12/6C SOOW SUPER VU-TRON BLK	FOOT	18	13	18	Various Lengths
09206.35.01	12/6C SOOW SUPER VU-TRON BLK	FOOT	22	20	1	250 FT Reel
09206.99.01	12/6C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09206.41.01M	12/6C SOOW SUPER VU-TRON BLK	FOOT	30	30	20	1000 FT Reel
09207.41.01M	12/7C SOOW SUPER VU-TRON BLK	FOOT	30	30	21	1000 FT Reel
09207.35.01M	12/7C SOOW SUPER VU-TRON BLK	FOOT	22	20	1	250 FT Reel
09207.41.01	12/7C SOOW SUPER VU-TRON BLK	FOOT	30	22	30	1000 FT Reel
09207.XX.01	12/7C SOOW SUPER VU-TRON BLK	FOOT	20	13	20	Various Lengths
09207.35.01	12/7C SOOW SUPER VU-TRON BLK	FOOT	18	13	18	250 FT Reel
09207.99.01	12/7C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
09208.41.01	12/8C SOOW SUPER VU-TRON BLK	FOOT	32	26	32	1000 FT Reel
09208.XX.01	12/8C SOOW SUPER VU-TRON BLK	FOOT	20	13	20	Various Lengths
09208.35.01	12/8C SOOW SUPER VU-TRON BLK	FOOT	24	22	24	250 FT Reel
09208.38.01	12/8C SOOW SUPER VU-TRON BLK	FOOT	24	22	24	500 FT Reel
09208.99.01	12/8C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09208.41.01M	12/8C SOOW SUPER VU-TRON BLK	FOOT	32	32	26	1000 FT Reel
09208.99.01M	12/8C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09209.XX.01	12/9C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Various Lengths
09209.99.01	12/9C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09210.99.01M	12/10C SOOW SUPER VU-TRON BLK	FOOT	49	42	48	Factory Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
09210.41.01	12/10C SOOW SUPER VU-TRON BLK	FOOT	49	42	48	1000 FT Reel
09210.XX.01	12/10C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Various Lengths
09210.99.01	12/10C SOOW SUPER VU-TRON BLK	FOOT	49	42	48	Factory Reel
09212.99.01M	12/12C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09212.XX.01	12/12C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Various Lengths
09212.99.01	12/12C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel
09214.99.01M	12/14C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09214.XX.01	12/14C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Various Lengths
09214.99.01	12/14C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09216.99.01	12/16C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
09216.99.01M	12/16C SOOW SUPER VU-TRON BLK	FOOT	49	42	1	Factory Reel
09220.99.01M	12/20C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09220.99.01	12/20C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09224.99.01M	12/24C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09224.XX.01	12/24C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Various Lengths
09224.99.01	12/24C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09226.XX.01	12/26C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Various Lengths
09226.99.01	12/26C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel
09230.XX.01	12/30C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Various Lengths
09230.99.01	12/30C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
09230.99.01M	12/30C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09605.41.01	16/5C SOOW SUPER VU-TRON BLK	FOOT	20	20	20	1000 FT Reel
09605.44.01	16/5C SOOW SUPER VU-TRON BLK	FOOT	30	22	30	2500 FT Reel
09605.46.01	16/5C SOOW SUPER VU-TRON BLK	FOOT	30	22	30	5000 FT Reel
09605.XX.01	16/5C SOOW SUPER VU-TRON BLK	FOOT	12	13	12	Various Lengths
09605.35.01	16/5C SOOW SUPER VU-TRON BLK	FOOT	14	13	14	250 FT Reel
09605.38.01	16/5C SOOW SUPER VU-TRON BLK	FOOT	16	13	16	500 FT Reel
09605.99.01	16/5C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09605.41.01M	16/5C SOOW SUPER VU-TRON BLK	FOOT	20	20	20	1000 FT Reel
09605.44.01M	16/5C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	2500 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
09605.46.01M	16/5C SOOW SUPER VU-TRON BLK	FOOT	22	20	1	5000 FT Reel
09605.35.01M	16/5C SOOW SUPER VU-TRON BLK	FOOT	14	13	14	250 FT Reel
09606.41.01M	16/6C SOOW SUPER VU-TRON BLK	FOOT	24	24	21	1000 FT Reel
09606.44.01M	16/6C SOOW SUPER VU-TRON BLK	FOOT	22	20	1	2500 FT Reel
09606.46.01M	16/6C SOOW SUPER VU-TRON BLK	FOOT	22	20	1	5000 FT Reel
09606.35.01M	16/6C SOOW SUPER VU-TRON BLK	FOOT	14	13	14	250 FT Reel
09606.41.01	16/6C SOOW SUPER VU-TRON BLK	FOOT	20	20	20	1000 FT Reel
09606.44.01	16/6C SOOW SUPER VU-TRON BLK	FOOT	30	22	30	2500 FT Reel
09606.46.01	16/6C SOOW SUPER VU-TRON BLK	FOOT	36	25	36	5000 FT Reel
09606.XX.01	16/6C SOOW SUPER VU-TRON BLK	FOOT	14	13	14	Various Lengths

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
09606.35.01	16/6C SOOW SUPER VU-TRON BLK	FOOT	14	13	14	250 FT Reel
09606.38.01	16/6C SOOW SUPER VU-TRON BLK	FOOT	20	13	20	500 FT Reel
09606.99.01	16/6C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09607.41.01M	16/7C SOOW SUPER VU-TRON BLK	FOOT	24	24	21	1000 FT Reel
09607.35.01M	16/7C SOOW SUPER VU-TRON BLK	FOOT	14	13	14	250 FT Reel
09607.99.01M	16/7C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09607.41.01	16/7C SOOW SUPER VU-TRON BLK	FOOT	24	22	24	1000 FT Reel
09607.44.01	16/7C SOOW SUPER VU-TRON BLK	FOOT	34	20	34	2500 FT Reel
09607.46.01	16/7C SOOW SUPER VU-TRON BLK	FOOT	34	20	34	5000 FT Reel
09607.XX.01	16/7C SOOW SUPER VU-TRON BLK	FOOT	14	13	14	Various Lengths

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
09607.35.01	16/7C SOOW SUPER VU-TRON BLK	FOOT	14	13	14	250 FT Reel
09607.38.01	16/7C SOOW SUPER VU-TRON BLK	FOOT	18	13	18	500 FT Reel
09607.99.01	16/7C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09608.41.01M	16/8C SOOW SUPER VU-TRON BLK	FOOT	24	24	21	1000 FT Reel
09608.44.01M	16/8C SOOW SUPER VU-TRON BLK	FOOT	34	34	18	2500 FT Reel
09608.35.01M	16/8C SOOW SUPER VU-TRON BLK	FOOT	14	13	14	250 FT Reel
09608.XX.01M	16/8C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Various Lengths
09608.41.01	16/8C SOOW SUPER VU-TRON BLK	FOOT	24	22	24	1000 FT Reel
09608.44.01	16/8C SOOW SUPER VU-TRON BLK	FOOT	36	25	36	2500 FT Reel
09608.XX.01	16/8C SOOW SUPER VU-TRON BLK	FOOT	14	13	14	Various Lengths

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
09608.35.01	16/8C SOOW SUPER VU-TRON BLK	FOOT	14	13	14	250 FT Reel
09608.38.01	16/8C SOOW SUPER VU-TRON BLK	FOOT	20	13	20	500 FT Reel
09608.99.01	16/8C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09609.99.01M	16/9C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel
09609.41.01	16/9C SOOW SUPER VU-TRON BLK	FOOT	27	22	27	1000 FT Reel
09609.XX.01	16/9C SOOW SUPER VU-TRON BLK	FOOT	27	22	27	Various Lengths
09609.99.01	16/9C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel
09610.XX.01	16/10C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Various Lengths
09610.35.01	16/10C SOOW SUPER VU-TRON BLK	FOOT	18	18	12	250 FT Reel
09610.99.01	16/10C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
09610.99.01M	16/10C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel
09612.99.01M	16/12C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel
09612.XX.01	16/12C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Various Lengths
09612.35.01	16/12C SOOW SUPER VU-TRON BLK	FOOT	27	22	27	250 FT Reel
09612.99.01	16/12C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel
09614.99.01M	16/14C SOOW SUPER VU-TRON BLK	FOOT	49	42	1	Factory Reel
09614.41.01	16/14C SOOW SUPER VU-TRON BLK	FOOT	27	22	27	1000 FT Reel
09614.XX.01	16/14C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Various Lengths
09614.99.01	16/14C SOOW SUPER VU-TRON BLK	FOOT	49	42	49	Factory Reel
09616.XX.01M	16/16C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Various Lengths

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
09616.99.01M	16/16C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel
09616.XX.01	16/16C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Various Lengths
09616.35.01	16/16C SOOW SUPER VU-TRON BLK	FOOT	22	20	1	250 FT Reel
09616.99.01	16/16C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel
09620.99.01M	16/20C SOOW SUPER VU-TRON BLK	FOOT	49	42	48	Factory Reel
09620.XX.01	16/20C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Various Lengths
09620.99.01	16/20C SOOW SUPER VU-TRON BLK	FOOT	49	42	48	Factory Reel
09624.99.01M	16/24C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09624.XX.01	16/24C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Various Lengths
09624.99.01	16/24C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
09630.99.01M	16/30C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel
09630.XX.01	16/30C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Various Lengths
09630.99.01	16/30C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel
09805.41.01M	18/5C SOOW SUPER VU-TRON BLK	FOOT	20	20	20	1000 FT Reel
09805.44.01M	18/5C SOOW SUPER VU-TRON BLK	FOOT	22	20	1	2500 FT Reel
09805.38.01M	18/5C SOOW SUPER VU-TRON BLK	FOOT	22	20	1	500 FT Reel
09805.41.01	18/5C SOOW SUPER VU-TRON BLK	FOOT	20	20	20	1000 FT Reel
09805.44.01	18/5C SOOW SUPER VU-TRON BLK	FOOT	27	22	27	2500 FT Reel
09805.XX.01	18/5C SOOW SUPER VU-TRON BLK	FOOT	14	13	14	Various Lengths
09805.35.01	18/5C SOOW SUPER VU-TRON BLK	FOOT	14	13	14	250 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
09805.38.01	18/5C SOOW SUPER VU-TRON BLK	FOOT	16	13	16	500 FT Reel
09805.99.01	18/5C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09806.41.01M	18/6C SOOW SUPER VU-TRON BLK	FOOT	20	20	20	1000 FT Reel
09806.44.01M	18/6C SOOW SUPER VU-TRON BLK	FOOT	22	20	1	2500 FT Reel
09806.46.01M	18/6C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	5000 FT Reel
09806.99.01M	18/6C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09806.41.01	18/6C SOOW SUPER VU-TRON BLK	FOOT	20	20	20	1000 FT Reel
09806.46.01	18/6C SOOW SUPER VU-TRON BLK	FOOT	36	25	36	5000 FT Reel
09806.XX.01	18/6C SOOW SUPER VU-TRON BLK	FOOT	14	13	14	Various Lengths
09806.35.01	18/6C SOOW SUPER VU-TRON BLK	FOOT	14	13	14	250 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
09806.38.01	18/6C SOOW SUPER VU-TRON BLK	FOOT	16	13	16	500 FT Reel
09806.99.01	18/6C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09807.41.01M	18/7C SOOW SUPER VU-TRON BLK	FOOT	24	24	18	1000 FT Reel
09807.35.01M	18/7C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	250 FT Reel
09807.XX.01M	18/7C SOOW SUPER VU-TRON BLK	FOOT	22	20	1	Various Lengths
09807.41.01	18/7C SOOW SUPER VU-TRON BLK	FOOT	20	20	20	1000 FT Reel
09807.44.01	18/7C SOOW SUPER VU-TRON BLK	FOOT	27	22	27	2500 FT Reel
09807.35.01	18/7C SOOW SUPER VU-TRON BLK	FOOT	14	13	14	250 FT Reel
09807.99.01	18/7C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09808.41.01	18/8C SOOW SUPER VU-TRON BLK	FOOT	24	22	24	1000 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
09808.44.01	18/8C SOOW SUPER VU-TRON BLK	FOOT	32	26	32	2500 FT Reel
09808.XX.01	18/8C SOOW SUPER VU-TRON BLK	FOOT	16	13	16	Various Lengths
09808.35.01	18/8C SOOW SUPER VU-TRON BLK	FOOT	14	13	14	250 FT Reel
09808.38.01	18/8C SOOW SUPER VU-TRON BLK	FOOT	18	13	18	500 FT Reel
09808.99.01	18/8C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09808.41.01M	18/8C SOOW SUPER VU-TRON BLK	FOOT	30	30	28	1000 FT Reel
09808.44.01M	18/8C SOOW SUPER VU-TRON BLK	FOOT	32	26	32	2500 FT Reel
09808.99.01M	18/8C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09810.99.01M	18/10C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel
09810.41.01	18/10C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	1000 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
09810.38.01	18/10C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	500 FT Reel
09810.XX.01	18/10C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Various Lengths
09810.99.01	18/10C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel
09812.35.01	18/12C SOOW SUPER VU-TRON BLK	FOOT	24	22	24	250 FT Reel
09812.XX.01	18/12C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Various Lengths
09812.99.01	18/12C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel
09812.99.01M	18/12C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel
09814.99.01M	18/14C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09814.XX.01	18/14C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Various Lengths
09814.99.01	18/14C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
09816.XX.01	18/16C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Various Lengths
09816.99.01	18/16C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel
09816.99.01M	18/16C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09820.99.01M	18/20C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09820.XX.01	18/20C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Various Lengths
09820.99.01	18/20C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel
09824.99.01M	18/24C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09824.41.01	18/24C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	1000 FT Reel
09824.XX.01	18/24C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Various Lengths
09824.38.01	18/24C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	500 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
09824.99.01	18/24C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel
09830.99.01M	18/30C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09830.99.01	18/30C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09405.41.01	14/5C SOOW SUPER VU-TRON BLK	FOOT	27	22	27	1000 FT Reel
09405.44.01	14/5C SOOW SUPER VU-TRON BLK	FOOT	36	25	36	2500 FT Reel
09405.XX.01	14/5C SOOW SUPER VU-TRON BLK	FOOT	16	13	16	Various Lengths
09405.35.01	14/5C SOOW SUPER VU-TRON BLK	FOOT	16	13	16	250 FT Reel
09405.38.01	14/5C SOOW SUPER VU-TRON BLK	FOOT	20	13	20	500 FT Reel
09405.99.01	14/5C SOOW SUPER VU-TRON BLK	FOOT	30	22	30	Factory Reel
09405.41.01M	14/5C SOOW SUPER VU-TRON BLK	FOOT	27	27	21	1000 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
09405.44.01M	14/5C SOOW SUPER VU-TRON BLK	FOOT	36	35	36	2500 FT Reel
09405.35.01M	14/5C SOOW SUPER VU-TRON BLK	FOOT	22	20	1	250 FT Reel
09406.41.01	14/6C SOOW SUPER VU-TRON BLK	FOOT	27	22	27	1000 FT Reel
09406.44.01	14/6C SOOW SUPER VU-TRON BLK	FOOT	27	22	27	2500 FT Reel
09406.XX.01	14/6C SOOW SUPER VU-TRON BLK	FOOT	16	13	16	Various Lengths
09406.35.01	14/6C SOOW SUPER VU-TRON BLK	FOOT	16	13	16	250 FT Reel
09406.38.01	14/6C SOOW SUPER VU-TRON BLK	FOOT	20	20	20	500 FT Reel
09406.99.01	14/6C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel
09406.41.01M	14/6C SOOW SUPER VU-TRON BLK	FOOT	26	27	18	1000 FT Reel
09407.41.01	14/7C SOOW SUPER VU-TRON BLK	FOOT	27	22	27	1000 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
09407.44.01	14/7C SOOW SUPER VU-TRON BLK	FOOT	36	25	36	2500 FT Reel
09407.XX.01	14/7C SOOW SUPER VU-TRON BLK	FOOT	16	13	16	Various Lengths
09407.35.01	14/7C SOOW SUPER VU-TRON BLK	FOOT	16	13	16	250 FT Reel
09407.99.01	14/7C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel
09407.41.01M	14/7C SOOW SUPER VU-TRON BLK	FOOT	27	27	21	1000 FT Reel
09407.35.01M	14/7C SOOW SUPER VU-TRON BLK	FOOT	22	20	1	250 FT Reel
09407.99.01M	14/7C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel
09408.41.01M	14/8C SOOW SUPER VU-TRON BLK	FOOT	30	30	21	1000 FT Reel
09408.41.01	14/8C SOOW SUPER VU-TRON BLK	FOOT	30	22	30	1000 FT Reel
09408.XX.01	14/8C SOOW SUPER VU-TRON BLK	FOOT	20	13	20	Various Lengths

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
09408.35.01	14/8C SOOW SUPER VU-TRON BLK	FOOT	20	13	20	250 FT Reel
09408.38.01	14/8C SOOW SUPER VU-TRON BLK	FOOT	24	22	24	500 FT Reel
09410.XX.01M	14/10C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Various Lengths
09410.99.01M	14/10C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09410.XX.01	14/10C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Various Lengths
09410.99.01	14/10C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel
09412.XX.01	14/12C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Various Lengths
09412.99.01	14/12C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel
09412.99.01M	14/12C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09414.99.01	14/14C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
09416.99.01M	14/16C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09416.XX.01	14/16C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Various Lengths
09416.99.01	14/16C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09420.99.01M	14/20C SOOW SUPER VU-TRON BLK	FOOT	48	48	1	Factory Reel
09420.XX.01	14/20C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Various Lengths
09420.99.01	14/20C SOOW SUPER VU-TRON BLK	FOOT	48	48	1	Factory Reel
09424.99.01	14/24C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel
09424.99.01M	14/24C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel
09428.99.01	14/28C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel
09430.XX.01	14/30C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Various Lengths

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
09430.99.01	14/30C SOOW SUPER VU-TRON BLK	FOOT	48	42	48	Factory Reel
09430.99.01M	14/30C SOOW SUPER VU-TRON BLK	FOOT	48	42	1	Factory Reel