ATTN: IEWC

IN RESPONSE TO YOUR REQUEST FOR SPECS ON PART BRC1402P-8-09 (B14209-FGINDU), 14/2 BRAKE CABLE, PLEASE FIND THE FOLLOWING:

- 1) GA: 14 GA. 2 CONDUCTORS
- 2) STRANDING: 19/.0142 BC
- 3) OVERALL O.D: .180X.300 O.D.
- 4) JACKET TYPE: BLACK 80 DEGREE PVC
- 5) INNER CONDUCTORS; BLACK AND WHITE
- 6) COPPER CONTENT: 24#/M'
- 7) STANDARD PUT-UP: 5000' PER 30" REEL

THIS IS TO CONFIRM THAT PART B14209-FGINDU, 14/2 BRAKE CABLE LISTED MEETS THE ABOVE SPECS.

ANDY HARWOOD VICE PRESIDENT