

CAROLPRENE SOOW

Rubber cord that performs in heat & cold, Resistant to oil/chemicals



GENERAL INFO

Thermoset rubber cord products have evolved over the last 50 years from simple and unsophisticated to a product line where specialized, technologically advanced products are in demand for exacting commercial and industrial applications. No longer are rubber cord products used only in applications where flexibility is needed; today typical applications require cord to perform well in environments of extreme heat and cold and on job sites and factory floors where resistance to oil, chemicals and abrasion is mandatory. General Cable's role, as the producer of the premiere Carol® Brand rubber cord products, is to ensure that new product development, product innovation and quality not only keep pace with industry requirements but also set the trends. Our rubber cord products carry a full range of listings and certifications with Underwriters Laboratories, Inc. and the Canadian Standard Association. In addition, many products meet or exceed the requirements of OSHA, MSHA and other relevant industry standards. Carol Brand is simply the most accepted in the industry, having proven itself on the job time after time. Our rubber cord line is the most comprehensive in the industry, ensuring that the proper Carol product can always be specified.

CONSTRUCTION/DESIGN

Nominal outer diameter [inch]	Conductor strand count	Cable marking	Conductor category	AWG size
1.085	133/0.0211	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Class 2 = stranded	2
1.17	133/0.0211	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Class 2 = stranded	2
1.46	133/23	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Class 2 = stranded	2
1.17	133/0.0211	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Class 2 = stranded	2
1.46	133/23	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Class 2 = stranded	2
1.39	133/0.0211	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Class 2 = stranded	2
1.58	133/23	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Class 2 = stranded	2
1.58	133/23	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Class 2 = stranded	2
0.87	119/25	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Class 2 = stranded	4
1.14	133/25	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Class 2 = stranded	4
1.14	133/25	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Class 2 = stranded	4
0.925	119/25	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Class 2 = stranded	4
1.26	133/25	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Class 2 = stranded	4

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
01819.99.01	2/3C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	2	Black, White, Green	3	Black
01819.41.01	2/3C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	2	Black, White, Green	3	Black
01819.XX.01	2/3C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	2	Black, White, Green	3	Black
01819.35.01	2/3C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	2	Black, White, Green	3	Black
01819.38.01	2/3C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	2	Black, White, Green	3	Black
01818.99.01	2/4C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	2	Black, White, Red, Green	4	Black
01818.41.01	2/4C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	2	Black, White, Red, Green	4	Black
01818.44.01	2/4C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	2	Black, White, Red, Green	4	Black
01818.46.01	2/4C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	2	Black, White, Red, Green	4	Black
01818.XX.01	2/4C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	2	Black, White, Red, Green	4	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
01818.35.01	2/4C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	2	Black, White, Red, Green	4	Black
01818.38.01	2/4C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	2	Black, White, Red, Green	4	Black
16094.99.01	2/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	2	Black, White, Red, Green	4	Black
16094.41.01	2/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	2	Black, White, Red, Green	4	Black
16094.XX.01	2/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	2	Black, White, Red, Green	4	Black
16094.35.01	2/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	2	Black, White, Red, Green	4	Black
16094.40.01	2/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	2	Black, White, Red, Green	4	Black
01818.38.05	2/4C SOOW CAROLPRENE YLW	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	2	Black, White, Red, Green	4	Yellow
16094.XX.01M	2/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	2	Black, White, Red, Green	4	Black
16094.40.01M	2/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	2	Black, White, Red, Green	4	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
98187.99.01	2/5C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	2	Black, White, Red, Green, Orange	5	Black
98187.XX.01	2/5C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	2	Black, White, Red, Green, Orange	5	Black
16095.99.01	2/5C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	2	Black, White, Red, Green, Orange	5	Black
16095.99.01M	2/5C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	2	Black, White, Red, Green, Orange	5	Black
01823.99.01	4/2C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	4	Black, White	2	Black
01823.41.01	4/2C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	4	Black, White	2	Black
01823.43.01	4/2C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	4	Black, White	2	Black
01823.46.01	4/2C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	4	Black, White	2	Black
01823.XX.01	4/2C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	4	Black, White	2	Black
01823.35.01	4/2C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	4	Black, White	2	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
16083.XX.01	4/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	4	Black, White, Green	3	Black
16083.35.01	4/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	4	Black, White, Green	3	Black
16083.40.01	4/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	4	Black, White, Green	3	Black
16083.XX.01M	4/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	4	Black, White, Green	3	Black
01822.99.01	4/3C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	4	Black, White, Green	3	Black
01822.41.01	4/3C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	4	Black, White, Green	3	Black
01822.46.01	4/3C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	4	Black, White, Green	3	Black
01822.XX.01	4/3C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	4	Black, White, Green	3	Black
01822.35.01	4/3C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	4	Black, White, Green	3	Black
01822.38.01	4/3C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	4	Black, White, Green	3	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
16084.99.01	4/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	4	Black, White, Red, Green	4	Black
16084.41.01	4/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	4	Black, White, Red, Green	4	Black
16084.46.01	4/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	4	Black, White, Red, Green	4	Black
16084.XX.01	4/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	4	Black, White, Red, Green	4	Black
16084.35.01	4/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	4	Black, White, Red, Green	4	Black
16084.38.01	4/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	4	Black, White, Red, Green	4	Black
16084.40.01	4/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	4	Black, White, Red, Green	4	Black
01821.99.01	4/4C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	4	Black, White, Red, Green	4	Black
01821.41.01	4/4C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	4	Black, White, Red, Green	4	Black
01821.44.01	4/4C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	4	Black, White, Red, Green	4	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
01821.46.01	4/4C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	4	Black, White, Red, Green	4	Black
01821.XX.01	4/4C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	4	Black, White, Red, Green	4	Black
01821.35.01	4/4C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	4	Black, White, Red, Green	4	Black
01821.38.01	4/4C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	4	Black, White, Red, Green	4	Black
16084.41.01M	4/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	4	Black, White, Red, Green	4	Black
16084.44.01M	4/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	4	Black, White, Red, Green	4	Black
16084.XX.01M	4/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	4	Black, White, Red, Green	4	Black
16084.35.01M	4/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	4	Black, White, Red, Green	4	Black
16084.40.01M	4/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	4	Black, White, Red, Green	4	Black
98463.99.01	4/5C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	4	Black, White, Red, Green, Orange	5	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
98463.XX.01	4/5C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	4	Black, White, Red, Green, Orange	5	Black
16085.99.01	4/5C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	4	Black, White, Red, Green, Orange	5	Black
16085.XX.01	4/5C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	4	Black, White, Red, Green, Orange	5	Black
16085.99.01M	4/5C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	4	Black, White, Red, Green, Orange	5	Black
01825.99.01	6/3C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	6	Black, White, Green	3	Black
01825.41.01	6/3C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	6	Black, White, Green	3	Black
01825.44.01	6/3C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	6	Black, White, Green	3	Black
01825.XX.01	6/3C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	6	Black, White, Green	3	Black
01825.33.01	6/3C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	6	Black, White, Green	3	Black
01825.35.01	6/3C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	6	Black, White, Green	3	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
01825.38.01	6/3C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	6	Black, White, Green	3	Black
01825.99.01M	6/3C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	6	Black, White, Green	3	Black
01825.41.01M	6/3C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	6	Black, White, Green	3	Black
16073.44.01M	6/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	6	Black, White, Green	3	Black
16073.35.01M	6/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	6	Black, White, Green	3	Black
16073.40.01M	6/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	6	Black, White, Green	3	Black
16073.99.01	6/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	6	Black, White, Green	3	Black
16073.41.01	6/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	6	Black, White, Green	3	Black
16073.46.01	6/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	6	Black, White, Green	3	Black
16073.XX.01	6/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	6	Black, White, Green	3	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
16073.35.01	6/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	6	Black, White, Green	3	Black
16073.40.01	6/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	6	Black, White, Green	3	Black
01824.38.05	6/4C SOOW CAROLPRENE YLW	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	6	Black, White, Red, Green	4	Yellow
01824.38T.05	6/4C SOOW CAROLPRENE YLW	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	6	Black, White, Red, Green	4	Yellow
16074.41.01M	6/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	6	Black, White, Red, Green	4	Black
16074.44.01M	6/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	6	Black, White, Red, Green	4	Black
16074.XX.01M	6/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	6	Black, White, Red, Green	4	Black
16074.35.01M	6/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	6	Black, White, Red, Green	4	Black
16074.40.01M	6/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	6	Black, White, Red, Green	4	Black
16074.99.01	6/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	6	Black, White, Red, Green	4	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
16074.41.01	6/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	6	Black, White, Red, Green	4	Black
16074.44.01	6/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	6	Black, White, Red, Green	4	Black
16074.46.01	6/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	6	Black, White, Red, Green	4	Black
16074.XX.01	6/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	6	Black, White, Red, Green	4	Black
16074.35.01	6/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	6	Black, White, Red, Green	4	Black
16074.38.01	6/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	6	Black, White, Red, Green	4	Black
16074.40.01	6/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	6	Black, White, Red, Green	4	Black
01824.99.01	6/4C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	6	Black, White, Red, Green	4	Black
01824.41.01	6/4C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	6	Black, White, Red, Green	4	Black
01824.44.01	6/4C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	6	Black, White, Red, Green	4	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
01824.46.01	6/4C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	6	Black, White, Red, Green	4	Black
01824.XX.01	6/4C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	6	Black, White, Red, Green	4	Black
01824.35.01	6/4C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	6	Black, White, Red, Green	4	Black
01824.38.01	6/4C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	6	Black, White, Red, Green	4	Black
16075.99.01M	6/5C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	6	Black, White, Red, Green, Orange	5	Black
98270.99.01	6/5C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	6	Black, White, Red, Green, Orange	5	Black
98270.XX.01	6/5C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	6	Black, White, Red, Green, Orange	5	Black
16075.99.01	6/5C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	6	Black, White, Red, Green, Orange	5	Black
16075.41.01	6/5C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	6	Black, White, Red, Green, Orange	5	Black
16075.46.01	6/5C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	6	Black, White, Red, Green, Orange	5	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
16075.XX.01	6/5C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	6	Black, White, Red, Green, Orange	5	Black
01811.99.01	8/2C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	8	Black, White	2	Black
01811.46.01	8/2C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	8	Black, White	2	Black
01811.XX.01	8/2C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	8	Black, White	2	Black
01812.99.01	8/3C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	8	Black, White, Green	3	Black
01812.41.01	8/3C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	8	Black, White, Green	3	Black
01812.44.01	8/3C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	8	Black, White, Green	3	Black
01812.XX.01	8/3C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	8	Black, White, Green	3	Black
01812.33.01	8/3C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	8	Black, White, Green	3	Black
01812.35.01	8/3C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	8	Black, White, Green	3	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
01812.38.01	8/3C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	8	Black, White, Green	3	Black
16063.41.01	8/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	8	Black, White, Green	3	Black
16063.46.01	8/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	8	Black, White, Green	3	Black
16063.35.01	8/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	8	Black, White, Green	3	Black
16063.38.01	8/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	8	Black, White, Green	3	Black
16063.40.01	8/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	8	Black, White, Green	3	Black
16063.XX.01	8/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	8	Black, White, Green	3	Black
16063.35.01M	8/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	8	Black, White, Green	3	Black
16063.38.01M	8/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	8	Black, White, Green	3	Black
16063.40.01M	8/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	8	Black, White, Green	3	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
16064.99.01	8/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	8	Black, White, Red, Green	4	Black
16064.41.01	8/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	8	Black, White, Red, Green	4	Black
16064.46.01	8/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	8	Black, White, Red, Green	4	Black
16064.XX.01	8/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	8	Black, White, Red, Green	4	Black
16064.35.01	8/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	8	Black, White, Red, Green	4	Black
16064.40.01	8/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	8	Black, White, Red, Green	4	Black
01827.38.05	8/4C SOOW CAROLPRENE YLW	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	8	Black, White, Red, Green	4	Yellow
01827.99.01	8/4C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	8	Black, White, Red, Green	4	Black
01827.41.01	8/4C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	8	Black, White, Red, Green	4	Black
01827.44.01	8/4C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	8	Black, White, Red, Green	4	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
01827.46.01	8/4C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	8	Black, White, Red, Green	4	Black
01827.XX.01	8/4C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	8	Black, White, Red, Green	4	Black
01827.35.01	8/4C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	8	Black, White, Red, Green	4	Black
01827.38.01	8/4C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	8	Black, White, Red, Green	4	Black
16064.44.01M	8/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	8	Black, White, Red, Green	4	Black
16064.XX.01M	8/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	8	Black, White, Red, Green	4	Black
16064.35.01M	8/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	8	Black, White, Red, Green	4	Black
16064.40.01M	8/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	8	Black, White, Red, Green	4	Black
98267.99.01	8/5C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	8	Black, White, Red, Green, Orange	5	Black
98267.41.01	8/5C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	8	Black, White, Red, Green, Orange	5	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
98267.XX.01	8/5C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	8	Black, White, Red, Green, Orange	5	Black
98267.35.01	8/5C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	8	Black, White, Red, Green, Orange	5	Black
16065.99.01M	8/5C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	8	Black, White, Red, Green, Orange	5	Black
16065.35.01M	8/5C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	8	Black, White, Red, Green, Orange	5	Black
16065.99.01	8/5C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	8	Black, White, Red, Green, Orange	5	Black
16065.41.01	8/5C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	8	Black, White, Red, Green, Orange	5	Black
16065.35.01	8/5C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	8	Black, White, Red, Green, Orange	5	Black
16065.XX.01	8/5C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	8	Black, White, Red, Green, Orange	5	Black
02767.41.03M	10/2C SOOW CAROLPRENE RED	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White	2	Red
02767.35.03M	10/2C SOOW CAROLPRENE RED	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White	2	Red

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
02767.41.03	10/2C SOOW CAROLPRENE RED	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White	2	Red
02767.XX.03	10/2C SOOW CAROLPRENE RED	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White	2	Red
02767.35.03	10/2C SOOW CAROLPRENE RED	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White	2	Red
02767.41T.01M	10/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White	2	Black
02767.46.01M	10/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White	2	Black
02767.85.01M	10/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White	2	Black
02767.41T.01	10/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White	2	Black
02767.46.01	10/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White	2	Black
02767.85.01	10/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White	2	Black
02728.99.01	10/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
02728.XX.01	10/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Black
02728.41T.01	10/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Black
02728.44.01	10/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Black
02728.46.01	10/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Black
02728.35.01	10/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Black
02728.35T.01	10/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Black
02728.38T.01	10/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Black
02728.85.01	10/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Black
02428.41T.05M	10/3C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Yellow
02428.35T.05M	10/3C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Yellow

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
02428.41T.05	10/3C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Yellow
02428.46.05	10/3C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Yellow
02428.XX.05	10/3C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Yellow
02428.35.05	10/3C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Yellow
02428.35T.05	10/3C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Yellow
02728.99.01M	10/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Black
02728.41T.01M	10/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Black
02728.44.01M	10/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Black
02728.46.01M	10/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Black
02728.35T.01M	10/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
02728.38T.01M	10/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Black
02728.41T.04	10/3C SOOW CAROLPRENE ORG	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Green	3	Orange
02727.99.01M	10/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Red, Green	4	Black
02727.41T.01M	10/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Red, Green	4	Black
02727.44.01M	10/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Red, Green	4	Black
02727.46.01M	10/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Red, Green	4	Black
02727.35T.01M	10/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Red, Green	4	Black
02727.38T.01M	10/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Red, Green	4	Black
02727.99.01	10/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Red, Green	4	Black
02727.41T.01	10/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Red, Green	4	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
02727.44.01	10/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Red, Green	4	Black
02727.46.01	10/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Red, Green	4	Black
02727.XX.01	10/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Red, Green	4	Black
02727.35T.01	10/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Red, Green	4	Black
02727.38T.01	10/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Red, Green	4	Black
02727.85.01	10/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Red, Green	4	Black
02427.41T.05M	10/4C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Red, Green	4	Yellow
02427.35.05M	10/4C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Red, Green	4	Yellow
02427.35T.05M	10/4C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Red, Green	4	Yellow
02427.99.05	10/4C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Red, Green	4	Yellow

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
02427.41T.05	10/4C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Red, Green	4	Yellow
02427.XX.05	10/4C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Red, Green	4	Yellow
02427.35.05	10/4C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Red, Green	4	Yellow
02427.35T.05	10/4C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	10	Black, White, Red, Green	4	Yellow
02724.41T.01M	12/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White	2	Black
02724.46.01M	12/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White	2	Black
02724.85.01M	12/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White	2	Black
02724.41.03	12/2C SOOW CAROLPRENE RED	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White	2	Red
02724.46.03	12/2C SOOW CAROLPRENE RED	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White	2	Red
02724.35.03	12/2C SOOW CAROLPRENE RED	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White	2	Red

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
02724.41.03M	12/2C SOOW CAROLPRENE RED	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White	2	Red
02724.46.03M	12/2C SOOW CAROLPRENE RED	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White	2	Red
02724.35.03M	12/2C SOOW CAROLPRENE RED	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White	2	Red
02724.41T.01	12/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White	2	Black
02724.46.01	12/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White	2	Black
02724.L2.01	12/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White	2	Black
02724.38.01	12/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White	2	Black
02724.85.01	12/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White	2	Black
02725.99.01M	12/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Black
02725.41T.01M	12/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
02725.44.01M	12/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Black
02725.46.01M	12/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Black
02725.35T.01M	12/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Black
02725.38T.01M	12/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Black
02725.41T.04	12/3C SOOW CAROLPRENE ORG	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Orange
02725.XX.04	12/3C SOOW CAROLPRENE ORG	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Orange
02725.35.04	12/3C SOOW CAROLPRENE ORG	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Orange
02425.41T.05	12/3C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Yellow
02425.XX.05	12/3C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Yellow
02425.35.05	12/3C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Yellow

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
02425.35T.05	12/3C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Yellow
02425.41T.05M	12/3C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Yellow
02425.35T.05M	12/3C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Yellow
02725.99.01	12/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Black
02725.41T.01	12/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Black
02725.44.01	12/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Black
02725.46.01	12/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Black
02725.XX.01	12/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Black
02725.35.01	12/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Black
02725.35T.01	12/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
02725.38T.01	12/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Black
02725.82.01	12/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Black
02725.85.01	12/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Green	3	Black
02426.99.05	12/4C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Yellow
02426.41T.05	12/4C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Yellow
02426.XX.05	12/4C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Yellow
02426.35T.05	12/4C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Yellow
02426.41T.05M	12/4C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Yellow
02426.35T.05M	12/4C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Yellow
02726.99.01	12/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
02726.41T.01	12/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Black
02726.44.01	12/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Black
02726.46.01	12/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Black
02726.XX.01	12/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Black
02726.35.01	12/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Black
02726.35T.01	12/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Black
02726.38T.01	12/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Black
02726.85.01	12/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Black
02726.41T.01M	12/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Black
02726.44.01M	12/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
02726.46.01M	12/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Black
02726.XX.01M	12/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Black
02726.35T.01M	12/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Black
02726.38T.01M	12/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	12	Black, White, Red, Green	4	Black
02722.41T.01M	16/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White	2	Black
02722.46.01M	16/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White	2	Black
02722.35.01M	16/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White	2	Black
02722.35T.01M	16/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White	2	Black
02722.99.01	16/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White	2	Black
02722.41T.01	16/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White	2	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
02722.44.01	16/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White	2	Black
02722.46.01	16/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White	2	Black
02722.35.01	16/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White	2	Black
02722.35T.01	16/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White	2	Black
02465.41T.05M	16/3C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Yellow
02465.35T.05M	16/3C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Yellow
02765.99.01	16/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black
02765.41T.01	16/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black
02765.44.01	16/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black
02765.46.01	16/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
02765.XX.01	16/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black
02765.35.01	16/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black
02765.35T.01	16/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black
02765.38T.01	16/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black
02765.82.01	16/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black
02465.41T.05	16/3C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Yellow
02465.XX.05	16/3C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Yellow
02465.35T.05	16/3C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Yellow
02765.99.01M	16/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black
02765.41T.01M	16/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
02765.44.01M	16/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black
02765.46.01M	16/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black
02765.35T.01M	16/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black
02765.38T.01M	16/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Green	3	Black
02466.41T.05	16/4C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Red, Green	4	Yellow
02466.XX.05	16/4C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Red, Green	4	Yellow
02466.35T.05	16/4C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Red, Green	4	Yellow
02766.99.01	16/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Red, Green	4	Black
02766.41.01	16/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Red, Green	4	Black
02766.41T.01	16/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Red, Green	4	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
02766.44.01	16/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Red, Green	4	Black
02766.46.01	16/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Red, Green	4	Black
02766.35T.01	16/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Red, Green	4	Black
02766.38T.01	16/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Red, Green	4	Black
02766.41T.01M	16/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Red, Green	4	Black
02766.44.01M	16/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Red, Green	4	Black
02766.46.01M	16/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Red, Green	4	Black
02766.35T.01M	16/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Red, Green	4	Black
02766.38T.01M	16/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Red, Green	4	Black
02466.41T.05M	16/4C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Red, Green	4	Yellow

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
02466.35T.05M	16/4C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	16	Black, White, Red, Green	4	Yellow
02757.41.01	16/5C SOOW CAROLPRENE BLK		16	NA	5	Black
02763.41T.01M	18/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White	2	Black
02763.35.01M	18/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White	2	Black
02763.35T.01M	18/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White	2	Black
02763.99.01	18/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White	2	Black
02763.41T.01	18/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White	2	Black
02763.44.01	18/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White	2	Black
02763.46.01	18/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White	2	Black
02763.35.01	18/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White	2	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
02763.35T.01	18/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White	2	Black
02469.41T.05	18/3C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Green	3	Yellow
02469.XX.05	18/3C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Green	3	Yellow
02469.35T.05	18/3C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Green	3	Yellow
02769.99.01M	18/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Green	3	Black
02769.41T.01M	18/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Green	3	Black
02769.46.01M	18/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Green	3	Black
02769.35T.01M	18/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Green	3	Black
02769.38.01M	18/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Green	3	Black
02469.35T.05M	18/3C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Green	3	Yellow

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
02769.99.01	18/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Green	3	Black
02769.41T.01	18/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Green	3	Black
02769.44.01	18/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Green	3	Black
02769.46.01	18/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Green	3	Black
02769.35.01	18/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Green	3	Black
02769.35T.01	18/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Green	3	Black
02769.38.01	18/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Green	3	Black
02770.99.01M	18/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Red, Green	4	Black
02770.41T.01M	18/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Red, Green	4	Black
02770.46.01M	18/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Red, Green	4	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
02770.35.01M	18/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Red, Green	4	Black
02770.35T.01M	18/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Red, Green	4	Black
02770.99.01	18/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Red, Green	4	Black
02770.41T.01	18/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Red, Green	4	Black
02770.46.01	18/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Red, Green	4	Black
02770.44.01	18/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Red, Green	4	Black
02770.35.01	18/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Red, Green	4	Black
02770.35T.01	18/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Red, Green	4	Black
02770.38.01	18/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Red, Green	4	Black
02470.35T.05	18/4C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	18	Black, White, Red, Green	4	Yellow

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
02723.41T.01M	14/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White	2	Black
02723.46.01M	14/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White	2	Black
02723.38T.01M	14/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White	2	Black
02723.85.01M	14/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White	2	Black
02723.41T.03	14/2C SOOW CAROLPRENE RED	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White	2	Red
02723.41T.03M	14/2C SOOW CAROLPRENE RED	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White	2	Red
02723.XX.01	14/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White	2	Black
02723.41T.01	14/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White	2	Black
02723.44.01	14/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White	2	Black
02723.46.01	14/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White	2	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
02723.38T.01	14/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White	2	Black
02723.85.01	14/2C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White	2	Black
02765R.44.01	16/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other		3	Black
02765R.46.01	16/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other		3	Black
02769R.46.01	18/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
01812R.35.01	8/3C SOOW CAROLPRENE BLK	CAROL (SIZE) TYPE SOOW 90°C P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA	Other	Black, White, Green	3	Black
02728R.41T.01	10/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
02728R.44.01	10/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
02462.41T.05	14/3C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Yellow
02462.XX.05	14/3C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm ²) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Yellow

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
02462.35.05	14/3C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Yellow
02462.35T.05	14/3C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Yellow
02762R.44.01	14/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
02762R.46.01	14/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
02762.41T.01M	14/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
02762.44.01M	14/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
02762.46.01M	14/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
02762.35T.01M	14/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
02762.38T.01M	14/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
02762.99.01	14/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
02762.41T.01	14/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
02762.44.01	14/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
02762.46.01	14/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
02762.XX.01	14/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
02762.35T.01	14/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
02762.38T.01	14/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
02762.82.01	14/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
02762.85.01	14/3C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Black
02462.41T.05M	14/3C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Yellow
02462.35T.05M	14/3C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Yellow

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
02465R.46.05	16/3C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Green	3	Yellow
02768.99.01	14/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Red, Green, Orange	4	Black
02768.41T.01	14/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Red, Green, Orange	4	Black
02768.44.01	14/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Red, Green, Orange	4	Black
02768.46.01	14/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Red, Green, Orange	4	Black
02768.35T.01	14/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Red, Green, Orange	4	Black
02768.38T.01	14/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Red, Green, Orange	4	Black
02768.85.01	14/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Red, Green, Orange	4	Black
02468.41T.05	14/4C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Red, Green	4	Yellow
02468.35T.05	14/4C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Red, Green	4	Yellow

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
02468.41T.05M	14/4C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Red, Green	4	Yellow
02468.35T.05M	14/4C SOOW CAROLPRENE YLW	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K 123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Red, Green	4	Yellow
02768.41T.01M	14/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Red, Green	4	Black
02768.44.01M	14/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Red, Green	4	Black
02768.46.01M	14/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Red, Green	4	Black
02768.35T.01M	14/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Red, Green	4	Black
02768.38T.01M	14/4C SOOW CAROLPRENE BLK	CAROL (SIZE) (mm2) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)	Other	Black, White, Red, Green	4	Black

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
01819.99.01	2/3C SOOW CAROLPRENE BLK		0.055	1.085			1.4	27.56
01819.41.01	2/3C SOOW CAROLPRENE BLK		0.055	1.085			1.4	27.56
01819.XX.01	2/3C SOOW CAROLPRENE BLK		0.055	1.085			1.4	27.56
01819.35.01	2/3C SOOW CAROLPRENE BLK		0.055	1.085			1.4	27.56
01819.38.01	2/3C SOOW CAROLPRENE BLK		0.055	1.085			1.4	27.56
01818.99.01	2/4C SOOW CAROLPRENE BLK		0.055	1.17			1.4	29.72
01818.41.01	2/4C SOOW CAROLPRENE BLK		0.055	1.17			1.4	29.72
01818.44.01	2/4C SOOW CAROLPRENE BLK		0.055	1.17			1.4	29.72
01818.46.01	2/4C SOOW CAROLPRENE BLK		0.055	1.17			1.4	29.72
01818.XX.01	2/4C SOOW CAROLPRENE BLK		0.055	1.17			1.4	29.72

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
01818.35.01	2/4C SOOW CAROLPRENE BLK		0.055	1.17			1.4	29.72
01818.38.01	2/4C SOOW CAROLPRENE BLK		0.055	1.17			1.4	29.72
16094.99.01	2/4C SOOW CAROLPRENE BLK		0.06	1.46			1.52	37.08
16094.41.01	2/4C SOOW CAROLPRENE BLK		0.06	1.46			1.52	37.08
16094.XX.01	2/4C SOOW CAROLPRENE BLK		0.06	1.46			1.52	37.08
16094.35.01	2/4C SOOW CAROLPRENE BLK		0.06	1.46			1.52	37.08
16094.40.01	2/4C SOOW CAROLPRENE BLK		0.06	1.46			1.52	37.08
01818.38.05	2/4C SOOW CAROLPRENE YLW		0.055	1.17			1.4	29.72
16094.XX.01M	2/4C SOOW CAROLPRENE BLK		0.06	1.46			1.52	37.08
16094.40.01M	2/4C SOOW CAROLPRENE BLK		0.06	1.46			1.52	37.08

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
98187.99.01	2/5C SOOW CAROLPRENE BLK		0.055	1.39			1.4	35.31
98187.XX.01	2/5C SOOW CAROLPRENE BLK		0.055	1.39			1.4	35.31
16095.99.01	2/5C SOOW CAROLPRENE BLK		0.06	1.58			1.52	40.13
16095.99.01M	2/5C SOOW CAROLPRENE BLK		0.06	1.58			1.52	40.13
01823.99.01	4/2C SOOW CAROLPRENE BLK		0.05	0.87			1.27	22.09
01823.41.01	4/2C SOOW CAROLPRENE BLK		0.05	0.87			1.27	22.09
01823.43.01	4/2C SOOW CAROLPRENE BLK		0.05	0.87			1.27	22.09
01823.46.01	4/2C SOOW CAROLPRENE BLK		0.05	0.87			1.27	22.09
01823.XX.01	4/2C SOOW CAROLPRENE BLK		0.05	0.87			1.27	22.09
01823.35.01	4/2C SOOW CAROLPRENE BLK		0.05	0.87			1.27	22.09

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
16083.XX.01	4/3C SOOW CAROLPRENE BLK		0.06	1.14			1.52	28.96
16083.35.01	4/3C SOOW CAROLPRENE BLK		0.06	1.14			1.52	28.96
16083.40.01	4/3C SOOW CAROLPRENE BLK		0.06	1.14			1.52	28.96
16083.XX.01M	4/3C SOOW CAROLPRENE BLK		0.06	1.14			1.52	28.96
01822.99.01	4/3C SOOW CAROLPRENE BLK		0.05	0.925			1.27	23.49
01822.41.01	4/3C SOOW CAROLPRENE BLK		0.05	0.925			1.27	23.49
01822.46.01	4/3C SOOW CAROLPRENE BLK		0.05	0.925			1.27	23.49
01822.XX.01	4/3C SOOW CAROLPRENE BLK		0.05	0.925			1.27	23.49
01822.35.01	4/3C SOOW CAROLPRENE BLK		0.05	0.925			1.27	23.49
01822.38.01	4/3C SOOW CAROLPRENE BLK		0.05	0.925			1.27	23.49

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
16084.99.01	4/4C SOOW CAROLPRENE BLK		0.06	1.26			1.52	32
16084.41.01	4/4C SOOW CAROLPRENE BLK		0.06	1.26			1.52	32
16084.46.01	4/4C SOOW CAROLPRENE BLK		0.06	1.26			1.52	32
16084.XX.01	4/4C SOOW CAROLPRENE BLK		0.06	1.26			1.52	32
16084.35.01	4/4C SOOW CAROLPRENE BLK		0.06	1.26			1.52	32
16084.38.01	4/4C SOOW CAROLPRENE BLK		0.06	1.26			1.52	32
16084.40.01	4/4C SOOW CAROLPRENE BLK		0.06	1.26			1.52	32
01821.99.01	4/4C SOOW CAROLPRENE BLK		0.05	1.015			1.27	25.78
01821.41.01	4/4C SOOW CAROLPRENE BLK		0.05	1.015			1.27	25.78
01821.44.01	4/4C SOOW CAROLPRENE BLK		0.05	1.015			1.27	25.78

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
01821.46.01	4/4C SOOW CAROLPRENE BLK		0.05	1.015			1.27	25.78
01821.XX.01	4/4C SOOW CAROLPRENE BLK		0.05	1.015			1.27	25.78
01821.35.01	4/4C SOOW CAROLPRENE BLK		0.05	1.015			1.27	25.78
01821.38.01	4/4C SOOW CAROLPRENE BLK		0.05	1.015			1.27	25.78
16084.41.01M	4/4C SOOW CAROLPRENE BLK		0.06	1.26			1.52	32
16084.44.01M	4/4C SOOW CAROLPRENE BLK		0.06	1.26			1.52	32
16084.XX.01M	4/4C SOOW CAROLPRENE BLK		0.06	1.26			1.52	32
16084.35.01M	4/4C SOOW CAROLPRENE BLK		0.06	1.26			1.52	32
16084.40.01M	4/4C SOOW CAROLPRENE BLK		0.06	1.26			1.52	32
98463.99.01	4/5C SOOW CAROLPRENE BLK		0.05	1.115			1.27	28.32

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
98463.XX.01	4/5C SOOW CAROLPRENE BLK		0.05	1.115			1.27	28.32
16085.99.01	4/5C SOOW CAROLPRENE BLK		0.06	1.365			1.52	34.67
16085.XX.01	4/5C SOOW CAROLPRENE BLK		0.06	1.365			1.52	34.67
16085.99.01M	4/5C SOOW CAROLPRENE BLK		0.06	1.365			1.52	34.67
01825.99.01	6/3C SOOW CAROLPRENE BLK		0.05	0.79			1.27	20.07
01825.41.01	6/3C SOOW CAROLPRENE BLK		0.05	0.79			1.27	20.07
01825.44.01	6/3C SOOW CAROLPRENE BLK		0.05	0.79			1.27	20.07
01825.XX.01	6/3C SOOW CAROLPRENE BLK		0.05	0.79			1.27	20.07
01825.33.01	6/3C SOOW CAROLPRENE BLK		0.05	0.79			1.27	20.07
01825.35.01	6/3C SOOW CAROLPRENE BLK		0.05	0.79			1.27	20.07

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
01825.38.01	6/3C SOOW CAROLPRENE BLK		0.05	0.79			1.27	20.07
01825.99.01M	6/3C SOOW CAROLPRENE BLK		0.05	0.79			1.27	20.07
01825.41.01M	6/3C SOOW CAROLPRENE BLK		0.05	0.79			1.27	20.07
16073.44.01M	6/3C SOOW CAROLPRENE BLK		0.06	0.98			1.52	24.89
16073.35.01M	6/3C SOOW CAROLPRENE BLK		0.06	0.98			1.52	24.89
16073.40.01M	6/3C SOOW CAROLPRENE BLK		0.06	0.98			1.52	24.89
16073.99.01	6/3C SOOW CAROLPRENE BLK		0.06	0.98			1.52	24.89
16073.41.01	6/3C SOOW CAROLPRENE BLK		0.06	0.98			1.52	24.89
16073.46.01	6/3C SOOW CAROLPRENE BLK		0.06	0.98			1.52	24.89
16073.XX.01	6/3C SOOW CAROLPRENE BLK		0.06	0.98			1.52	24.89

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
16073.35.01	6/3C SOOW CAROLPRENE BLK		0.06	0.98			1.52	24.89
16073.40.01	6/3C SOOW CAROLPRENE BLK		0.06	0.98			1.52	24.89
01824.38.05	6/4C SOOW CAROLPRENE YLW		0.05	0.865			1.27	21.97
01824.38T.05	6/4C SOOW CAROLPRENE YLW		0.05	0.865			1.27	21.97
16074.41.01M	6/4C SOOW CAROLPRENE BLK		0.06	1.08			1.52	27.43
16074.44.01M	6/4C SOOW CAROLPRENE BLK		0.06	1.08			1.52	27.43
16074.XX.01M	6/4C SOOW CAROLPRENE BLK		0.06	1.08			1.52	27.43
16074.35.01M	6/4C SOOW CAROLPRENE BLK		0.06	1.08			1.52	27.43
16074.40.01M	6/4C SOOW CAROLPRENE BLK		0.06	1.08			1.52	27.43
16074.99.01	6/4C SOOW CAROLPRENE BLK		0.06	1.08			1.52	27.43

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
16074.41.01	6/4C SOOW CAROLPRENE BLK		0.06	1.08			1.52	27.43
16074.44.01	6/4C SOOW CAROLPRENE BLK		0.06	1.08			1.52	27.43
16074.46.01	6/4C SOOW CAROLPRENE BLK		0.06	1.08			1.52	27.43
16074.XX.01	6/4C SOOW CAROLPRENE BLK		0.06	1.08			1.52	27.43
16074.35.01	6/4C SOOW CAROLPRENE BLK		0.06	1.08			1.52	27.43
16074.38.01	6/4C SOOW CAROLPRENE BLK		0.06	1.08			1.52	27.43
16074.40.01	6/4C SOOW CAROLPRENE BLK		0.06	1.08			1.52	27.43
01824.99.01	6/4C SOOW CAROLPRENE BLK		0.05	0.865			1.27	21.97
01824.41.01	6/4C SOOW CAROLPRENE BLK		0.05	0.865			1.27	21.97
01824.44.01	6/4C SOOW CAROLPRENE BLK		0.05	0.865			1.27	21.97

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
01824.46.01	6/4C SOOW CAROLPRENE BLK		0.05	0.865			1.27	21.97
01824.XX.01	6/4C SOOW CAROLPRENE BLK		0.05	0.865			1.27	21.97
01824.35.01	6/4C SOOW CAROLPRENE BLK		0.05	0.865			1.27	21.97
01824.38.01	6/4C SOOW CAROLPRENE BLK		0.05	0.865			1.27	21.97
16075.99.01M	6/5C SOOW CAROLPRENE BLK		0.06	1.2			1.52	30.48
98270.99.01	6/5C SOOW CAROLPRENE BLK		0.05	0.945			1.27	24
98270.XX.01	6/5C SOOW CAROLPRENE BLK		0.05	0.945			1.27	24
16075.99.01	6/5C SOOW CAROLPRENE BLK		0.06	1.2			1.52	30.48
16075.41.01	6/5C SOOW CAROLPRENE BLK		0.06	1.2			1.52	30.48
16075.46.01	6/5C SOOW CAROLPRENE BLK		0.06	1.2			1.52	30.48

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
16075.XX.01	6/5C SOOW CAROLPRENE BLK		0.06	1.2			1.52	30.48
01811.99.01	8/2C SOOW CAROLPRENE BLK		0.05	0.66			1.27	16.76
01811.46.01	8/2C SOOW CAROLPRENE BLK		0.05	0.66			1.27	16.76
01811.XX.01	8/2C SOOW CAROLPRENE BLK		0.05	0.66			1.27	16.76
01812.99.01	8/3C SOOW CAROLPRENE BLK		0.05	0.695			1.27	17.65
01812.41.01	8/3C SOOW CAROLPRENE BLK		0.05	0.695			1.27	17.65
01812.44.01	8/3C SOOW CAROLPRENE BLK		0.05	0.695			1.27	17.65
01812.XX.01	8/3C SOOW CAROLPRENE BLK		0.05	0.695			1.27	17.65
01812.33.01	8/3C SOOW CAROLPRENE BLK		0.05	0.695			1.27	17.65
01812.35.01	8/3C SOOW CAROLPRENE BLK		0.05	0.695			1.27	17.65

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
01812.38.01	8/3C SOOW CAROLPRENE BLK		0.05	0.695			1.27	17.65
16063.41.01	8/3C SOOW CAROLPRENE BLK		0.06	0.84			1.52	21.33
16063.46.01	8/3C SOOW CAROLPRENE BLK		0.06	0.84			1.52	21.33
16063.35.01	8/3C SOOW CAROLPRENE BLK		0.06	0.84			1.52	21.33
16063.38.01	8/3C SOOW CAROLPRENE BLK		0.06	0.84			1.52	21.33
16063.40.01	8/3C SOOW CAROLPRENE BLK		0.06	0.84			1.52	21.33
16063.XX.01	8/3C SOOW CAROLPRENE BLK		0.06	0.84			1.52	21.33
16063.35.01M	8/3C SOOW CAROLPRENE BLK		0.06	0.84			1.52	21.33
16063.38.01M	8/3C SOOW CAROLPRENE BLK		0.06	0.84			1.52	21.33
16063.40.01M	8/3C SOOW CAROLPRENE BLK		0.06	0.84			1.52	21.33

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
16064.99.01	8/4C SOOW CAROLPRENE BLK		0.06	0.945			1.52	24
16064.41.01	8/4C SOOW CAROLPRENE BLK		0.06	0.945			1.52	24
16064.46.01	8/4C SOOW CAROLPRENE BLK		0.06	0.945			1.52	24
16064.XX.01	8/4C SOOW CAROLPRENE BLK		0.06	0.945			1.52	24
16064.35.01	8/4C SOOW CAROLPRENE BLK		0.06	0.945			1.52	24
16064.40.01	8/4C SOOW CAROLPRENE BLK		0.06	0.945			1.52	24
01827.38.05	8/4C SOOW CAROLPRENE YLW		0.05	0.76			1.27	19.3
01827.99.01	8/4C SOOW CAROLPRENE BLK		0.05	0.76			1.27	19.3
01827.41.01	8/4C SOOW CAROLPRENE BLK		0.05	0.76			1.27	19.3
01827.44.01	8/4C SOOW CAROLPRENE BLK		0.05	0.76			1.27	19.3

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
01827.46.01	8/4C SOOW CAROLPRENE BLK		0.05	0.76			1.27	19.3
01827.XX.01	8/4C SOOW CAROLPRENE BLK		0.05	0.76			1.27	19.3
01827.35.01	8/4C SOOW CAROLPRENE BLK		0.05	0.76			1.27	19.3
01827.38.01	8/4C SOOW CAROLPRENE BLK		0.05	0.76			1.27	19.3
16064.44.01M	8/4C SOOW CAROLPRENE BLK		0.06	0.945			1.52	24
16064.XX.01M	8/4C SOOW CAROLPRENE BLK		0.06	0.945			1.52	24
16064.35.01M	8/4C SOOW CAROLPRENE BLK		0.06	0.945			1.52	24
16064.40.01M	8/4C SOOW CAROLPRENE BLK		0.06	0.945			1.52	24
98267.99.01	8/5C SOOW CAROLPRENE BLK		0.05	0.84			1.27	21.34
98267.41.01	8/5C SOOW CAROLPRENE BLK		0.05	0.84			1.27	21.34

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
98267.XX.01	8/5C SOOW CAROLPRENE BLK		0.05	0.84			1.27	21.34
98267.35.01	8/5C SOOW CAROLPRENE BLK		0.05	0.84			1.27	21.34
16065.99.01M	8/5C SOOW CAROLPRENE BLK		0.06	1.03			1.52	26.16
16065.35.01M	8/5C SOOW CAROLPRENE BLK		0.06	1.03			1.52	26.16
16065.99.01	8/5C SOOW CAROLPRENE BLK		0.06	1.03			1.52	26.16
16065.41.01	8/5C SOOW CAROLPRENE BLK		0.06	1.03			1.52	26.16
16065.35.01	8/5C SOOW CAROLPRENE BLK		0.06	1.03			1.52	26.16
16065.XX.01	8/5C SOOW CAROLPRENE BLK		0.06	1.03			1.52	26.16
02767.41.03M	10/2C SOOW CAROLPRENE RED		0.045	0.62			1.14	15.75
02767.35.03M	10/2C SOOW CAROLPRENE RED		0.045	0.62			1.14	15.75

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
02767.41.03	10/2C SOOW CAROLPRENE RED		0.045	0.62			1.14	15.75
02767.XX.03	10/2C SOOW CAROLPRENE RED		0.045	0.62			1.14	15.75
02767.35.03	10/2C SOOW CAROLPRENE RED		0.045	0.62			1.14	15.75
02767.41T.01M	10/2C SOOW CAROLPRENE BLK		0.045	0.62			1.14	15.75
02767.46.01M	10/2C SOOW CAROLPRENE BLK		0.045	0.62			1.14	15.75
02767.85.01M	10/2C SOOW CAROLPRENE BLK		0.045	0.62			1.14	15.75
02767.41T.01	10/2C SOOW CAROLPRENE BLK		0.045	0.62			1.14	15.75
02767.46.01	10/2C SOOW CAROLPRENE BLK		0.045	0.62			1.14	15.75
02767.85.01	10/2C SOOW CAROLPRENE BLK		0.045	0.62			1.14	15.75
02728.99.01	10/3C SOOW CAROLPRENE BLK		0.045	0.66			1.14	16.76

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
02728.XX.01	10/3C SOOW CAROLPRENE BLK		0.045	0.66			1.14	16.76
02728.41T.01	10/3C SOOW CAROLPRENE BLK		0.045	0.66			1.14	16.76
02728.44.01	10/3C SOOW CAROLPRENE BLK		0.045	0.66			1.14	16.76
02728.46.01	10/3C SOOW CAROLPRENE BLK		0.045	0.66			1.14	16.76
02728.35.01	10/3C SOOW CAROLPRENE BLK		0.045	0.66			1.14	16.76
02728.35T.01	10/3C SOOW CAROLPRENE BLK		0.045	0.66			1.14	16.76
02728.38T.01	10/3C SOOW CAROLPRENE BLK		0.045	0.66			1.14	16.76
02728.85.01	10/3C SOOW CAROLPRENE BLK		0.045	0.66			1.14	16.76
02428.41T.05M	10/3C SOOW CAROLPRENE YLW		0.045	0.66			1.14	16.76
02428.35T.05M	10/3C SOOW CAROLPRENE YLW		0.045	0.66			1.14	16.76

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
02428.41T.05	10/3C SOOW CAROLPRENE YLW		0.045	0.66			1.14	16.76
02428.46.05	10/3C SOOW CAROLPRENE YLW		0.045	0.66			1.14	16.76
02428.XX.05	10/3C SOOW CAROLPRENE YLW		0.045	0.66			1.14	16.76
02428.35.05	10/3C SOOW CAROLPRENE YLW		0.045	0.66			1.14	16.76
02428.35T.05	10/3C SOOW CAROLPRENE YLW		0.045	0.66			1.14	16.76
02728.99.01M	10/3C SOOW CAROLPRENE BLK		0.045	0.66			1.14	16.76
02728.41T.01M	10/3C SOOW CAROLPRENE BLK		0.045	0.66			1.14	16.76
02728.44.01M	10/3C SOOW CAROLPRENE BLK		0.045	0.66			1.14	16.76
02728.46.01M	10/3C SOOW CAROLPRENE BLK		0.045	0.66			1.14	16.76
02728.35T.01M	10/3C SOOW CAROLPRENE BLK		0.045	0.66			1.14	16.76

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
02728.38T.01M	10/3C SOOW CAROLPRENE BLK		0.045	0.66			1.14	16.76
02728.41T.04	10/3C SOOW CAROLPRENE ORG		0.045	0.66			1.14	16.76
02727.99.01M	10/4C SOOW CAROLPRENE BLK		0.045	0.715			1.14	18.16
02727.41T.01M	10/4C SOOW CAROLPRENE BLK		0.045	0.715			1.14	18.16
02727.44.01M	10/4C SOOW CAROLPRENE BLK		0.045	0.715			1.14	18.16
02727.46.01M	10/4C SOOW CAROLPRENE BLK		0.045	0.715			1.14	18.16
02727.35T.01M	10/4C SOOW CAROLPRENE BLK		0.045	0.715			1.14	18.16
02727.38T.01M	10/4C SOOW CAROLPRENE BLK		0.045	0.715			1.14	18.16
02727.99.01	10/4C SOOW CAROLPRENE BLK		0.045	0.715			1.14	18.16
02727.41T.01	10/4C SOOW CAROLPRENE BLK		0.045	0.715			1.14	18.16

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
02727.44.01	10/4C SOOW CAROLPRENE BLK		0.045	0.715			1.14	18.16
02727.46.01	10/4C SOOW CAROLPRENE BLK		0.045	0.715			1.14	18.16
02727.XX.01	10/4C SOOW CAROLPRENE BLK		0.045	0.715			1.14	18.16
02727.35T.01	10/4C SOOW CAROLPRENE BLK		0.045	0.715			1.14	18.16
02727.38T.01	10/4C SOOW CAROLPRENE BLK		0.045	0.715			1.14	18.16
02727.85.01	10/4C SOOW CAROLPRENE BLK		0.045	0.715			1.14	18.16
02427.41T.05M	10/4C SOOW CAROLPRENE YLW		0.045	0.715			1.14	18.16
02427.35.05M	10/4C SOOW CAROLPRENE YLW		0.045	0.715			1.14	18.16
02427.35T.05M	10/4C SOOW CAROLPRENE YLW		0.045	0.715			1.14	18.16
02427.99.05	10/4C SOOW CAROLPRENE YLW		0.045	0.715			1.14	18.16

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
02427.41T.05	10/4C SOOW CAROLPRENE YLW		0.045	0.715			1.14	18.16
02427.XX.05	10/4C SOOW CAROLPRENE YLW		0.045	0.715			1.14	18.16
02427.35.05	10/4C SOOW CAROLPRENE YLW		0.045	0.715			1.14	18.16
02427.35T.05	10/4C SOOW CAROLPRENE YLW		0.045	0.715			1.14	18.16
02724.41T.01M	12/2C SOOW CAROLPRENE BLK		0.045	0.57			1.14	14.48
02724.46.01M	12/2C SOOW CAROLPRENE BLK		0.045	0.57			1.14	14.48
02724.85.01M	12/2C SOOW CAROLPRENE BLK		0.045	0.57			1.14	14.48
02724.41.03	12/2C SOOW CAROLPRENE RED		0.045	0.57			1.14	14.48
02724.46.03	12/2C SOOW CAROLPRENE RED		0.045	0.57			1.14	14.48
02724.35.03	12/2C SOOW CAROLPRENE RED		0.045	0.57			1.14	14.48

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
02724.41.03M	12/2C SOOW CAROLPRENE RED		0.045	0.57			1.14	14.48
02724.46.03M	12/2C SOOW CAROLPRENE RED		0.045	0.57			1.14	14.48
02724.35.03M	12/2C SOOW CAROLPRENE RED		0.045	0.57			1.14	14.48
02724.41T.01	12/2C SOOW CAROLPRENE BLK		0.045	0.57			1.14	14.48
02724.46.01	12/2C SOOW CAROLPRENE BLK		0.045	0.57			1.14	14.48
02724.L2.01	12/2C SOOW CAROLPRENE BLK		0.045	0.57			1.14	14.48
02724.38.01	12/2C SOOW CAROLPRENE BLK		0.045	0.57			1.14	14.48
02724.85.01	12/2C SOOW CAROLPRENE BLK		0.045	0.57			1.14	14.48
02725.99.01M	12/3C SOOW CAROLPRENE BLK		0.045	0.595			1.14	15.11
02725.41T.01M	12/3C SOOW CAROLPRENE BLK		0.045	0.595			1.14	15.11

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
02725.44.01M	12/3C SOOW CAROLPRENE BLK		0.045	0.595			1.14	15.11
02725.46.01M	12/3C SOOW CAROLPRENE BLK		0.045	0.595			1.14	15.11
02725.35T.01M	12/3C SOOW CAROLPRENE BLK		0.045	0.595			1.14	15.11
02725.38T.01M	12/3C SOOW CAROLPRENE BLK		0.045	0.595			1.14	15.11
02725.41T.04	12/3C SOOW CAROLPRENE ORG		0.045	0.595			1.14	15.11
02725.XX.04	12/3C SOOW CAROLPRENE ORG		0.045	0.595			1.14	15.11
02725.35.04	12/3C SOOW CAROLPRENE ORG		0.045	0.595			1.14	15.11
02425.41T.05	12/3C SOOW CAROLPRENE YLW		0.045	0.595			1.14	15.11
02425.XX.05	12/3C SOOW CAROLPRENE YLW		0.045	0.595			1.14	15.11
02425.35.05	12/3C SOOW CAROLPRENE YLW		0.045	0.595			1.14	15.11

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
02425.35T.05	12/3C SOOW CAROLPRENE YLW		0.045	0.595			1.14	15.11
02425.41T.05M	12/3C SOOW CAROLPRENE YLW		0.045	0.595			1.14	15.11
02425.35T.05M	12/3C SOOW CAROLPRENE YLW		0.045	0.595			1.14	15.11
02725.99.01	12/3C SOOW CAROLPRENE BLK		0.045	0.595			1.14	15.11
02725.41T.01	12/3C SOOW CAROLPRENE BLK		0.045	0.595			1.14	15.11
02725.44.01	12/3C SOOW CAROLPRENE BLK		0.045	0.595			1.14	15.11
02725.46.01	12/3C SOOW CAROLPRENE BLK		0.045	0.595			1.14	15.11
02725.XX.01	12/3C SOOW CAROLPRENE BLK		0.045	0.595			1.14	15.11
02725.35.01	12/3C SOOW CAROLPRENE BLK		0.045	0.595			1.14	15.11
02725.35T.01	12/3C SOOW CAROLPRENE BLK		0.045	0.595			1.14	15.11

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
02725.38T.01	12/3C SOOW CAROLPRENE BLK		0.045	0.595			1.14	15.11
02725.82.01	12/3C SOOW CAROLPRENE BLK		0.045	0.595			1.14	15.11
02725.85.01	12/3C SOOW CAROLPRENE BLK		0.045	0.595			1.14	15.11
02426.99.05	12/4C SOOW CAROLPRENE YLW		0.045	0.65			1.14	16.51
02426.41T.05	12/4C SOOW CAROLPRENE YLW		0.045	0.65			1.14	16.51
02426.XX.05	12/4C SOOW CAROLPRENE YLW		0.045	0.65			1.14	16.51
02426.35T.05	12/4C SOOW CAROLPRENE YLW		0.045	0.65			1.14	16.51
02426.41T.05M	12/4C SOOW CAROLPRENE YLW		0.045	0.65			1.14	16.51
02426.35T.05M	12/4C SOOW CAROLPRENE YLW		0.045	0.65			1.14	16.51
02726.99.01	12/4C SOOW CAROLPRENE BLK		0.045	0.65			1.14	16.51

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
02726.41T.01	12/4C SOOW CAROLPRENE BLK		0.045	0.65			1.14	16.51
02726.44.01	12/4C SOOW CAROLPRENE BLK		0.045	0.65			1.14	16.51
02726.46.01	12/4C SOOW CAROLPRENE BLK		0.045	0.65			1.14	16.51
02726.XX.01	12/4C SOOW CAROLPRENE BLK		0.045	0.65			1.14	16.51
02726.35.01	12/4C SOOW CAROLPRENE BLK		0.045	0.65			1.14	16.51
02726.35T.01	12/4C SOOW CAROLPRENE BLK		0.045	0.65			1.14	16.51
02726.38T.01	12/4C SOOW CAROLPRENE BLK		0.045	0.65			1.14	16.51
02726.85.01	12/4C SOOW CAROLPRENE BLK		0.045	0.65			1.14	16.51
02726.41T.01M	12/4C SOOW CAROLPRENE BLK		0.045	0.65			1.14	16.51
02726.44.01M	12/4C SOOW CAROLPRENE BLK		0.045	0.65			1.14	16.51

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
02726.46.01M	12/4C SOOW CAROLPRENE BLK		0.045	0.65			1.14	16.51
02726.XX.01M	12/4C SOOW CAROLPRENE BLK		0.045	0.65			1.14	16.51
02726.35T.01M	12/4C SOOW CAROLPRENE BLK		0.045	0.65			1.14	16.51
02726.38T.01M	12/4C SOOW CAROLPRENE BLK		0.045	0.65			1.14	16.51
02722.41T.01M	16/2C SOOW CAROLPRENE BLK		0.03	0.37			0.76	9.4
02722.46.01M	16/2C SOOW CAROLPRENE BLK		0.03	0.37			0.76	9.4
02722.35.01M	16/2C SOOW CAROLPRENE BLK		0.03	0.37			0.76	9.4
02722.35T.01M	16/2C SOOW CAROLPRENE BLK		0.03	0.37			0.76	9.4
02722.99.01	16/2C SOOW CAROLPRENE BLK		0.03	0.37			0.76	9.4
02722.41T.01	16/2C SOOW CAROLPRENE BLK		0.03	0.37			0.76	9.4

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
02722.44.01	16/2C SOOW CAROLPRENE BLK		0.03	0.37			0.76	9.4
02722.46.01	16/2C SOOW CAROLPRENE BLK		0.03	0.37			0.76	9.4
02722.35.01	16/2C SOOW CAROLPRENE BLK		0.03	0.37			0.76	9.4
02722.35T.01	16/2C SOOW CAROLPRENE BLK		0.03	0.37			0.76	9.4
02465.41T.05M	16/3C SOOW CAROLPRENE YLW		0.03	0.39			0.76	9.91
02465.35T.05M	16/3C SOOW CAROLPRENE YLW		0.03	0.39			0.76	9.91
02765.99.01	16/3C SOOW CAROLPRENE BLK		0.03	0.39			0.76	9.91
02765.41T.01	16/3C SOOW CAROLPRENE BLK		0.03	0.39			0.76	9.91
02765.44.01	16/3C SOOW CAROLPRENE BLK		0.03	0.39			0.76	9.91
02765.46.01	16/3C SOOW CAROLPRENE BLK		0.03	0.39			0.76	9.91

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
02765.XX.01	16/3C SOOW CAROLPRENE BLK		0.03	0.39			0.76	9.91
02765.35.01	16/3C SOOW CAROLPRENE BLK		0.03	0.39			0.76	9.91
02765.35T.01	16/3C SOOW CAROLPRENE BLK		0.03	0.39			0.76	9.91
02765.38T.01	16/3C SOOW CAROLPRENE BLK		0.03	0.39			0.76	9.91
02765.82.01	16/3C SOOW CAROLPRENE BLK		0.03	0.39			0.76	9.91
02465.41T.05	16/3C SOOW CAROLPRENE YLW		0.03	0.39			0.76	9.91
02465.XX.05	16/3C SOOW CAROLPRENE YLW		0.03	0.39			0.76	9.91
02465.35T.05	16/3C SOOW CAROLPRENE YLW		0.03	0.39			0.76	9.91
02765.99.01M	16/3C SOOW CAROLPRENE BLK		0.03	0.39			0.76	9.91
02765.41T.01M	16/3C SOOW CAROLPRENE BLK		0.03	0.39			0.76	9.91

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
02765.44.01M	16/3C SOOW CAROLPRENE BLK		0.03	0.39			0.76	9.91
02765.46.01M	16/3C SOOW CAROLPRENE BLK		0.03	0.39			0.76	9.91
02765.35T.01M	16/3C SOOW CAROLPRENE BLK		0.03	0.39			0.76	9.91
02765.38T.01M	16/3C SOOW CAROLPRENE BLK		0.03	0.39			0.76	9.91
02466.41T.05	16/4C SOOW CAROLPRENE YLW		0.03	0.42			0.76	10.67
02466.XX.05	16/4C SOOW CAROLPRENE YLW		0.03	0.42			0.76	10.67
02466.35T.05	16/4C SOOW CAROLPRENE YLW		0.03	0.42			0.76	10.67
02766.99.01	16/4C SOOW CAROLPRENE BLK		0.03	0.42			0.76	10.67
02766.41.01	16/4C SOOW CAROLPRENE BLK		0.03	0.42			0.76	10.67
02766.41T.01	16/4C SOOW CAROLPRENE BLK		0.03	0.42			0.76	10.67

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
02766.44.01	16/4C SOOW CAROLPRENE BLK		0.03	0.42			0.76	10.67
02766.46.01	16/4C SOOW CAROLPRENE BLK		0.03	0.42			0.76	10.67
02766.35T.01	16/4C SOOW CAROLPRENE BLK		0.03	0.42			0.76	10.67
02766.38T.01	16/4C SOOW CAROLPRENE BLK		0.03	0.42			0.76	10.67
02766.41T.01M	16/4C SOOW CAROLPRENE BLK		0.03	0.42			0.76	10.67
02766.44.01M	16/4C SOOW CAROLPRENE BLK		0.03	0.42			0.76	10.67
02766.46.01M	16/4C SOOW CAROLPRENE BLK		0.03	0.42			0.76	10.67
02766.35T.01M	16/4C SOOW CAROLPRENE BLK		0.03	0.42			0.76	10.67
02766.38T.01M	16/4C SOOW CAROLPRENE BLK		0.03	0.42			0.76	10.67
02466.41T.05M	16/4C SOOW CAROLPRENE YLW		0.03	0.42			0.76	10.67

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
02466.35T.05M	16/4C SOOW CAROLPRENE YLW		0.03	0.42			0.76	10.67
02757.41.01	16/5C SOOW CAROLPRENE BLK							
02763.41T.01M	18/2C SOOW CAROLPRENE BLK		0.03	0.345			0.76	8.76
02763.35.01M	18/2C SOOW CAROLPRENE BLK		0.03	0.345			0.76	8.76
02763.35T.01M	18/2C SOOW CAROLPRENE BLK		0.03	0.345			0.76	8.76
02763.99.01	18/2C SOOW CAROLPRENE BLK		0.03	0.345			0.76	8.76
02763.41T.01	18/2C SOOW CAROLPRENE BLK		0.03	0.345			0.76	8.76
02763.44.01	18/2C SOOW CAROLPRENE BLK		0.03	0.345			0.76	8.76
02763.46.01	18/2C SOOW CAROLPRENE BLK		0.03	0.345			0.76	8.76
02763.35.01	18/2C SOOW CAROLPRENE BLK		0.03	0.345			0.76	8.76

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
02763.35T.01	18/2C SOOW CAROLPRENE BLK		0.03	0.345			0.76	8.76
02469.41T.05	18/3C SOOW CAROLPRENE YLW		0.03	0.365			0.76	9.27
02469.XX.05	18/3C SOOW CAROLPRENE YLW		0.03	0.365			0.76	9.27
02469.35T.05	18/3C SOOW CAROLPRENE YLW		0.03	0.365			0.76	9.27
02769.99.01M	18/3C SOOW CAROLPRENE BLK		0.03	0.365			0.76	9.27
02769.41T.01M	18/3C SOOW CAROLPRENE BLK		0.03	0.365			0.76	9.27
02769.46.01M	18/3C SOOW CAROLPRENE BLK		0.03	0.365			0.76	9.27
02769.35T.01M	18/3C SOOW CAROLPRENE BLK		0.03	0.365			0.76	9.27
02769.38.01M	18/3C SOOW CAROLPRENE BLK		0.03	0.365			0.76	9.27
02469.35T.05M	18/3C SOOW CAROLPRENE YLW		0.03	0.365			0.76	9.27

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
02769.99.01	18/3C SOOW CAROLPRENE BLK		0.03	0.365			0.76	9.27
02769.41T.01	18/3C SOOW CAROLPRENE BLK		0.03	0.365			0.76	9.27
02769.44.01	18/3C SOOW CAROLPRENE BLK		0.03	0.365			0.76	9.27
02769.46.01	18/3C SOOW CAROLPRENE BLK		0.03	0.365			0.76	9.27
02769.35.01	18/3C SOOW CAROLPRENE BLK		0.03	0.365			0.76	9.27
02769.35T.01	18/3C SOOW CAROLPRENE BLK		0.03	0.365			0.76	9.27
02769.38.01	18/3C SOOW CAROLPRENE BLK		0.03	0.365			0.76	9.27
02770.99.01M	18/4C SOOW CAROLPRENE BLK		0.03	0.39			0.76	9.91
02770.41T.01M	18/4C SOOW CAROLPRENE BLK		0.03	0.39			0.76	9.91
02770.46.01M	18/4C SOOW CAROLPRENE BLK		0.03	0.39			0.76	9.91

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
02770.35.01M	18/4C SOOW CAROLPRENE BLK		0.03	0.39			0.76	9.91
02770.35T.01M	18/4C SOOW CAROLPRENE BLK		0.03	0.39			0.76	9.91
02770.99.01	18/4C SOOW CAROLPRENE BLK		0.03	0.39			0.76	9.91
02770.41T.01	18/4C SOOW CAROLPRENE BLK		0.03	0.39			0.76	9.91
02770.46.01	18/4C SOOW CAROLPRENE BLK		0.03	0.39			0.76	9.91
02770.44.01	18/4C SOOW CAROLPRENE BLK		0.03	0.39			0.76	9.91
02770.35.01	18/4C SOOW CAROLPRENE BLK		0.03	0.39			0.76	9.91
02770.35T.01	18/4C SOOW CAROLPRENE BLK		0.03	0.39			0.76	9.91
02770.38.01	18/4C SOOW CAROLPRENE BLK		0.03	0.39			0.76	9.91
02470.35T.05	18/4C SOOW CAROLPRENE YLW		0.03	0.39			0.76	9.91

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
02723.41T.01M	14/2C SOOW CAROLPRENE BLK		0.045	0.51			1.14	12.95
02723.46.01M	14/2C SOOW CAROLPRENE BLK		0.045	0.51			1.14	12.95
02723.38T.01M	14/2C SOOW CAROLPRENE BLK		0.045	0.51			1.14	12.95
02723.85.01M	14/2C SOOW CAROLPRENE BLK		0.045	0.51			1.14	12.95
02723.41T.03	14/2C SOOW CAROLPRENE RED		0.045	0.51			1.14	12.95
02723.41T.03M	14/2C SOOW CAROLPRENE RED		0.045	0.51			1.14	12.95
02723.XX.01	14/2C SOOW CAROLPRENE BLK		0.045	0.51			1.14	12.95
02723.41T.01	14/2C SOOW CAROLPRENE BLK		0.045	0.51			1.14	12.95
02723.44.01	14/2C SOOW CAROLPRENE BLK		0.045	0.51			1.14	12.95
02723.46.01	14/2C SOOW CAROLPRENE BLK		0.045	0.51			1.14	12.95

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
02723.38T.01	14/2C SOOW CAROLPRENE BLK		0.045	0.51			1.14	12.95
02723.85.01	14/2C SOOW CAROLPRENE BLK		0.045	0.51			1.14	12.95
02765R.44.01	16/3C SOOW CAROLPRENE BLK							
02765R.46.01	16/3C SOOW CAROLPRENE BLK							
02769R.46.01	18/3C SOOW CAROLPRENE BLK							
01812R.35.01	8/3C SOOW CAROLPRENE BLK							
02728R.41T.01	10/3C SOOW CAROLPRENE BLK							
02728R.44.01	10/3C SOOW CAROLPRENE BLK							
02462.41T.05	14/3C SOOW CAROLPRENE YLW		0.045	0.535			1.14	13.59
02462.XX.05	14/3C SOOW CAROLPRENE YLW		0.045	0.535			1.14	13.59

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
02462.35.05	14/3C SOOW CAROLPRENE YLW		0.045	0.535			1.14	13.59
02462.35T.05	14/3C SOOW CAROLPRENE YLW		0.045	0.535			1.14	13.59
02762R.44.01	14/3C SOOW CAROLPRENE BLK							
02762R.46.01	14/3C SOOW CAROLPRENE BLK							
02762.41T.01M	14/3C SOOW CAROLPRENE BLK		0.045	0.535			1.14	13.59
02762.44.01M	14/3C SOOW CAROLPRENE BLK		0.045	0.535			1.14	13.59
02762.46.01M	14/3C SOOW CAROLPRENE BLK		0.045	0.535			1.14	13.59
02762.35T.01M	14/3C SOOW CAROLPRENE BLK		0.045	0.535			1.14	13.59
02762.38T.01M	14/3C SOOW CAROLPRENE BLK		0.045	0.535			1.14	13.59
02762.99.01	14/3C SOOW CAROLPRENE BLK		0.045	0.535			1.14	13.59

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
02762.41T.01	14/3C SOOW CAROLPRENE BLK		0.045	0.535			1.14	13.59
02762.44.01	14/3C SOOW CAROLPRENE BLK		0.045	0.535			1.14	13.59
02762.46.01	14/3C SOOW CAROLPRENE BLK		0.045	0.535			1.14	13.59
02762.XX.01	14/3C SOOW CAROLPRENE BLK		0.045	0.535			1.14	13.59
02762.35T.01	14/3C SOOW CAROLPRENE BLK		0.045	0.535			1.14	13.59
02762.38T.01	14/3C SOOW CAROLPRENE BLK		0.045	0.535			1.14	13.59
02762.82.01	14/3C SOOW CAROLPRENE BLK		0.045	0.535			1.14	13.59
02762.85.01	14/3C SOOW CAROLPRENE BLK		0.045	0.535			1.14	13.59
02462.41T.05M	14/3C SOOW CAROLPRENE YLW		0.045	0.535			1.14	13.59
02462.35T.05M	14/3C SOOW CAROLPRENE YLW		0.045	0.535			1.14	13.59

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
02465R.46.05	16/3C SOOW CAROLPRENE YLW							
02768.99.01	14/4C SOOW CAROLPRENE BLK		0.045	0.575			1.14	14.61
02768.41T.01	14/4C SOOW CAROLPRENE BLK		0.045	0.575			1.14	14.61
02768.44.01	14/4C SOOW CAROLPRENE BLK		0.045	0.575			1.14	14.61
02768.46.01	14/4C SOOW CAROLPRENE BLK		0.045	0.575			1.14	14.61
02768.35T.01	14/4C SOOW CAROLPRENE BLK		0.045	0.575			1.14	14.61
02768.38T.01	14/4C SOOW CAROLPRENE BLK		0.045	0.575			1.14	14.61
02768.85.01	14/4C SOOW CAROLPRENE BLK		0.045	0.575			1.14	14.61
02468.41T.05	14/4C SOOW CAROLPRENE YLW		0.045	0.575			1.14	14.61
02468.35T.05	14/4C SOOW CAROLPRENE YLW		0.045	0.575			1.14	14.61

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
02468.41T.05M	14/4C SOOW CAROLPRENE YLW		0.045	0.575			1.14	14.61
02468.35T.05M	14/4C SOOW CAROLPRENE YLW		0.045	0.575			1.14	14.61
02768.41T.01M	14/4C SOOW CAROLPRENE BLK		0.045	0.575			1.14	14.61
02768.44.01M	14/4C SOOW CAROLPRENE BLK		0.045	0.575			1.14	14.61
02768.46.01M	14/4C SOOW CAROLPRENE BLK		0.045	0.575			1.14	14.61
02768.35T.01M	14/4C SOOW CAROLPRENE BLK		0.045	0.575			1.14	14.61
02768.38T.01M	14/4C SOOW CAROLPRENE BLK		0.045	0.575			1.14	14.61

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	01819.99.01	2/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,003	LBS
	01819.41.01	2/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,003	LBS
	01819.XX.01	2/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,003	LBS
	01819.35.01	2/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,003	LBS
	01819.38.01	2/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,003	LBS
	01818.99.01	2/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,248	LBS
	01818.41.01	2/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	1,248	LBS
	01818.44.01	2/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	1,248	LBS
	01818.46.01	2/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	1,248	LBS
	01818.XX.01	2/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,248	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	01818.35.01	2/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	1,248	LBS
	01818.38.01	2/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	1,248	LBS
	16094.99.01	2/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,699	LBS
	16094.41.01	2/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	1,699	LBS
	16094.XX.01	2/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,699	LBS
	16094.35.01	2/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,699	LBS
	16094.40.01	2/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	1,699	LBS
	01818.38.05	2/4C SOOW CAROLPRENE YLW	US	Distribution products	MTO	1,248	LBS
	16094.XX.01M	2/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,699	LBS
	16094.40.01M	2/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,699	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	98187.99.01	2/5C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,684	LBS
	98187.XX.01	2/5C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,684	LBS
	16095.99.01	2/5C SOOW CAROLPRENE BLK	US	Distribution products	MTO	2,066	LBS
	16095.99.01M	2/5C SOOW CAROLPRENE BLK	US	Distribution products	MTO	2,066	LBS
	01823.99.01	4/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	515	LBS
	01823.41.01	4/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	515	LBS
	01823.43.01	4/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	515	LBS
	01823.46.01	4/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	515	LBS
	01823.XX.01	4/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	515	LBS
	01823.35.01	4/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	515	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	16083.XX.01	4/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	926	LBS
	16083.35.01	4/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	926	LBS
	16083.40.01	4/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	926	LBS
	16083.XX.01M	4/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	926	LBS
	01822.99.01	4/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	683	LBS
	01822.41.01	4/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	683	LBS
	01822.46.01	4/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	683	LBS
	01822.XX.01	4/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	683	LBS
	01822.35.01	4/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	683	LBS
	01822.38.01	4/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	683	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	16084.99.01	4/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,145	LBS
	16084.41.01	4/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,145	LBS
	16084.46.01	4/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,145	LBS
	16084.XX.01	4/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,145	LBS
	16084.35.01	4/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,145	LBS
	16084.38.01	4/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	1,145	LBS
	16084.40.01	4/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	1,145	LBS
	01821.99.01	4/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	851	LBS
	01821.41.01	4/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	851	LBS
	01821.44.01	4/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	851	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	01821.46.01	4/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	851	LBS
	01821.XX.01	4/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	851	LBS
	01821.35.01	4/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	851	LBS
	01821.38.01	4/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	851	LBS
	16084.41.01M	4/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	1,145	LBS
	16084.44.01M	4/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,145	LBS
	16084.XX.01M	4/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,145	LBS
	16084.35.01M	4/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,145	LBS
	16084.40.01M	4/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,145	LBS
	98463.99.01	4/5C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,039	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	98463.XX.01	4/5C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,039	LBS
	16085.99.01	4/5C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,419	LBS
	16085.XX.01	4/5C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,419	LBS
	16085.99.01M	4/5C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,419	LBS
	01825.99.01	6/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	482	LBS
	01825.41.01	6/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	482	LBS
	01825.44.01	6/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	482	LBS
	01825.XX.01	6/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	482	LBS
	01825.33.01	6/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	482	LBS
	01825.35.01	6/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	482	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	01825.38.01	6/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	482	LBS
	01825.99.01M	6/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	482	LBS
	01825.41.01M	6/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	482	LBS
	16073.44.01M	6/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	637	LBS
	16073.35.01M	6/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	637	LBS
	16073.40.01M	6/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	637	LBS
	16073.99.01	6/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	637	LBS
	16073.41.01	6/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	637	LBS
	16073.46.01	6/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	637	LBS
	16073.XX.01	6/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	637	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	16073.35.01	6/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	637	LBS
	16073.40.01	6/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	637	LBS
	01824.38.05	6/4C SOOW CAROLPRENE YLW	US	Distribution products	MTO	599	LBS
	01824.38T.05	6/4C SOOW CAROLPRENE YLW	US	Distribution products	MTO	599	LBS
	16074.41.01M	6/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	830	LBS
	16074.44.01M	6/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	830	LBS
	16074.XX.01M	6/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	830	LBS
	16074.35.01M	6/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	830	LBS
	16074.40.01M	6/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	830	LBS
	16074.99.01	6/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	830	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	16074.41.01	6/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	830	LBS
	16074.44.01	6/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	830	LBS
	16074.46.01	6/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	830	LBS
	16074.XX.01	6/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	830	LBS
	16074.35.01	6/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	830	LBS
	16074.38.01	6/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	830	LBS
	16074.40.01	6/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	830	LBS
	01824.99.01	6/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	599	LBS
	01824.41.01	6/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	599	LBS
	01824.44.01	6/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	599	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	01824.46.01	6/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	599	LBS
	01824.XX.01	6/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	599	LBS
	01824.35.01	6/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	599	LBS
	01824.38.01	6/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	599	LBS
	16075.99.01M	6/5C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,015	LBS
	98270.99.01	6/5C SOOW CAROLPRENE BLK	US	Distribution products	MTO	750	LBS
	98270.XX.01	6/5C SOOW CAROLPRENE BLK	US	Distribution products	MTO	750	LBS
	16075.99.01	6/5C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,015	LBS
	16075.41.01	6/5C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,015	LBS
	16075.46.01	6/5C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,015	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	16075.XX.01	6/5C SOOW CAROLPRENE BLK	US	Distribution products	MTO	1,015	LBS
	01811.99.01	8/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	278	LBS
	01811.46.01	8/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	278	LBS
	01811.XX.01	8/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	278	LBS
	01812.99.01	8/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	343	LBS
	01812.41.01	8/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	343	LBS
	01812.44.01	8/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	343	LBS
	01812.XX.01	8/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	343	LBS
	01812.33.01	8/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	343	LBS
	01812.35.01	8/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	343	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	01812.38.01	8/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	343	LBS
	16063.41.01	8/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	450	LBS
	16063.46.01	8/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	450	LBS
	16063.35.01	8/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	450	LBS
	16063.38.01	8/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	450	LBS
	16063.40.01	8/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	450	LBS
	16063.XX.01	8/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	450	LBS
	16063.35.01M	8/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	450	LBS
	16063.38.01M	8/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	450	LBS
	16063.40.01M	8/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	450	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	16064.99.01	8/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	580	LBS
	16064.41.01	8/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	580	LBS
	16064.46.01	8/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	580	LBS
	16064.XX.01	8/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	580	LBS
	16064.35.01	8/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	580	LBS
	16064.40.01	8/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	580	LBS
	01827.38.05	8/4C SOOW CAROLPRENE YLW	US	Distribution products	MTO	442	LBS
	01827.99.01	8/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	442	LBS
	01827.41.01	8/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	442	LBS
	01827.44.01	8/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	442	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	01827.46.01	8/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	442	LBS
	01827.XX.01	8/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	442	LBS
	01827.35.01	8/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	442	LBS
	01827.38.01	8/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	442	LBS
	16064.44.01M	8/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	580	LBS
	16064.XX.01M	8/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	580	LBS
	16064.35.01M	8/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	580	LBS
	16064.40.01M	8/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	580	LBS
	98267.99.01	8/5C SOOW CAROLPRENE BLK	US	Distribution products	MTO	542	LBS
	98267.41.01	8/5C SOOW CAROLPRENE BLK	US	Distribution products	MTS	542	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	98267.XX.01	8/5C SOOW CAROLPRENE BLK	US	Distribution products	MTO	542	LBS
	98267.35.01	8/5C SOOW CAROLPRENE BLK	US	Distribution products	MTS	542	LBS
	16065.99.01M	8/5C SOOW CAROLPRENE BLK	US	Distribution products	MTO	700	LBS
	16065.35.01M	8/5C SOOW CAROLPRENE BLK	US	Distribution products	MTO	700	LBS
	16065.99.01	8/5C SOOW CAROLPRENE BLK	US	Distribution products	MTO	700	LBS
	16065.41.01	8/5C SOOW CAROLPRENE BLK	US	Distribution products	MTS	700	LBS
	16065.35.01	8/5C SOOW CAROLPRENE BLK	US	Distribution products	MTO	700	LBS
	16065.XX.01	8/5C SOOW CAROLPRENE BLK	US	Distribution products	MTO	700	LBS
	02767.41.03M	10/2C SOOW CAROLPRENE RED	US	Distribution products	MTS	230	LBS
	02767.35.03M	10/2C SOOW CAROLPRENE RED	US	Distribution products	MTO	230	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	02767.41.03	10/2C SOOW CAROLPRENE RED	US	Distribution products	MTO	230	LBS
	02767.XX.03	10/2C SOOW CAROLPRENE RED	US	Distribution products	MTO	230	LBS
	02767.35.03	10/2C SOOW CAROLPRENE RED	US	Distribution products	MTO	230	LBS
	02767.41T.01M	10/2C SOOW CAROLPRENE BLK	US	Distribution products	MTS	230	LBS
	02767.46.01M	10/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	230	LBS
	02767.85.01M	10/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	230	LBS
	02767.41T.01	10/2C SOOW CAROLPRENE BLK	US	Distribution products	MTS	230	LBS
	02767.46.01	10/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	230	LBS
	02767.85.01	10/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	230	LBS
	02728.99.01	10/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	289	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	02728.XX.01	10/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	289	LBS
	02728.41T.01	10/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	289	LBS
	02728.44.01	10/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	289	LBS
	02728.46.01	10/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	289	LBS
	02728.35.01	10/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	289	LBS
	02728.35T.01	10/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	289	LBS
	02728.38T.01	10/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	289	LBS
	02728.85.01	10/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	289	LBS
	02428.41T.05M	10/3C SOOW CAROLPRENE YLW	US	Distribution products	MTO	295	LBS
	02428.35T.05M	10/3C SOOW CAROLPRENE YLW	US	Distribution products	MTO	295	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	02428.41T.05	10/3C SOOW CAROLPRENE YLW	US	Distribution products	MTO	295	LBS
	02428.46.05	10/3C SOOW CAROLPRENE YLW	US	Distribution products	MTO	295	LBS
	02428.XX.05	10/3C SOOW CAROLPRENE YLW	US	Distribution products	MTO	295	LBS
	02428.35.05	10/3C SOOW CAROLPRENE YLW	US	Distribution products	MTO	295	LBS
	02428.35T.05	10/3C SOOW CAROLPRENE YLW	US	Distribution products	MTO	295	LBS
	02728.99.01M	10/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	289	LBS
	02728.41T.01M	10/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	289	LBS
	02728.44.01M	10/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	289	LBS
	02728.46.01M	10/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	289	LBS
	02728.35T.01M	10/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	289	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	02728.38T.01M	10/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	289	LBS
	02728.41T.04	10/3C SOOW CAROLPRENE ORG	US	Distribution products	MTO	289	LBS
	02727.99.01M	10/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	351	LBS
	02727.41T.01M	10/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	351	LBS
	02727.44.01M	10/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	351	LBS
	02727.46.01M	10/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	351	LBS
	02727.35T.01M	10/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	351	LBS
	02727.38T.01M	10/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	351	LBS
	02727.99.01	10/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	351	LBS
	02727.41T.01	10/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	351	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	02727.44.01	10/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	351	LBS
	02727.46.01	10/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	351	LBS
	02727.XX.01	10/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	351	LBS
	02727.35T.01	10/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	351	LBS
	02727.38T.01	10/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	351	LBS
	02727.85.01	10/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	351	LBS
	02427.41T.05M	10/4C SOOW CAROLPRENE YLW	US	Distribution products	MTO	353	LBS
	02427.35.05M	10/4C SOOW CAROLPRENE YLW	US	Distribution products	MTO	353	LBS
	02427.35T.05M	10/4C SOOW CAROLPRENE YLW	US	Distribution products	MTO	353	LBS
	02427.99.05	10/4C SOOW CAROLPRENE YLW	US	Distribution products	MTO	353	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	02427.41T.05	10/4C SOOW CAROLPRENE YLW	US	Distribution products	MTS	353	LBS
	02427.XX.05	10/4C SOOW CAROLPRENE YLW	US	Distribution products	MTO	353	LBS
	02427.35.05	10/4C SOOW CAROLPRENE YLW	US	Distribution products	MTO	353	LBS
	02427.35T.05	10/4C SOOW CAROLPRENE YLW	US	Distribution products	MTS	353	LBS
	02724.41T.01M	12/2C SOOW CAROLPRENE BLK	US	Distribution products	MTS	168	LBS
	02724.46.01M	12/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	168	LBS
	02724.85.01M	12/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	168	LBS
	02724.41.03	12/2C SOOW CAROLPRENE RED	US	Distribution products	MTO	168	LBS
	02724.46.03	12/2C SOOW CAROLPRENE RED	US	Distribution products	MTO	168	LBS
	02724.35.03	12/2C SOOW CAROLPRENE RED	US	Distribution products	MTO	168	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	02724.41.03M	12/2C SOOW CAROLPRENE RED	US	Distribution products	MTS	168	LBS
	02724.46.03M	12/2C SOOW CAROLPRENE RED	US	Distribution products	MTO	168	LBS
	02724.35.03M	12/2C SOOW CAROLPRENE RED	US	Distribution products	MTS	168	LBS
	02724.41T.01	12/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	168	LBS
	02724.46.01	12/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	168	LBS
	02724.L2.01	12/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	168	LBS
	02724.38.01	12/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	168	LBS
	02724.85.01	12/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	168	LBS
	02725.99.01M	12/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	223	LBS
	02725.41T.01M	12/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	223	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	02725.44.01M	12/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	223	LBS
	02725.46.01M	12/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	223	LBS
	02725.35T.01M	12/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	223	LBS
	02725.38T.01M	12/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	223	LBS
	02725.41T.04	12/3C SOOW CAROLPRENE ORG	US	Distribution products	MTO	223	LBS
	02725.XX.04	12/3C SOOW CAROLPRENE ORG	US	Distribution products	MTO	223	LBS
	02725.35.04	12/3C SOOW CAROLPRENE ORG	US	Distribution products	MTO	223	LBS
	02425.41T.05	12/3C SOOW CAROLPRENE YLW	US	Distribution products	MTS	229	LBS
	02425.XX.05	12/3C SOOW CAROLPRENE YLW	US	Distribution products	MTO	229	LBS
	02425.35.05	12/3C SOOW CAROLPRENE YLW	US	Distribution products	MTO	229	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	02425.35T.05	12/3C SOOW CAROLPRENE YLW	US	Distribution products	MTS	229	LBS
	02425.41T.05M	12/3C SOOW CAROLPRENE YLW	US	Distribution products	MTO	229	LBS
	02425.35T.05M	12/3C SOOW CAROLPRENE YLW	US	Distribution products	MTO	229	LBS
	02725.99.01	12/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	223	LBS
	02725.41T.01	12/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	223	LBS
	02725.44.01	12/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	223	LBS
	02725.46.01	12/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	223	LBS
	02725.XX.01	12/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	223	LBS
	02725.35.01	12/3C SOOW CAROLPRENE BLK	US	Distribution products		223	LBS
	02725.35T.01	12/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	223	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	02725.38T.01	12/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	223	LBS
	02725.82.01	12/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	223	LBS
	02725.85.01	12/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	223	LBS
	02426.99.05	12/4C SOOW CAROLPRENE YLW	US	Distribution products	MTO	280	LBS
	02426.41T.05	12/4C SOOW CAROLPRENE YLW	US	Distribution products	MTS	280	LBS
	02426.XX.05	12/4C SOOW CAROLPRENE YLW	US	Distribution products	MTO	280	LBS
	02426.35T.05	12/4C SOOW CAROLPRENE YLW	US	Distribution products	MTS	280	LBS
	02426.41T.05M	12/4C SOOW CAROLPRENE YLW	US	Distribution products	MTO	280	LBS
	02426.35T.05M	12/4C SOOW CAROLPRENE YLW	US	Distribution products	MTO	280	LBS
	02726.99.01	12/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	276	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	02726.41T.01	12/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	276	LBS
	02726.44.01	12/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	276	LBS
	02726.46.01	12/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	276	LBS
	02726.XX.01	12/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	276	LBS
	02726.35.01	12/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	276	LBS
	02726.35T.01	12/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	276	LBS
	02726.38T.01	12/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	276	LBS
	02726.85.01	12/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	276	LBS
	02726.41T.01M	12/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	276	LBS
	02726.44.01M	12/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	276	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	02726.46.01M	12/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	276	LBS
	02726.XX.01M	12/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	276	LBS
	02726.35T.01M	12/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	276	LBS
	02726.38T.01M	12/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	276	LBS
	02722.41T.01M	16/2C SOOW CAROLPRENE BLK	US	Distribution products	MTS	77	LBS
	02722.46.01M	16/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	77	LBS
	02722.35.01M	16/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	77	LBS
	02722.35T.01M	16/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	77	LBS
	02722.99.01	16/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	77	LBS
	02722.41T.01	16/2C SOOW CAROLPRENE BLK	US	Distribution products	MTS	77	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	02722.44.01	16/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	77	LBS
	02722.46.01	16/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	77	LBS
	02722.35.01	16/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	77	LBS
	02722.35T.01	16/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	77	LBS
	02465.41T.05M	16/3C SOOW CAROLPRENE YLW	US	Distribution products	MTS	103	LBS
	02465.35T.05M	16/3C SOOW CAROLPRENE YLW	US	Distribution products	MTS	103	LBS
	02765.99.01	16/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	94	LBS
	02765.41T.01	16/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	94	LBS
	02765.44.01	16/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	94	LBS
	02765.46.01	16/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	94	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	02765.XX.01	16/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	94	LBS
	02765.35.01	16/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	94	LBS
	02765.35T.01	16/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	94	LBS
	02765.38T.01	16/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	94	LBS
	02765.82.01	16/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	94	LBS
	02465.41T.05	16/3C SOOW CAROLPRENE YLW	US	Distribution products	MTS	103	LBS
	02465.XX.05	16/3C SOOW CAROLPRENE YLW	US	Distribution products	MTO	103	LBS
	02465.35T.05	16/3C SOOW CAROLPRENE YLW	US	Distribution products	MTS	103	LBS
	02765.99.01M	16/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	94	LBS
	02765.41T.01M	16/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	94	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	02765.44.01M	16/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	94	LBS
	02765.46.01M	16/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	94	LBS
	02765.35T.01M	16/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	94	LBS
	02765.38T.01M	16/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	94	LBS
	02466.41T.05	16/4C SOOW CAROLPRENE YLW	US	Distribution products	MTO	119	LBS
	02466.XX.05	16/4C SOOW CAROLPRENE YLW	US	Distribution products	MTO	119	LBS
	02466.35T.05	16/4C SOOW CAROLPRENE YLW	US	Distribution products	MTS	119	LBS
	02766.99.01	16/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	114	LBS
	02766.41.01	16/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	114	LBS
	02766.41T.01	16/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	114	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	02766.44.01	16/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	114	LBS
	02766.46.01	16/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	114	LBS
	02766.35T.01	16/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	114	LBS
	02766.38T.01	16/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	114	LBS
	02766.41T.01M	16/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	114	LBS
	02766.44.01M	16/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	114	LBS
	02766.46.01M	16/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	114	LBS
	02766.35T.01M	16/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	114	LBS
	02766.38T.01M	16/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	114	LBS
	02466.41T.05M	16/4C SOOW CAROLPRENE YLW	US	Distribution products	MTO	119	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	02466.35T.05M	16/4C SOOW CAROLPRENE YLW	US	Distribution products	MTO	119	LBS
	02757.41.01	16/5C SOOW CAROLPRENE BLK	US	Distribution products	MTO		LBS
	02763.41T.01M	18/2C SOOW CAROLPRENE BLK	US	Distribution products	MTS	65	LBS
	02763.35.01M	18/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	65	LBS
	02763.35T.01M	18/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	65	LBS
	02763.99.01	18/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	65	LBS
	02763.41T.01	18/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	65	LBS
	02763.44.01	18/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	65	LBS
	02763.46.01	18/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	65	LBS
	02763.35.01	18/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	65	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	02763.35T.01	18/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	65	LBS
	02469.41T.05	18/3C SOOW CAROLPRENE YLW	US	Distribution products	MTO	84	LBS
	02469.XX.05	18/3C SOOW CAROLPRENE YLW	US	Distribution products	MTO	84	LBS
	02469.35T.05	18/3C SOOW CAROLPRENE YLW	US	Distribution products	MTS	84	LBS
	02769.99.01M	18/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	80	LBS
	02769.41T.01M	18/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	80	LBS
	02769.46.01M	18/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	80	LBS
	02769.35T.01M	18/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	80	LBS
	02769.38.01M	18/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	80	LBS
	02469.35T.05M	18/3C SOOW CAROLPRENE YLW	US	Distribution products	MTO	84	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	02769.99.01	18/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	80	LBS
	02769.41T.01	18/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	80	LBS
	02769.44.01	18/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	80	LBS
	02769.46.01	18/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	80	LBS
	02769.35.01	18/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	80	LBS
	02769.35T.01	18/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	80	LBS
	02769.38.01	18/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	80	LBS
	02770.99.01M	18/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	94	LBS
	02770.41T.01M	18/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	94	LBS
	02770.46.01M	18/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	94	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	02770.35.01M	18/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	94	LBS
	02770.35T.01M	18/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	94	LBS
	02770.99.01	18/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	94	LBS
	02770.41T.01	18/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	94	LBS
	02770.46.01	18/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	94	LBS
	02770.44.01	18/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	94	LBS
	02770.35.01	18/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	94	LBS
	02770.35T.01	18/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	94	LBS
	02770.38.01	18/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	94	LBS
	02470.35T.05	18/4C SOOW CAROLPRENE YLW	US	Distribution products	MTO	101	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	02723.41T.01M	14/2C SOOW CAROLPRENE BLK	US	Distribution products	MTS	154	LBS
	02723.46.01M	14/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	154	LBS
	02723.38T.01M	14/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	154	LBS
	02723.85.01M	14/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	154	LBS
	02723.41T.03	14/2C SOOW CAROLPRENE RED	US	Distribution products	MTO	154	LBS
	02723.41T.03M	14/2C SOOW CAROLPRENE RED	US	Distribution products	MTO	154	LBS
	02723.XX.01	14/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	154	LBS
	02723.41T.01	14/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	154	LBS
	02723.44.01	14/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	154	LBS
	02723.46.01	14/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	154	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	02723.38T.01	14/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	154	LBS
	02723.85.01	14/2C SOOW CAROLPRENE BLK	US	Distribution products	MTO	154	LBS
	02765R.44.01	16/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO		LBS
	02765R.46.01	16/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO		LBS
	02769R.46.01	18/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO		LBS
	01812R.35.01	8/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO		LBS
	02728R.41T.01	10/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO		LBS
	02728R.44.01	10/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO		LBS
	02462.41T.05	14/3C SOOW CAROLPRENE YLW	US	Distribution products	MTS	172	LBS
	02462.XX.05	14/3C SOOW CAROLPRENE YLW	US	Distribution products	MTO	172	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	02462.35.05	14/3C SOOW CAROLPRENE YLW	US	Distribution products	MTO	172	LBS
	02462.35T.05	14/3C SOOW CAROLPRENE YLW	US	Distribution products	MTS	172	LBS
	02762R.44.01	14/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO		LBS
	02762R.46.01	14/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO		LBS
	02762.41T.01M	14/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	171	LBS
	02762.44.01M	14/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	171	LBS
	02762.46.01M	14/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	171	LBS
	02762.35T.01M	14/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	171	LBS
	02762.38T.01M	14/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	171	LBS
	02762.99.01	14/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	171	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	02762.41T.01	14/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	171	LBS
	02762.44.01	14/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	171	LBS
	02762.46.01	14/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	171	LBS
	02762.XX.01	14/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	171	LBS
	02762.35T.01	14/3C SOOW CAROLPRENE BLK	US	Distribution products	MTS	171	LBS
	02762.38T.01	14/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	171	LBS
	02762.82.01	14/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	171	LBS
	02762.85.01	14/3C SOOW CAROLPRENE BLK	US	Distribution products	MTO	171	LBS
	02462.41T.05M	14/3C SOOW CAROLPRENE YLW	US	Distribution products	MTO	172	LBS
	02462.35T.05M	14/3C SOOW CAROLPRENE YLW	US	Distribution products	MTO	172	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	02465R.46.05	16/3C SOOW CAROLPRENE YLW	US	Distribution products	MTO		LBS
	02768.99.01	14/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	209	LBS
	02768.41T.01	14/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	209	LBS
	02768.44.01	14/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	209	LBS
	02768.46.01	14/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	209	LBS
	02768.35T.01	14/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	209	LBS
	02768.38T.01	14/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	209	LBS
	02768.85.01	14/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	209	LBS
	02468.41T.05	14/4C SOOW CAROLPRENE YLW	US	Distribution products	MTS	208	LBS
	02468.35T.05	14/4C SOOW CAROLPRENE YLW	US	Distribution products	MTS	208	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	02468.41T.05M	14/4C SOOW CAROLPRENE YLW	US	Distribution products	MTO	208	LBS
	02468.35T.05M	14/4C SOOW CAROLPRENE YLW	US	Distribution products	MTO	208	LBS
	02768.41T.01M	14/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	209	LBS
	02768.44.01M	14/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	209	LBS
	02768.46.01M	14/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	209	LBS
	02768.35T.01M	14/4C SOOW CAROLPRENE BLK	US	Distribution products	MTS	209	LBS
	02768.38T.01M	14/4C SOOW CAROLPRENE BLK	US	Distribution products	MTO	209	LBS

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
01819.99.01	2/3C SOOW CAROLPRENE BLK	FOOT	16	16	19	Factory Reel
01819.41.01	2/3C SOOW CAROLPRENE BLK	FOOT	36	25	36	1000 FT Reel
01819.XX.01	2/3C SOOW CAROLPRENE BLK	FOOT	24	22	24	Various Lengths
01819.35.01	2/3C SOOW CAROLPRENE BLK	FOOT	24	22	24	250 FT Reel
01819.38.01	2/3C SOOW CAROLPRENE BLK	FOOT	34	20	34	500 FT Reel
01818.99.01	2/4C SOOW CAROLPRENE BLK	FOOT	48	42	48	Factory Reel
01818.41.01	2/4C SOOW CAROLPRENE BLK	FOOT	42	28	42	1000 FT Reel
01818.44.01	2/4C SOOW CAROLPRENE BLK	FOOT	48	42	48	2500 FT Reel
01818.46.01	2/4C SOOW CAROLPRENE BLK	FOOT	48	42	48	5000 FT Reel
01818.XX.01	2/4C SOOW CAROLPRENE BLK	FOOT	24	22	24	Various Lengths

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
01818.35.01	2/4C SOOW CAROLPRENE BLK	FOOT	24	22	24	250 FT Reel
01818.38.01	2/4C SOOW CAROLPRENE BLK	FOOT	32	26	32	500 FT Reel
16094.99.01	2/4C SOOW CAROLPRENE BLK	FOOT	48	34	48	Factory Reel
16094.41.01	2/4C SOOW CAROLPRENE BLK	FOOT	48	34	48	1000 FT Reel
16094.XX.01	2/4C SOOW CAROLPRENE BLK	FOOT	30	22	30	Various Lengths
16094.35.01	2/4C SOOW CAROLPRENE BLK	FOOT	32	26	32	250 FT Reel
16094.40.01	2/4C SOOW CAROLPRENE BLK	FOOT	48	34	48	Long Length Reel
01818.38.05	2/4C SOOW CAROLPRENE YLW	FOOT	32	26	32	500 FT Reel
16094.XX.01M	2/4C SOOW CAROLPRENE BLK	FOOT	48	42	1	Various Lengths
16094.40.01M	2/4C SOOW CAROLPRENE BLK	FOOT	16	16	19	Long Length Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
98187.99.01	2/5C SOOW CAROLPRENE BLK	FOOT	48	42	48	Factory Reel
98187.XX.01	2/5C SOOW CAROLPRENE BLK	FOOT	27	22	27	Various Lengths
16095.99.01	2/5C SOOW CAROLPRENE BLK	FOOT	48	34	48	Factory Reel
16095.99.01M	2/5C SOOW CAROLPRENE BLK	FOOT	16	16	19	Factory Reel
01823.99.01	4/2C SOOW CAROLPRENE BLK	FOOT	48	34	48	Factory Reel
01823.41.01	4/2C SOOW CAROLPRENE BLK	FOOT	36	25	36	1000 FT Reel
01823.43.01	4/2C SOOW CAROLPRENE BLK	FOOT	36	25	36	2000 FT Reel
01823.46.01	4/2C SOOW CAROLPRENE BLK	FOOT	48	34	48	5000 FT Reel
01823.XX.01	4/2C SOOW CAROLPRENE BLK	FOOT	36	25	36	Various Lengths
01823.35.01	4/2C SOOW CAROLPRENE BLK	FOOT	24	22	24	250 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
16083.XX.01	4/3C SOOW CAROLPRENE BLK	FOOT	24	22	24	Various Lengths
16083.35.01	4/3C SOOW CAROLPRENE BLK	FOOT	24	22	24	250 FT Reel
16083.40.01	4/3C SOOW CAROLPRENE BLK	FOOT	58	38	58	Long Length Reel
16083.XX.01M	4/3C SOOW CAROLPRENE BLK	FOOT	48	42	1	Various Lengths
01822.99.01	4/3C SOOW CAROLPRENE BLK	FOOT	16	16	19	Factory Reel
01822.41.01	4/3C SOOW CAROLPRENE BLK	FOOT	32	26	32	1000 FT Reel
01822.46.01	4/3C SOOW CAROLPRENE BLK	FOOT	16	16	19	5000 FT Reel
01822.XX.01	4/3C SOOW CAROLPRENE BLK	FOOT	24	22	24	Various Lengths
01822.35.01	4/3C SOOW CAROLPRENE BLK	FOOT	24	22	24	250 FT Reel
01822.38.01	4/3C SOOW CAROLPRENE BLK	FOOT	27	22	27	500 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
16084.99.01	4/4C SOOW CAROLPRENE BLK	FOOT	48	34	48	Factory Reel
16084.41.01	4/4C SOOW CAROLPRENE BLK	FOOT	48	34	48	1000 FT Reel
16084.46.01	4/4C SOOW CAROLPRENE BLK	FOOT	58	38	58	5000 FT Reel
16084.XX.01	4/4C SOOW CAROLPRENE BLK	FOOT	27	22	27	Various Lengths
16084.35.01	4/4C SOOW CAROLPRENE BLK	FOOT	27	22	27	250 FT Reel
16084.38.01	4/4C SOOW CAROLPRENE BLK	FOOT	27	22	27	500 FT Reel
16084.40.01	4/4C SOOW CAROLPRENE BLK	FOOT	48	34	48	Long Length Reel
01821.99.01	4/4C SOOW CAROLPRENE BLK	FOOT	48	42	48	Factory Reel
01821.41.01	4/4C SOOW CAROLPRENE BLK	FOOT	36	25	36	1000 FT Reel
01821.44.01	4/4C SOOW CAROLPRENE BLK	FOOT	48	34	48	2500 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
01821.46.01	4/4C SOOW CAROLPRENE BLK	FOOT	48	34	48	5000 FT Reel
01821.XX.01	4/4C SOOW CAROLPRENE BLK	FOOT	27	22	27	Various Lengths
01821.35.01	4/4C SOOW CAROLPRENE BLK	FOOT	24	22	24	250 FT Reel
01821.38.01	4/4C SOOW CAROLPRENE BLK	FOOT	30	22	30	500 FT Reel
16084.41.01M	4/4C SOOW CAROLPRENE BLK	FOOT	22	20	1	1000 FT Reel
16084.44.01M	4/4C SOOW CAROLPRENE BLK	FOOT	48	42	1	2500 FT Reel
16084.XX.01M	4/4C SOOW CAROLPRENE BLK	FOOT	48	42	1	Various Lengths
16084.35.01M	4/4C SOOW CAROLPRENE BLK	FOOT	22	20	1	250 FT Reel
16084.40.01M	4/4C SOOW CAROLPRENE BLK	FOOT	16	16	19	Long Length Reel
98463.99.01	4/5C SOOW CAROLPRENE BLK	FOOT	48	42	1	Factory Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
98463.XX.01	4/5C SOOW CAROLPRENE BLK	FOOT	24	22	24	Various Lengths
16085.99.01	4/5C SOOW CAROLPRENE BLK	FOOT	58	38	58	Factory Reel
16085.XX.01	4/5C SOOW CAROLPRENE BLK	FOOT	30	22	30	Various Lengths
16085.99.01M	4/5C SOOW CAROLPRENE BLK	FOOT	48	42	1	Factory Reel
01825.99.01	6/3C SOOW CAROLPRENE BLK	FOOT	48	42	1	Factory Reel
01825.41.01	6/3C SOOW CAROLPRENE BLK	FOOT	30	22	30	1000 FT Reel
01825.44.01	6/3C SOOW CAROLPRENE BLK	FOOT	42	29	42	2500 FT Reel
01825.XX.01	6/3C SOOW CAROLPRENE BLK	FOOT	20	13	20	Various Lengths
01825.33.01	6/3C SOOW CAROLPRENE BLK	FOOT	12	13	12	100 FT Reel
01825.35.01	6/3C SOOW CAROLPRENE BLK	FOOT	18	13	18	250 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
01825.38.01	6/3C SOOW CAROLPRENE BLK	FOOT	24	22	24	500 FT Reel
01825.99.01M	6/3C SOOW CAROLPRENE BLK	FOOT	48	42	1	Factory Reel
01825.41.01M	6/3C SOOW CAROLPRENE BLK	FOOT	34	34	26	1000 FT Reel
16073.44.01M	6/3C SOOW CAROLPRENE BLK	FOOT	58	38	58	2500 FT Reel
16073.35.01M	6/3C SOOW CAROLPRENE BLK	FOOT	24	22	24	250 FT Reel
16073.40.01M	6/3C SOOW CAROLPRENE BLK	FOOT	48	42	1	Long Length Reel
16073.99.01	6/3C SOOW CAROLPRENE BLK	FOOT	36	25	36	Factory Reel
16073.41.01	6/3C SOOW CAROLPRENE BLK	FOOT	36	25	36	1000 FT Reel
16073.46.01	6/3C SOOW CAROLPRENE BLK	FOOT	58	38	58	5000 FT Reel
16073.XX.01	6/3C SOOW CAROLPRENE BLK	FOOT	24	22	24	Various Lengths

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
16073.35.01	6/3C SOOW CAROLPRENE BLK	FOOT	24	22	24	250 FT Reel
16073.40.01	6/3C SOOW CAROLPRENE BLK	FOOT	58	38	58	Long Length Reel
01824.38.05	6/4C SOOW CAROLPRENE YLW	FOOT	24	22	24	500 FT Reel
01824.38T.05	6/4C SOOW CAROLPRENE YLW	FOOT	24	22	24	500 FT Reel
16074.41.01M	6/4C SOOW CAROLPRENE BLK	FOOT	36	25	36	1000 FT Reel
16074.44.01M	6/4C SOOW CAROLPRENE BLK	FOOT	22	20	1	2500 FT Reel
16074.XX.01M	6/4C SOOW CAROLPRENE BLK	FOOT	16	16	19	Various Lengths
16074.35.01M	6/4C SOOW CAROLPRENE BLK	FOOT	30	30	28	250 FT Reel
16074.40.01M	6/4C SOOW CAROLPRENE BLK	FOOT	58	38	58	Long Length Reel
16074.99.01	6/4C SOOW CAROLPRENE BLK	FOOT	36	25	36	Factory Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
16074.41.01	6/4C SOOW CAROLPRENE BLK	FOOT	36	25	36	1000 FT Reel
16074.44.01	6/4C SOOW CAROLPRENE BLK	FOOT	58	38	58	2500 FT Reel
16074.46.01	6/4C SOOW CAROLPRENE BLK	FOOT	36	25	36	5000 FT Reel
16074.XX.01	6/4C SOOW CAROLPRENE BLK	FOOT	24	22	24	Various Lengths
16074.35.01	6/4C SOOW CAROLPRENE BLK	FOOT	24	22	24	250 FT Reel
16074.38.01	6/4C SOOW CAROLPRENE BLK	FOOT	22	20	1	500 FT Reel
16074.40.01	6/4C SOOW CAROLPRENE BLK	FOOT	58	38	58	Long Length Reel
01824.99.01	6/4C SOOW CAROLPRENE BLK	FOOT	48	42	48	Factory Reel
01824.41.01	6/4C SOOW CAROLPRENE BLK	FOOT	32	26	32	1000 FT Reel
01824.44.01	6/4C SOOW CAROLPRENE BLK	FOOT	48	34	48	2500 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
01824.46.01	6/4C SOOW CAROLPRENE BLK	FOOT	58	38	58	5000 FT Reel
01824.XX.01	6/4C SOOW CAROLPRENE BLK	FOOT	20	20	20	Various Lengths
01824.35.01	6/4C SOOW CAROLPRENE BLK	FOOT	20	20	20	250 FT Reel
01824.38.01	6/4C SOOW CAROLPRENE BLK	FOOT	24	22	24	500 FT Reel
16075.99.01M	6/5C SOOW CAROLPRENE BLK	FOOT	48	42	1	Factory Reel
98270.99.01	6/5C SOOW CAROLPRENE BLK	FOOT	48	42	48	Factory Reel
98270.XX.01	6/5C SOOW CAROLPRENE BLK	FOOT	20	20	20	Various Lengths
16075.99.01	6/5C SOOW CAROLPRENE BLK	FOOT	48	42	48	Factory Reel
16075.41.01	6/5C SOOW CAROLPRENE BLK	FOOT	42	28	42	1000 FT Reel
16075.46.01	6/5C SOOW CAROLPRENE BLK	FOOT	58	38	58	5000 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
16075.XX.01	6/5C SOOW CAROLPRENE BLK	FOOT	24	22	24	Various Lengths
01811.99.01	8/2C SOOW CAROLPRENE BLK	FOOT	16	16	19	Factory Reel
01811.46.01	8/2C SOOW CAROLPRENE BLK	FOOT	42	29	42	5000 FT Reel
01811.XX.01	8/2C SOOW CAROLPRENE BLK	FOOT	16	16	19	Various Lengths
01812.99.01	8/3C SOOW CAROLPRENE BLK	FOOT	48	34	48	Factory Reel
01812.41.01	8/3C SOOW CAROLPRENE BLK	FOOT	27	22	27	1000 FT Reel
01812.44.01	8/3C SOOW CAROLPRENE BLK	FOOT	42	29	42	2500 FT Reel
01812.XX.01	8/3C SOOW CAROLPRENE BLK	FOOT	16	13	16	Various Lengths
01812.33.01	8/3C SOOW CAROLPRENE BLK	FOOT	12	13	12	100 FT Reel
01812.35.01	8/3C SOOW CAROLPRENE BLK	FOOT	16	13	16	250 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
01812.38.01	8/3C SOOW CAROLPRENE BLK	FOOT	20	20	20	500 FT Reel
16063.41.01	8/3C SOOW CAROLPRENE BLK	FOOT	32	26	32	1000 FT Reel
16063.46.01	8/3C SOOW CAROLPRENE BLK	FOOT	32	26	32	5000 FT Reel
16063.35.01	8/3C SOOW CAROLPRENE BLK	FOOT	20	13	20	250 FT Reel
16063.38.01	8/3C SOOW CAROLPRENE BLK	FOOT	24	22	24	500 FT Reel
16063.40.01	8/3C SOOW CAROLPRENE BLK	FOOT	48	42	42	Long Length Reel
16063.XX.01	8/3C SOOW CAROLPRENE BLK	FOOT	16	16	19	Various Lengths
16063.35.01M	8/3C SOOW CAROLPRENE BLK	FOOT	22	20	1	250 FT Reel
16063.38.01M	8/3C SOOW CAROLPRENE BLK	FOOT	22	20	1	500 FT Reel
16063.40.01M	8/3C SOOW CAROLPRENE BLK	FOOT	48	42	1	Long Length Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
16064.99.01	8/4C SOOW CAROLPRENE BLK	FOOT	36	25	36	Factory Reel
16064.41.01	8/4C SOOW CAROLPRENE BLK	FOOT	36	25	36	1000 FT Reel
16064.46.01	8/4C SOOW CAROLPRENE BLK	FOOT	36	25	36	5000 FT Reel
16064.XX.01	8/4C SOOW CAROLPRENE BLK	FOOT	20	20	20	Various Lengths
16064.35.01	8/4C SOOW CAROLPRENE BLK	FOOT	20	20	20	250 FT Reel
16064.40.01	8/4C SOOW CAROLPRENE BLK	FOOT	48	48	42	Long Length Reel
01827.38.05	8/4C SOOW CAROLPRENE YLW	FOOT	22	20	1	500 FT Reel
01827.99.01	8/4C SOOW CAROLPRENE BLK	FOOT	16	16	19	Factory Reel
01827.41.01	8/4C SOOW CAROLPRENE BLK	FOOT	30	22	30	1000 FT Reel
01827.44.01	8/4C SOOW CAROLPRENE BLK	FOOT	42	29	42	2500 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
01827.46.01	8/4C SOOW CAROLPRENE BLK	FOOT	58	38	58	5000 FT Reel
01827.XX.01	8/4C SOOW CAROLPRENE BLK	FOOT	20	13	20	Various Lengths
01827.35.01	8/4C SOOW CAROLPRENE BLK	FOOT	18	13	18	250 FT Reel
01827.38.01	8/4C SOOW CAROLPRENE BLK	FOOT	24	22	24	500 FT Reel
16064.44.01M	8/4C SOOW CAROLPRENE BLK	FOOT	48	48	42	2500 FT Reel
16064.XX.01M	8/4C SOOW CAROLPRENE BLK	FOOT	16	16	19	Various Lengths
16064.35.01M	8/4C SOOW CAROLPRENE BLK	FOOT	20	20	20	250 FT Reel
16064.40.01M	8/4C SOOW CAROLPRENE BLK	FOOT	48	48	42	Long Length Reel
98267.99.01	8/5C SOOW CAROLPRENE BLK	FOOT	48	42	1	Factory Reel
98267.41.01	8/5C SOOW CAROLPRENE BLK	FOOT	30	22	30	1000 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
98267.XX.01	8/5C SOOW CAROLPRENE BLK	FOOT	20	13	20	Various Lengths
98267.35.01	8/5C SOOW CAROLPRENE BLK	FOOT	20	13	20	250 FT Reel
16065.99.01M	8/5C SOOW CAROLPRENE BLK	FOOT	48	42	1	Factory Reel
16065.35.01M	8/5C SOOW CAROLPRENE BLK	FOOT	22	20	1	250 FT Reel
16065.99.01	8/5C SOOW CAROLPRENE BLK	FOOT	48	42	48	Factory Reel
16065.41.01	8/5C SOOW CAROLPRENE BLK	FOOT	36	25	36	1000 FT Reel
16065.35.01	8/5C SOOW CAROLPRENE BLK	FOOT	24	22	24	250 FT Reel
16065.XX.01	8/5C SOOW CAROLPRENE BLK	FOOT	48	42	48	Various Lengths
02767.41.03M	10/2C SOOW CAROLPRENE RED	FOOT	22	20	1	1000 FT Reel
02767.35.03M	10/2C SOOW CAROLPRENE RED	FOOT	22	20	1	250 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
02767.41.03	10/2C SOOW CAROLPRENE RED	FOOT	24	22	24	1000 FT Reel
02767.XX.03	10/2C SOOW CAROLPRENE RED	FOOT	24	22	24	Various Lengths
02767.35.03	10/2C SOOW CAROLPRENE RED	FOOT	24	22	24	250 FT Reel
02767.41T.01M	10/2C SOOW CAROLPRENE BLK	FOOT	24	22	24	1000 FT Reel
02767.46.01M	10/2C SOOW CAROLPRENE BLK	FOOT	22	20	1	5000 FT Reel
02767.85.01M	10/2C SOOW CAROLPRENE BLK	FOOT	21	21	6	250 FT Coil
02767.41T.01	10/2C SOOW CAROLPRENE BLK	FOOT	24	22	24	1000 FT Reel
02767.46.01	10/2C SOOW CAROLPRENE BLK	FOOT	48	34	48	5000 FT Reel
02767.85.01	10/2C SOOW CAROLPRENE BLK	FOOT	20	21	14	250 FT Coil
02728.99.01	10/3C SOOW CAROLPRENE BLK	FOOT	48	42	48	Factory Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
02728.XX.01	10/3C SOOW CAROLPRENE BLK	FOOT	48	40	1	Various Lengths
02728.41T.01	10/3C SOOW CAROLPRENE BLK	FOOT	24	22	24	1000 FT Reel
02728.44.01	10/3C SOOW CAROLPRENE BLK	FOOT	36	25	36	2500 FT Reel
02728.46.01	10/3C SOOW CAROLPRENE BLK	FOOT	48	34	48	5000 FT Reel
02728.35.01	10/3C SOOW CAROLPRENE BLK	FOOT	16	13	16	250 FT Reel
02728.35T.01	10/3C SOOW CAROLPRENE BLK	FOOT	16	13	16	250 FT Reel
02728.38T.01	10/3C SOOW CAROLPRENE BLK	FOOT	20	20	16	500 FT Reel
02728.85.01	10/3C SOOW CAROLPRENE BLK	FOOT	20	21	7	250 FT Coil
02428.41T.05M	10/3C SOOW CAROLPRENE YLW	FOOT	22	20	1	1000 FT Reel
02428.35T.05M	10/3C SOOW CAROLPRENE YLW	FOOT	22	20	1	250 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
02428.41T.05	10/3C SOOW CAROLPRENE YLW	FOOT	22	20	22	1000 FT Reel
02428.46.05	10/3C SOOW CAROLPRENE YLW	FOOT	22	20	1	5000 FT Reel
02428.XX.05	10/3C SOOW CAROLPRENE YLW	FOOT	48	42	1	Various Lengths
02428.35.05	10/3C SOOW CAROLPRENE YLW	FOOT	14	14	12	250 FT Reel
02428.35T.05	10/3C SOOW CAROLPRENE YLW	FOOT	14	14	12	250 FT Reel
02728.99.01M	10/3C SOOW CAROLPRENE BLK	FOOT	48	42	1	Factory Reel
02728.41T.01M	10/3C SOOW CAROLPRENE BLK	FOOT	24	22	24	1000 FT Reel
02728.44.01M	10/3C SOOW CAROLPRENE BLK	FOOT	36	36	28	2500 FT Reel
02728.46.01M	10/3C SOOW CAROLPRENE BLK	FOOT	48	34	48	5000 FT Reel
02728.35T.01M	10/3C SOOW CAROLPRENE BLK	FOOT	16	13	16	250 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
02728.38T.01M	10/3C SOOW CAROLPRENE BLK	FOOT	22	20	1	500 FT Reel
02728.41T.04	10/3C SOOW CAROLPRENE ORG	FOOT	24	22	24	1000 FT Reel
02727.99.01M	10/4C SOOW CAROLPRENE BLK	FOOT	48	42	1	Factory Reel
02727.41T.01M	10/4C SOOW CAROLPRENE BLK	FOOT	27	22	18	1000 FT Reel
02727.44.01M	10/4C SOOW CAROLPRENE BLK	FOOT	36	36	28	2500 FT Reel
02727.46.01M	10/4C SOOW CAROLPRENE BLK	FOOT	48	34	48	5000 FT Reel
02727.35T.01M	10/4C SOOW CAROLPRENE BLK	FOOT	16	13	16	250 FT Reel
02727.38T.01M	10/4C SOOW CAROLPRENE BLK	FOOT	22	20	1	500 FT Reel
02727.99.01	10/4C SOOW CAROLPRENE BLK	FOOT	48	42	48	Factory Reel
02727.41T.01	10/4C SOOW CAROLPRENE BLK	FOOT	27	22	18	1000 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
02727.44.01	10/4C SOOW CAROLPRENE BLK	FOOT	36	25	36	2500 FT Reel
02727.46.01	10/4C SOOW CAROLPRENE BLK	FOOT	48	34	48	5000 FT Reel
02727.XX.01	10/4C SOOW CAROLPRENE BLK	FOOT	48	42	48	Various Lengths
02727.35T.01	10/4C SOOW CAROLPRENE BLK	FOOT	16	13	16	250 FT Reel
02727.38T.01	10/4C SOOW CAROLPRENE BLK	FOOT	20	20	20	500 FT Reel
02727.85.01	10/4C SOOW CAROLPRENE BLK	FOOT	20	21	7	250 FT Coil
02427.41T.05M	10/4C SOOW CAROLPRENE YLW	FOOT	22	20	1	1000 FT Reel
02427.35.05M	10/4C SOOW CAROLPRENE YLW	FOOT	22	20	1	250 FT Reel
02427.35T.05M	10/4C SOOW CAROLPRENE YLW	FOOT	22	20	1	250 FT Reel
02427.99.05	10/4C SOOW CAROLPRENE YLW	FOOT	48	40	48	Factory Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
02427.41T.05	10/4C SOOW CAROLPRENE YLW	FOOT	22	20	18	1000 FT Reel
02427.XX.05	10/4C SOOW CAROLPRENE YLW	FOOT	48	42	1	Various Lengths
02427.35.05	10/4C SOOW CAROLPRENE YLW	FOOT	14	14	12	250 FT Reel
02427.35T.05	10/4C SOOW CAROLPRENE YLW	FOOT	14	14	12	250 FT Reel
02724.41T.01M	12/2C SOOW CAROLPRENE BLK	FOOT	24	22	24	1000 FT Reel
02724.46.01M	12/2C SOOW CAROLPRENE BLK	FOOT	22	20	1	5000 FT Reel
02724.85.01M	12/2C SOOW CAROLPRENE BLK	FOOT	21	21	6	250 FT Coil
02724.41.03	12/2C SOOW CAROLPRENE RED	FOOT	24	22	24	1000 FT Reel
02724.46.03	12/2C SOOW CAROLPRENE RED	FOOT	42	28	42	5000 FT Reel
02724.35.03	12/2C SOOW CAROLPRENE RED	FOOT	24	22	24	250 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
02724.41.03M	12/2C SOOW CAROLPRENE RED	FOOT	22	20	1	1000 FT Reel
02724.46.03M	12/2C SOOW CAROLPRENE RED	FOOT	22	20	1	5000 FT Reel
02724.35.03M	12/2C SOOW CAROLPRENE RED	FOOT	22	20	1	250 FT Reel
02724.41T.01	12/2C SOOW CAROLPRENE BLK	FOOT	24	22	24	1000 FT Reel
02724.46.01	12/2C SOOW CAROLPRENE BLK	FOOT	42	28	42	5000 FT Reel
02724.L2.01	12/2C SOOW CAROLPRENE BLK	FOOT	22	20	18	Long Length Reel
02724.38.01	12/2C SOOW CAROLPRENE BLK	FOOT	22	20	18	500 FT Reel
02724.85.01	12/2C SOOW CAROLPRENE BLK	FOOT	20	21	14	250 FT Coil
02725.99.01M	12/3C SOOW CAROLPRENE BLK	FOOT	48	42	1	Factory Reel
02725.41T.01M	12/3C SOOW CAROLPRENE BLK	FOOT	24	22	24	1000 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
02725.44.01M	12/3C SOOW CAROLPRENE BLK	FOOT	36	36	26	2500 FT Reel
02725.46.01M	12/3C SOOW CAROLPRENE BLK	FOOT	42	28	42	5000 FT Reel
02725.35T.01M	12/3C SOOW CAROLPRENE BLK	FOOT	14	13	14	250 FT Reel
02725.38T.01M	12/3C SOOW CAROLPRENE BLK	FOOT	22	20	1	500 FT Reel
02725.41T.04	12/3C SOOW CAROLPRENE ORG	FOOT	24	22	24	1000 FT Reel
02725.XX.04	12/3C SOOW CAROLPRENE ORG	FOOT	24	22	24	Various Lengths
02725.35.04	12/3C SOOW CAROLPRENE ORG	FOOT	24	22	24	250 FT Reel
02425.41T.05	12/3C SOOW CAROLPRENE YLW	FOOT	22	20	18	1000 FT Reel
02425.XX.05	12/3C SOOW CAROLPRENE YLW	FOOT	48	42	1	Various Lengths
02425.35.05	12/3C SOOW CAROLPRENE YLW	FOOT	14	14	12	250 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
02425.35T.05	12/3C SOOW CAROLPRENE YLW	FOOT	14	14	12	250 FT Reel
02425.41T.05M	12/3C SOOW CAROLPRENE YLW	FOOT	22	20	1	1000 FT Reel
02425.35T.05M	12/3C SOOW CAROLPRENE YLW	FOOT	14	14	12	250 FT Reel
02725.99.01	12/3C SOOW CAROLPRENE BLK	FOOT	48	42	48	Factory Reel
02725.41T.01	12/3C SOOW CAROLPRENE BLK	FOOT	24	22	24	1000 FT Reel
02725.44.01	12/3C SOOW CAROLPRENE BLK	FOOT	32	26	32	2500 FT Reel
02725.46.01	12/3C SOOW CAROLPRENE BLK	FOOT	42	28	42	5000 FT Reel
02725.XX.01	12/3C SOOW CAROLPRENE BLK	FOOT	48	42	48	Various Lengths
02725.35.01	12/3C SOOW CAROLPRENE BLK	FOOT	14	13	14	250 FT Reel
02725.35T.01	12/3C SOOW CAROLPRENE BLK	FOOT	14	13	14	250 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
02725.38T.01	12/3C SOOW CAROLPRENE BLK	FOOT	20	13	20	500 FT Reel
02725.82.01	12/3C SOOW CAROLPRENE BLK	FOOT	11	11	8	50 FT Hanging Cuff
02725.85.01	12/3C SOOW CAROLPRENE BLK	FOOT	20	21	14	250 FT Coil
02426.99.05	12/4C SOOW CAROLPRENE YLW	FOOT	22	20	1	Factory Reel
02426.41T.05	12/4C SOOW CAROLPRENE YLW	FOOT	22	20	18	1000 FT Reel
02426.XX.05	12/4C SOOW CAROLPRENE YLW	FOOT	48	42	1	Various Lengths
02426.35T.05	12/4C SOOW CAROLPRENE YLW	FOOT	14	14	12	250 FT Reel
02426.41T.05M	12/4C SOOW CAROLPRENE YLW	FOOT	22	20	1	1000 FT Reel
02426.35T.05M	12/4C SOOW CAROLPRENE YLW	FOOT	22	20	1	250 FT Reel
02726.99.01	12/4C SOOW CAROLPRENE BLK	FOOT	48	42	48	Factory Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
02726.41T.01	12/4C SOOW CAROLPRENE BLK	FOOT	24	24	24	1000 FT Reel
02726.44.01	12/4C SOOW CAROLPRENE BLK	FOOT	36	25	36	2500 FT Reel
02726.46.01	12/4C SOOW CAROLPRENE BLK	FOOT	48	34	48	5000 FT Reel
02726.XX.01	12/4C SOOW CAROLPRENE BLK	FOOT	48	42	48	Various Lengths
02726.35.01	12/4C SOOW CAROLPRENE BLK	FOOT	16	13	16	250 FT Reel
02726.35T.01	12/4C SOOW CAROLPRENE BLK	FOOT	16	13	16	250 FT Reel
02726.38T.01	12/4C SOOW CAROLPRENE BLK	FOOT	20	20	20	500 FT Reel
02726.85.01	12/4C SOOW CAROLPRENE BLK	FOOT	20	21	7	250 FT Coil
02726.41T.01M	12/4C SOOW CAROLPRENE BLK	FOOT	24	22	24	1000 FT Reel
02726.44.01M	12/4C SOOW CAROLPRENE BLK	FOOT	36	36	28	2500 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
02726.46.01M	12/4C SOOW CAROLPRENE BLK	FOOT	48	34	48	5000 FT Reel
02726.XX.01M	12/4C SOOW CAROLPRENE BLK	FOOT	48	42	1	Various Lengths
02726.35T.01M	12/4C SOOW CAROLPRENE BLK	FOOT	16	13	16	250 FT Reel
02726.38T.01M	12/4C SOOW CAROLPRENE BLK	FOOT	22	20	1	500 FT Reel
02722.41T.01M	16/2C SOOW CAROLPRENE BLK	FOOT	16	13	16	1000 FT Reel
02722.46.01M	16/2C SOOW CAROLPRENE BLK	FOOT	22	20	1	5000 FT Reel
02722.35.01M	16/2C SOOW CAROLPRENE BLK	FOOT	22	20	1	250 FT Reel
02722.35T.01M	16/2C SOOW CAROLPRENE BLK	FOOT	11	11	9	250 FT Reel
02722.99.01	16/2C SOOW CAROLPRENE BLK	FOOT	48	42	48	Factory Reel
02722.41T.01	16/2C SOOW CAROLPRENE BLK	FOOT	16	13	16	1000 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
02722.44.01	16/2C SOOW CAROLPRENE BLK	FOOT	24	22	24	2500 FT Reel
02722.46.01	16/2C SOOW CAROLPRENE BLK	FOOT	34	20	34	5000 FT Reel
02722.35.01	16/2C SOOW CAROLPRENE BLK	FOOT	11	11	9	250 FT Reel
02722.35T.01	16/2C SOOW CAROLPRENE BLK	FOOT	11	11	9	250 FT Reel
02465.41T.05M	16/3C SOOW CAROLPRENE YLW	FOOT	22	20	1	1000 FT Reel
02465.35T.05M	16/3C SOOW CAROLPRENE YLW	FOOT	11	11	9	250 FT Reel
02765.99.01	16/3C SOOW CAROLPRENE BLK	FOOT	48	42	48	Factory Reel
02765.41T.01	16/3C SOOW CAROLPRENE BLK	FOOT	18	13	18	1000 FT Reel
02765.44.01	16/3C SOOW CAROLPRENE BLK	FOOT	24	22	24	2500 FT Reel
02765.46.01	16/3C SOOW CAROLPRENE BLK	FOOT	34	20	34	5000 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
02765.XX.01	16/3C SOOW CAROLPRENE BLK	FOOT	48	42	1	Various Lengths
02765.35.01	16/3C SOOW CAROLPRENE BLK	FOOT	11	11	9	250 FT Reel
02765.35T.01	16/3C SOOW CAROLPRENE BLK	FOOT	11	11	9	250 FT Reel
02765.38T.01	16/3C SOOW CAROLPRENE BLK	FOOT	14	13	14	500 FT Reel
02765.82.01	16/3C SOOW CAROLPRENE BLK	FOOT	11	11	8	50 FT Hanging Cuff
02465.41T.05	16/3C SOOW CAROLPRENE YLW	FOOT	18	18	12	1000 FT Reel
02465.XX.05	16/3C SOOW CAROLPRENE YLW	FOOT	48	42	1	Various Lengths
02465.35T.05	16/3C SOOW CAROLPRENE YLW	FOOT	11	11	9	250 FT Reel
02765.99.01M	16/3C SOOW CAROLPRENE BLK	FOOT	48	42	1	Factory Reel
02765.41T.01M	16/3C SOOW CAROLPRENE BLK	FOOT	18	13	18	1000 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
02765.44.01M	16/3C SOOW CAROLPRENE BLK	FOOT	24	24	21	2500 FT Reel
02765.46.01M	16/3C SOOW CAROLPRENE BLK	FOOT	34	20	34	5000 FT Reel
02765.35T.01M	16/3C SOOW CAROLPRENE BLK	FOOT	11	11	9	250 FT Reel
02765.38T.01M	16/3C SOOW CAROLPRENE BLK	FOOT	22	20	1	500 FT Reel
02466.41T.05	16/4C SOOW CAROLPRENE YLW	FOOT	18	18	12	1000 FT Reel
02466.XX.05	16/4C SOOW CAROLPRENE YLW	FOOT	48	42	1	Various Lengths
02466.35T.05	16/4C SOOW CAROLPRENE YLW	FOOT	11	11	12	250 FT Reel
02766.99.01	16/4C SOOW CAROLPRENE BLK	FOOT	48	42	48	Factory Reel
02766.41.01	16/4C SOOW CAROLPRENE BLK	FOOT	18	13	18	1000 FT Reel
02766.41T.01	16/4C SOOW CAROLPRENE BLK	FOOT	18	13	18	1000 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
02766.44.01	16/4C SOOW CAROLPRENE BLK	FOOT	24	22	24	2500 FT Reel
02766.46.01	16/4C SOOW CAROLPRENE BLK	FOOT	32	26	32	5000 FT Reel
02766.35T.01	16/4C SOOW CAROLPRENE BLK	FOOT	11	11	11	250 FT Reel
02766.38T.01	16/4C SOOW CAROLPRENE BLK	FOOT	16	13	16	500 FT Reel
02766.41T.01M	16/4C SOOW CAROLPRENE BLK	FOOT	18	13	18	1000 FT Reel
02766.44.01M	16/4C SOOW CAROLPRENE BLK	FOOT	24	24	21	2500 FT Reel
02766.46.01M	16/4C SOOW CAROLPRENE BLK	FOOT	36	36	28	5000 FT Reel
02766.35T.01M	16/4C SOOW CAROLPRENE BLK	FOOT	12	11	11	250 FT Reel
02766.38T.01M	16/4C SOOW CAROLPRENE BLK	FOOT	22	20	1	500 FT Reel
02466.41T.05M	16/4C SOOW CAROLPRENE YLW	FOOT	22	20	1	1000 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
02466.35T.05M	16/4C SOOW CAROLPRENE YLW	FOOT	11	11	12	250 FT Reel
02757.41.01	16/5C SOOW CAROLPRENE BLK	FOOT	0	0	0	1000 FT Reel
02763.41T.01M	18/2C SOOW CAROLPRENE BLK	FOOT	16	13	16	1000 FT Reel
02763.35.01M	18/2C SOOW CAROLPRENE BLK	FOOT	11	11	9	250 FT Reel
02763.35T.01M	18/2C SOOW CAROLPRENE BLK	FOOT	22	20	1	250 FT Reel
02763.99.01	18/2C SOOW CAROLPRENE BLK	FOOT	48	42	48	Factory Reel
02763.41T.01	18/2C SOOW CAROLPRENE BLK	FOOT	16	13	16	1000 FT Reel
02763.44.01	18/2C SOOW CAROLPRENE BLK	FOOT	32	26	32	2500 FT Reel
02763.46.01	18/2C SOOW CAROLPRENE BLK	FOOT	32	26	32	5000 FT Reel
02763.35.01	18/2C SOOW CAROLPRENE BLK	FOOT	11	11	9	250 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
02763.35T.01	18/2C SOOW CAROLPRENE BLK	FOOT	11	11	9	250 FT Reel
02469.41T.05	18/3C SOOW CAROLPRENE YLW	FOOT	16	16	12	1000 FT Reel
02469.XX.05	18/3C SOOW CAROLPRENE YLW	FOOT	48	42	1	Various Lengths
02469.35T.05	18/3C SOOW CAROLPRENE YLW	FOOT	11	11	9	250 FT Reel
02769.99.01M	18/3C SOOW CAROLPRENE BLK	FOOT	48	42	1	Factory Reel
02769.41T.01M	18/3C SOOW CAROLPRENE BLK	FOOT	16	13	16	1000 FT Reel
02769.46.01M	18/3C SOOW CAROLPRENE BLK	FOOT	22	20	1	5000 FT Reel
02769.35T.01M	18/3C SOOW CAROLPRENE BLK	FOOT	11	11	9	250 FT Reel
02769.38.01M	18/3C SOOW CAROLPRENE BLK	FOOT	22	20	1	500 FT Reel
02469.35T.05M	18/3C SOOW CAROLPRENE YLW	FOOT	11	11	9	250 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
02769.99.01	18/3C SOOW CAROLPRENE BLK	FOOT	48	42	48	Factory Reel
02769.41T.01	18/3C SOOW CAROLPRENE BLK	FOOT	16	13	16	1000 FT Reel
02769.44.01	18/3C SOOW CAROLPRENE BLK	FOOT	24	22	24	2500 FT Reel
02769.46.01	18/3C SOOW CAROLPRENE BLK	FOOT	30	22	30	5000 FT Reel
02769.35.01	18/3C SOOW CAROLPRENE BLK	FOOT	11	11	9	250 FT Reel
02769.35T.01	18/3C SOOW CAROLPRENE BLK	FOOT	11	11	9	250 FT Reel
02769.38.01	18/3C SOOW CAROLPRENE BLK	FOOT	14	13	14	500 FT Reel
02770.99.01M	18/4C SOOW CAROLPRENE BLK	FOOT	48	42	1	Factory Reel
02770.41T.01M	18/4C SOOW CAROLPRENE BLK	FOOT	18	13	18	1000 FT Reel
02770.46.01M	18/4C SOOW CAROLPRENE BLK	FOOT	22	20	1	5000 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
02770.35.01M	18/4C SOOW CAROLPRENE BLK	FOOT	22	20	1	250 FT Reel
02770.35T.01M	18/4C SOOW CAROLPRENE BLK	FOOT	11	11	9	250 FT Reel
02770.99.01	18/4C SOOW CAROLPRENE BLK	FOOT	48	42	1	Factory Reel
02770.41T.01	18/4C SOOW CAROLPRENE BLK	FOOT	18	13	18	1000 FT Reel
02770.46.01	18/4C SOOW CAROLPRENE BLK	FOOT	34	20	34	5000 FT Reel
02770.44.01	18/4C SOOW CAROLPRENE BLK	FOOT	14	14	12	2500 FT Reel
02770.35.01	18/4C SOOW CAROLPRENE BLK	FOOT	11	11	9	250 FT Reel
02770.35T.01	18/4C SOOW CAROLPRENE BLK	FOOT	11	11	9	250 FT Reel
02770.38.01	18/4C SOOW CAROLPRENE BLK	FOOT	1	1	1	500 FT Reel
02470.35T.05	18/4C SOOW CAROLPRENE YLW	FOOT	12	12	12	250 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
02723.41T.01M	14/2C SOOW CAROLPRENE BLK	FOOT	20	20	18	1000 FT Reel
02723.46.01M	14/2C SOOW CAROLPRENE BLK	FOOT	22	20	1	5000 FT Reel
02723.38T.01M	14/2C SOOW CAROLPRENE BLK	FOOT	14	13	14	500 FT Reel
02723.85.01M	14/2C SOOW CAROLPRENE BLK	FOOT	21	22	5	250 FT Coil
02723.41T.03	14/2C SOOW CAROLPRENE RED	FOOT	20	20	18	1000 FT Reel
02723.41T.03M	14/2C SOOW CAROLPRENE RED	FOOT	22	20	1	1000 FT Reel
02723.XX.01	14/2C SOOW CAROLPRENE BLK	FOOT	16	16	19	Various Lengths
02723.41T.01	14/2C SOOW CAROLPRENE BLK	FOOT	20	20	18	1000 FT Reel
02723.44.01	14/2C SOOW CAROLPRENE BLK	FOOT	30	22	30	2500 FT Reel
02723.46.01	14/2C SOOW CAROLPRENE BLK	FOOT	36	25	36	5000 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
02723.38T.01	14/2C SOOW CAROLPRENE BLK	FOOT	14	13	14	500 FT Reel
02723.85.01	14/2C SOOW CAROLPRENE BLK	FOOT	20	21	14	250 FT Coil
02765R.44.01	16/3C SOOW CAROLPRENE BLK	FOOT	22	20	1	2500 FT Reel
02765R.46.01	16/3C SOOW CAROLPRENE BLK	FOOT	22	20	1	5000 FT Reel
02769R.46.01	18/3C SOOW CAROLPRENE BLK	FOOT	22	20	1	5000 FT Reel
01812R.35.01	8/3C SOOW CAROLPRENE BLK	FOOT	22	20	1	250 FT Reel
02728R.41T.01	10/3C SOOW CAROLPRENE BLK	FOOT	22	20	1	1000 FT Reel
02728R.44.01	10/3C SOOW CAROLPRENE BLK	FOOT	22	20	1	2500 FT Reel
02462.41T.05	14/3C SOOW CAROLPRENE YLW	FOOT	24	24	18	1000 FT Reel
02462.XX.05	14/3C SOOW CAROLPRENE YLW	FOOT	48	42	1	Various Lengths

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
02462.35.05	14/3C SOOW CAROLPRENE YLW	FOOT	14	14	12	250 FT Reel
02462.35T.05	14/3C SOOW CAROLPRENE YLW	FOOT	14	14	12	250 FT Reel
02762R.44.01	14/3C SOOW CAROLPRENE BLK	FOOT	22	20	1	2500 FT Reel
02762R.46.01	14/3C SOOW CAROLPRENE BLK	FOOT	22	20	1	5000 FT Reel
02762.41T.01M	14/3C SOOW CAROLPRENE BLK	FOOT	24	22	24	1000 FT Reel
02762.44.01M	14/3C SOOW CAROLPRENE BLK	FOOT	36	25	26	2500 FT Reel
02762.46.01M	14/3C SOOW CAROLPRENE BLK	FOOT	36	25	36	5000 FT Reel
02762.35T.01M	14/3C SOOW CAROLPRENE BLK	FOOT	14	14	12	250 FT Reel
02762.38T.01M	14/3C SOOW CAROLPRENE BLK	FOOT	22	20	1	500 FT Reel
02762.99.01	14/3C SOOW CAROLPRENE BLK	FOOT	48	42	48	Factory Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
02762.41T.01	14/3C SOOW CAROLPRENE BLK	FOOT	24	22	24	1000 FT Reel
02762.44.01	14/3C SOOW CAROLPRENE BLK	FOOT	36	25	36	2500 FT Reel
02762.46.01	14/3C SOOW CAROLPRENE BLK	FOOT	36	25	36	5000 FT Reel
02762.XX.01	14/3C SOOW CAROLPRENE BLK	FOOT	48	42	1	Various Lengths
02762.35T.01	14/3C SOOW CAROLPRENE BLK	FOOT	14	14	12	250 FT Reel
02762.38T.01	14/3C SOOW CAROLPRENE BLK	FOOT	16	13	16	500 FT Reel
02762.82.01	14/3C SOOW CAROLPRENE BLK	FOOT	11	11	8	50 FT Hanging Cuff
02762.85.01	14/3C SOOW CAROLPRENE BLK	FOOT	20	21	14	250 FT Coil
02462.41T.05M	14/3C SOOW CAROLPRENE YLW	FOOT	22	20	1	1000 FT Reel
02462.35T.05M	14/3C SOOW CAROLPRENE YLW	FOOT	14	14	12	250 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
02465R.46.05	16/3C SOOW CAROLPRENE YLW	FOOT	48	42	1	5000 FT Reel
02768.99.01	14/4C SOOW CAROLPRENE BLK	FOOT	48	42	48	Factory Reel
02768.41T.01	14/4C SOOW CAROLPRENE BLK	FOOT	24	22	24	1000 FT Reel
02768.44.01	14/4C SOOW CAROLPRENE BLK	FOOT	36	25	36	2500 FT Reel
02768.46.01	14/4C SOOW CAROLPRENE BLK	FOOT	42	28	42	5000 FT Reel
02768.35T.01	14/4C SOOW CAROLPRENE BLK	FOOT	14	13	14	250 FT Reel
02768.38T.01	14/4C SOOW CAROLPRENE BLK	FOOT	18	13	18	500 FT Reel
02768.85.01	14/4C SOOW CAROLPRENE BLK	FOOT	20	21	14	250 FT Coil
02468.41T.05	14/4C SOOW CAROLPRENE YLW	FOOT	20	20	18	1000 FT Reel
02468.35T.05	14/4C SOOW CAROLPRENE YLW	FOOT	14	14	12	250 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
02468.41T.05M	14/4C SOOW CAROLPRENE YLW	FOOT	22	20	1	1000 FT Reel
02468.35T.05M	14/4C SOOW CAROLPRENE YLW	FOOT	22	20	1	250 FT Reel
02768.41T.01M	14/4C SOOW CAROLPRENE BLK	FOOT	24	22	24	1000 FT Reel
02768.44.01M	14/4C SOOW CAROLPRENE BLK	FOOT	22	20	1	2500 FT Reel
02768.46.01M	14/4C SOOW CAROLPRENE BLK	FOOT	22	20	1	5000 FT Reel
02768.35T.01M	14/4C SOOW CAROLPRENE BLK	FOOT	14	13	14	250 FT Reel
02768.38T.01M	14/4C SOOW CAROLPRENE BLK	FOOT	18	13	18	500 FT Reel