			DATE	REV	ECN	DESCRIPTION
PRODUCT	SPECIFICATION		10/30/2015	D		SPECIFICATION UPDATED
	<u>n echrication</u>					
Parent Number:	F18041-					
Description	18 16/30 TC AWM 1569 or 1007 TR-64	DIAMETER: (0.079			
<u>Description.</u>	<u>AWM I A/B</u>	$TOLERANCE \pm : \ \underline{C}$	<u>.003</u>			•
						Ø / '
Stranding:	<u>16/30 TC LHL</u>			▼		
						<i>MIN AVG WALL:</i> <u>0.015</u>
<u>Style:</u>	<u>UL: AWM 1007 OR 1569 CSA: TR-64</u>				1	MINIMUM WALL: 0.013
Insulation:	PVC					
<u>Print Legend:</u>	18 AWG (0.823mm2) E57498 (PLANT ID CODE AWM I A/B 105C 300V FT1	E) (AWM LOGO) AWM 1569 105C	OR 1007 80	<u> 0C 300V VV</u>	V-1 156	205 CSA TR-64 90C FT1 OR
Voltage:	300V					
<u>, , , , , , , , , , , , , , , , , , , </u>						
Temperature: 1569=105C, 1007=80C, TR64=90C, AWM I A/B=105C						
<u>Notes:</u>	1. Min Temp Rating: -15C					
	This and that a mailing with European Direction 2014/0					
This product complies with European Directive 2011/65/EU (RoHS 2) The information presented here is, to the best of our knowledge, true and accurate. Since conditions of use are beyond Southwire's control all product data presented is for informational						
purposes only and does not create a binding obligation or liability on Southwire or confer any rights on any customer. The sale of product(s) is conditioned upon acceptance of a purchase order subject to Southwire's standard terms and conditions contained therein, including without limitation Southwire's standard warranty. Southwire disclaims all liability in connection with the use of						
information contained						
	oprietary intellectual property of Southwire Company, L en consent of Southwire Company, LLC.	LC. Any information contained herein s	hall not be di	isclosed to		Southwire
					1	റംപിച്
<u>Customer Appro</u>						Copperfield
	Nbr(s):D	ate:			111	5 W. North Street
		Company Name:				men, IN 46506
1 ule:	0	ompuny wante:			Pho	ne: 1-574-546-5115