

AUTOMOTIVE PRIMARY WIRE

AUTOMOTIVE Revised Nov.2009

General Purpose Thermoplastic:

Polyvinyl chloride (PVC) insulated wire manufactured to SAE J1128 standards to meet the following specifications:

FORD: M1L 56A
CHRYSLER: MS-3450

GPT Bare Copper 80°C 60 Volts				
Product	#CU/MFT	Stranding	Wall Thickness	Min Order
GPT-20-7-B	3.46	7/0126	.023	55M
GPT-18-16-B	4.94	16/0098	.023	45M
GPT-18-61-B	4.90	61/36	.023	50M
GPT-16-19-B	7.40	19/0113	.023	30M
GPT-16-37-B	7.15	37/32	.023	40M
GPT-14-19-B	11.90	19/0142	.023	22M
GPT-12-19-B	18.35	19/0117	.026	23M
GPT-10-19-B	29.40	19/0224	.031	28M
GPT-8-19-B	48.00	19/0282	.037	25M
GPT-6-49-B	80.75	49/0232	.045	50M
GPT-6-37-B	82.00	37/0266	.045	20M
GPT-4-61-B	122.00	61/0249	.045	20M
GPT-4-133-B	122.00	133/0170	.045	20M

DELPHI PACKARD: ESM-3012

GPT Bare Copper 80°C 60 Volts				
Product	#CU/MFT	Stranding	Wall Thickness	Min Order
GPT-0.5-MM	3.46	7/0126	.023	55M
GPT-0.8-MM	4.94	16/0098	.023	45M
GPT-1.0-MM	7.40	19/0113	.023	30M
GPT-2.0-MM	11.90	19/0242	.023	22M
GPT-3.0-MM	18.35	19/0177	.026	23M
GPT-5.0-MM	29.40	19/0224	.031	28M
GPT-8.0-MM	48.00	19/0282	.037	25M

Minimum order requirement reflects quantity per color, per release. Different color quantities may be combined to determine pricing with solid colors treated separately from striped colors.

800-776-9223 (Ohio) 800-684-7823 (Texas)