

THERM-O-LINK INC.

10513 Freedom Street
GARRETTSVILLE, OHIO 44231

(330) 527-2124
FAX: (330) 527-2123

Material Specification

Customer: IEWC

TOL Part Number: **GPT-16-1003**
Spec Revision Level: A5
Customer Part Number: GPTM16T-0-P

Description: 16 GA GPT 105 DEGC PVC, 19 STRANDS, **TINNED COPPER MARINE WIRE WITH PRINT**
Conductor (Stranding): 19 X .0113" **Tinned Copper**
Conductor OD (Nom) 0.055 inches
Max. Lay Length: 2.0 inch Lay
Nom. Wall Thickness: 0.023 inches
Max . O.D: 0.115 inches
Nom O. D: 0.101 inches
Min O. D: 0.098 inches
Max Runout: 0.006 inches
Circular Mils (CMA): 2336 (Min)
Surface Print: GPT 16GA **MARINE WIRE** SAE J378 & J1128 60V DC
105C DRY

This Product is RoHS Compliant.

Specification Reference Data

SAE: J-1128 / J378	Ford: N/A	Chrysler: N/A
UL : N/A	CSA: N/A	Packard: N/A
Other: N/A		

Therm-O-Link, Inc. certifies that the above specifications are met or exceeded in the production of this product.

Verified By: Mir Hussain (Corporate Product Engineering Manager)
Date: 3-30-2017