PRODUCT DATA SHEET





METRIC FUSIBLE LINK

3MM2 19X25B M3382 DB

Conductor

Size: 3 mm2
Number of Strands: 19
Strand Diameter, Avg. Min: 0.443 mm
Conductor: Bare Copper

Insulation

Insulation Material: 150°C XLPE

 Min Wall:
 0.83 mm (0.033 in)

 Nom Wall:
 1.19 mm (0.047 in)

 Diameter, Min:
 4.53 mm (0.178 in)

 Diameter, Max:
 4.69 mm (0.185 in)

 Strip Force, Min:
 4.5 lbs. (20.0 N)

Voltage Rating: Road Vehicle Applications where nominal system voltage is 50 volts or less

Temperature Rating: -40°C to 150°C

Specifications: DELPHI: DELPHI M3382
Print Legend: "3 SQ. MM FUSIBLE LINK"

Part Number: 155908-21IE

Packaging: Drum
Color: Dark Blue

Other: RoHS Compliant

Rev 0 (2017-10-10) Written by: RHuang