

1MM2 19X.28B M3382 BK

Conductor

Size:	1 mm2
Number of Strands:	19
Strand Diameter, Avg. Min:	0.275 mm
Conductor:	Bare Copper

Insulation

Insulation Material:	150°C XLPE
Min Wall:	0.72 mm (0.028 in)
Nom Wall:	1.04 mm (0.041 in)
Diameter, Min:	3.36 mm (0.132 in)
Diameter, Max:	3.52 mm (0.139 in)
Strip Force, Min:	4.5 lbs. (20.0 N)

Voltage Rating:	Road Vehicle Applications where nominal system voltage is 50 volts or less
Temperature Rating:	-40°C to 150°C
Specifications:	DELPHI: DELPHI M3382
Print Legend:	"1 SQ. MM FUSIBLE LINK"
Part Number:	155909-21IE
Packaging:	Drum
Color:	Black
Other:	RoHS Compliant

Rev 0 (2017-10-10)

Written by: RHuang