



## PRODUCT INFORMATION SHEET

# UL STYLE 3284

## 4GA 133X25T 3284 BK

---

### Conductor

Size: 4 ga  
Number of Strands: 133  
Strand Diameter, Nom: 25 ga  
Conductor: Tinned Copper

---

### Insulation

Insulation Material: 125°C EPDM  
Min Wall: 1.83 mm ( 0.072 in )  
Nom Wall: 2.03 mm ( 0.080 in )  
Diameter, Nom: 11.33 mm ( 0.446 in )  
Strip Force, Min: 4 lbs. ( 17.8 N )  
Strip Force, Max: 40 lbs. ( 178.0 N )  
Separator: Physical

---

Voltage Rating: 600 V  
Temperature Rating: -40°C to 125°C  
Specifications: UL: 3284  
CSA: CL-1254  
Part Number: 138849-73IE  
Packaging: Reels  
Print Legend: 4 AWG (UL LOGO) AWM STYLE 3284 125°C 600V EP PRESTOLITE PG CSA CL-1254  
OR AWM I A/B 125°C 600V FT2  
Color: Black  
Other: RoHS Compliant