



ATTN: IEWC

IN RESPONSE TO YOUR REQUEST FOR SPECS ON PARTB02/13-FGINDU, 2/0 GA BATTERY CABLE, PLEASE FIND THE FOLLOWING:

- 1) GA: 2/0 GA**
- 2) STRANDING: 7X37/.0226 BC**
- 3) OVERALL O.D: .570 O.D.**
- 4) JACKET TYPE: 105 DEGREE PVC**
- 5) COPPER CONTENT: 428#/M'**
- 6) STANDARD PUT-UP: 1300' PER 30" REEL**

THIS IS TO CONFIRM THAT PART SGT2/0B259-1-P LISTED MEETS SAE J1127.

ANDY HARWOOD
VICE PRESIDENT OF SALES