



Southwire®

SPECIFICATION SHEET

PRODUCT DESCRIPTION: 18-16 2/C SJTOW Paper 105* 300V

STOCK NUMBER: 56-47-21-01

JACKET:

NOMINAL OUTSIDE DIAMETER: .290" in.
NOMINAL WALL THICKNESS: .030" in.
COMPOUND: Polyvinyl Chloride

CONDUCTOR:

NUMBER OF CONDUCTORS: 2
CONDUCTOR COLORS: Black, White
NOMINAL OUTSIDE DIAMETER : .109" in.
NOMINAL WALL THICKNESS : .030" in.
COPPER: 18 AWG 16X.010" SBC

TEMPERATURE: 105°C - max
-40°C - min

FILLERS: Reinforced Paperfiller

PRINT: **INDENT**

PRINT DESCRIPTION: (UL) VW-1 E46194 (M) SJTOW 2/C 18 AWG (0.824mm²) 105°C DRY 60°C WATER RESISTANT
300V (CSA) FT1, FT2 LL90458 (M)

PRODUCT MANUFACTURED IN ACCORDANCE TO:

UL STANDARD NO. 62 FLEXIBLE CORDS AND FIXTURE WIRES - FILE NO. E46194

CSA STANDARD C22.2 NO. 49 FLEXIBLE CORDS - FILE NO. LL90458

SOUTHWIRE COMPANY

3800 Industrial Parkway
MINERAL WELLS, TEXAS 76067
TEL (940) 328-1047
FAX (940) 328-1013