



ATTN: INDUSTRIAL ELECTRIC

IN RESPONSE TO YOUR REQUEST FOR SPECS ON PART B90701-FGINDU, 7 CONDUCTOR TRAILER CABLE, PLEASE FIND THE FOLLOWING:

- 1) GA: 12 GA. 6 CONDUCTORS GPT
10 GA. 1 CONDUCTOR GPT**
- 2) OVERALL O.D: .600 O.D. +/- .015**
- 3) STRANDING: 12 GA-19/.0176 BC, 10 GA-19/.0225 BC**
- 2) INNER COLORS: 12 GA: BLK, YELL, RED, GRN, BRN,
BLU/ 10 GA: WHT**
- 3) JACKET TYPE: 80 DEGREE BLACK PVC**
- 4) JACKET THICKNESS: APPROX. .070**
- 5) COPPER CONTENT: 143.07#/M'**
- 6) STANDARD PUT-UP: 1350' PER 30" REEL**
- 7) SEPARATOR: CREPE PAPER**

THIS IS TO CONFIRM THAT PART B90701-FGINDU LISTED MEETS THE ABOVE SPECS.

**ANDY HARWOOD
SALES MANAGER**