

ATTN: IEWC

IN RESPONSE TO YOUR REQUEST FOR SPECS ON PART B90707-FGINDU, 7 CONDUCTOR TRAILER CABLE, PLEASE FIND THE FOLLOWING:

- 1) GA: 14 GA. 4 CONDUCTORS GPT GRN/YEL/BRO/RED 12 GA. 1 CONDUCTOR GPT BLU 10 GA. 2 CONDUCTOR GPT WHT/BLK
- 2) OVERALL O.D: .550 O.D.
- 3) STRANDING: 14 GA-19/27 12 GA-19/25 10 GA-19/23 BC
- 2) INNER COLORS: BLUE, WHITE, BLACK, BROWN, GREEN, RED, YELLOW
- 3) JACKET TYPE: +80C and -30C DEGREE BLACK PVC
- 4) JACKET THICKNESS: APPROX. .055
- 5) PAPER SEPERATOR
- 6) COPPER CONTENT: 134#/M'
- 7) STANDARD PUT-UP: 1000' PER 30" REEL

THIS IS TO CONFIRM THAT PART B90707-FGINDU LISTED MEETS THE ABOVE SPECS.

ANDY HARWOOD VICE PRESIDENT