

ATTN: IEWC

IN RESPONSE TO YOUR REQUEST FOR SPECS ON PART B90207-FGINDU, 16/6 CABLE, PLEASE FIND THE FOLLOWING:

- 1) GA: 16 GA. 6 CONDUCTORS**
- 2) STRANDING: 19/.0112 BC**
- 3) OVERALL O.D: .395 O.D.**
- 4) WALL THICKNESS: .040**
- 5) JACKET TYPE: 80 DEGREE PVC**
- 6) INNER COLORS: BLK, BRN, GRN, YELL, RED, BLU**
- 7) COPPER CONTENT: 48#/M'**
- 8) STANDARD PUT-UP: 3500' PER 30" REEL**

THIS IS TO CONFIRM THAT PART B90207-FGINDU LISTED MEETS THE ABOVE SPECS.

**ANDY HARWOOD
VICE PRESIDENT**