

GNR-350

100-Channel Tower Standalone NVR



- 6-bay Tower Standalone NVR
- Maximum Number of Video Devices: 100 (Free License: 32)
- Multi-Browser Support for Lite Web Client
- System Monitoring and Notifications
- Location-based management with e-Map & Google Map
- Workstation, Web Client, Mobile Client
- Event Trigger, Response, Notification and Snapshot to Line Messenger
- Intel Core i3-13100, 16GB
- Support up to 8 disks (Optional)

► Specifications

Device

Product Type	Standalone NVR
Maximum Resolution	Support all ACTi cameras in all resolutions
Maximum Number of Video Devices	100
Maximum Number of POS devices	100 (requires additional license)
Maximum Number of Access Control and Network I/O devices	100 (requires additional license)
Maximum Number of Clients	Local: 1, Remote: 4

Hardware

CPU	Intel Core i3-13100
RAM	16GB, DDR4, 3200MT/s

License

License required	Yes
Free License	32 (32 channels for ACTi and 1 channel for third-party video device)

Live View

Display Layout Mode	Local: 1, 3, 4, 5, 6, 8, 9, 10, 12, 16 Remote (IE client): 1, 3, 4, 5, 6, 8, 9, 10, 12, 16, 18, 24, 25, 35, 36, 48, 49, 64 Remote (Lite web client): 1, 3, 4, 5, 6, 8, 9, 10, 12, 16 Remote (Workstation): 1, 3, 4, 5, 6, 8, 9, 10, 12, 16, 18, 24, 25, 35, 36, 48, 49, 64, 81, 100
Fisheye Dewarping	Yes
Local Live View performance	16ch (Max. 3Mbps at 1920x1080) Please check "Standalone NVR Performance Validator" (http://www.acti.com/SANVRPerformance)
Digital Zoom	Yes
Event Status	Display event status upon alarm or upon connection loss or recovery between server and client or when the allocated disk space is full
Instant Playback	Instant Playback in live view window
Embedded websites in Live View	Display and connect to pre-configured embedded website

Map

e-Map	Yes
Google Map	Yes
Layout	Area maps with camera icons, small live view windows, hyperlinked
Setup	e-Map image upload, Google maps settings and preset management, camera positioning, vision angle and pointed direction of camera, view positioning, source positioning, extended devices for Point-of-sale (POS), Access control and Network I/O
PTZ Mode	Mouse PTZ mode to control e-Map video streams

PTZ

PTZ Control	PTZ Control, Speed Control, 32 preset points
Joystick	USB based joystick supported

Video

Compression	H.265, H.264, MPEG-4, MJPEG
Hardware Accelerated Decoding	Yes (for workstation PC only), H.264, H.265
Built-in Analytics	Visual Tracking

Audio

Audio Type	2-way, Mic-in, Line-in, Line-out
------------	----------------------------------

Network

Network Protocol & Service	IPv4/v6, TCP, UDP, DHCP Client, HTTP, HTTPS, DNS, NTP, RTP, RTSP, SMTP, FTP, ICMP, ARP, UPnP, LDAP (client), iSCSi
Ethernet Port	1 x 2.5 Gigabit Ethernet, RJ-45 connector
Maximum Outgoing Throughput	384 Mbps

Recording

Scheduled Recording	Yes
Event Recording	Yes

Manual Recording	Yes
Event Speed-up Recording	Yes
Dual Stream Management	Yes
Maximum Recording Throughput	384 Mbps

Search & Playback

Playback Control	Continuous forward and backward playback with speeds (1/64, 1/32, 1/16, 1/8, 1/4, 1/2, 1, 2, 4, 8, 16, 32, 64, 128, 256) or frame-by-frame, pause, stop
Synchronized Playback	16 channels (Local), 64 channels (Remote IE client), 16 channels (Remote Lite web client), 100 channels (Remote Workstation)
Recording Search	Search video recordings by time, events, channels, bookmarks, notifications and listed as clickable time-based thumbnails for full-size view and snapshot download
Smart Search	Smart search of recorded video by Motion Detection and Tamper
Video Export	RAW, AVI, MP4, EXE, GPU Hardware accelerated video export supported with AVI format
Snapshot Export	BMP, JPEG, PNG
Embedded Media Player	Yes, supports up to 64 channels view

Event


Video Push	Support Video Push from ACTi Mobile Client devices
Event Trigger	<p>[NVR]: Disk full, Disk not found, Disk is available, S.M.A.R.T. Failure and Normal, Schedule service start and stop, Video Push start and stop, Time Backward, CPU limit exceeded for NVR services, GPU Loading Detection for workstation only, Memory limit exceeded for Server PC and NVR services, Network Send/Receive Limit Exceeded for Server PC.</p> <p>[Video Device]: Video motion detection, Passive IR sensor, External device through digital input, Sound detection, Intelligent event detection, Video Push start and stop, Video loss and recovery, Disk Write Failure and Available.</p> <p>[Extended Device]: Point-of-sale (POS) status, Network I/O status, Access Control status</p>
Event Response	Pop-up window with live video and event confirmation activation, Switch to hotspot window, Switch to customize view, Command a PTZ device to go to a preset point, Play alert sound, Activate external device through digital output, Execute system command to activate other programs, Upload video or snapshot to FTP server, E-mail notification with snapshots, Push notification, Send Snapshot to Line Messenger

Redundancy Server

Redundancy Service	Yes, N-to-N, N+1 (With limited functions when NVR 3 server acts as Redundancy server)
--------------------	---

System

Permission control	Unlimited number of users, Active Directory, Customizable permissions for user groups, Account lockout, Automatic logout after idle, Playback password protected, Password validity period, Password Expiration Notification
Watchdog	Support
Client PC Operating System	Windows 7 SP1, Windows 8.1, Windows 10, Windows Server 2008 R2 SP1, Windows Server 2012 R2, Windows Server 2016, Windows Server 2019



Server and Client PC requirements	Please use https://www.acti.com/pcselector For client PC requirements, please check the Performance: Live View section.
Server Operating System	Windows 10 IoT
Mobile Client Program	Mobile device application (ACTi Mobile Client) supports Live View, PTZ Control, Video Push, Event/time based search and playback, Supported device(s) iOS, Android device
USB	6-Port USB 2.0, 2-Port USB 3.0, 3-Port USB 3.2, 1-Port USB Type C
Language	Multi-Language

Integration

Unified Solution	Fully compatible with ACTi cameras, encoders, central management system, TV wall and intelligent video surveillance software
CMS Support	Yes (ACTi CMS 2)
GPS Position	Manual setting
Edge Recording	Automatically restore the lost videos from the memory card of camera to NVR server via ONVIF (Profile G) or proprietary protocol integrations after network connection recovery.
ONVIF Compliant	Yes, Profile S (contains the officially ONVIF conformant software NVR 3 Corporate)
Web Browser	IE 11 (Please verify that your computer meets the minimum system requirements for Internet Explorer from Microsoft website.), Lite web client: Microsoft Edge 80.0.361.66 (Normal mode) or newer, Google Chrome 71.0.3578 or newer, Firefox 64.0.2 or newer, Apple Safari 12.0.2 or newer
Third-party Integration	Point of Sale (POS), Access Control, Network I/O, Parking Management Station (PMS), (Various optional integrations requiring additional license)

Storage


Supported Storage Technology	NAS, SAN
System Drive	M.2 NVMe SSD, 250GB
Storage Bay	SATA, Max. 6 Disk(s) (without storage disks) Support up to 8 disks (Optional)
HDD Size	3.5"
Maximum Recording Capacity	22TB x6
RAID Level	Software RAID 0, 1, 5, 10
Supported Storage	Video Exporting: SATA disk Video Exporting: USB

Interface

Audio Interface	1/1, 3.5mm Phone Jack
External Storage Interface	USB
Expansion Slots Available	2 x PCIe 3.0 (x1) 1 x PCIe 4.0 (x4) 1 x PCIe 5.0 (x16)
Local Access	USB joystick, keyboard & mouse
Local Display Interface	HDMI x 1, Display Port x 1

General

Power Source	AC 100-240V
Power Supply	400W



Dimensions	(W x H x D): 190mm x 426mm x 491.5mm (7.48" x 16.77" x 19.35")
Bundled Accessories	Power cord
Fan	Yes
Operating Temperature	0°C ~ 40°C (32°F ~ 104°F)
Operating Humidity	10% - 85% RH
Remote Access	Workstation, Web Client, Mobile Client
Color	Black
Warranty	3 Year(s). For extended warranty offering, see http://www.acti.com/support/warranty

