



VPS

PRODUCT INFORMATION

- ✓ All Stainless Steel Housing, Platform and Pillar Sealed Indicator (IP67 indicator)
- ✓ Wash Down Design to IP65
- ✓ Food grade stainless steel to meet the toughest food requirements
- ✓ Wide Angle LCD (Backlight)
- ✓ User Programmable Capacity and Division
- ✓ Flexible Platform Collocation
- ✓ Wash Down Version: Aluminum Load Cell and Ionized Load
- ✓ Receiving Structure
- ✓ Fully stainless steel housing, weighing pan, indicator and pillar,
- ✓ Ionized load receiving structure and aluminium load cell
- ✓ Protection devices against overload and shock
- ✓ Power ON Zero Tracking, Re-zero, Auto Calibration, Auto Power
- ✓ Saving, Digital Motion Filtering Device, Auto Tare, Accumulation
- ✓ Memory and Dual Interval Selection Functions
- ✓ Complete with Low Battery and Charging Status Indicator
- ✓ Adjustable Feet, Rechargeable Battery, Bubble Level, Power
- ✓ Adaptor and Indicator Dust Cover Included
- ✓ Pan size: 11" x 13"
- ✓ Weighing Units: kg, lb, oz



PART NUMBER	CAPACITY	READABILITY
VPS-6	6 kg 13 lb	1 g 0.002 lb
VPS-15	15 kg 33 lb	0.002 kg 0.005 lb
VPS-30	30 kg 66 lb	0.005 kg 0.01 lb

