
# **DL-PS-96/24-JB-DIM-A**

24V DC LED POWER SUPPLIES DRIVERS IN JUNCTION BOX - DIMMING SERIES



Fixture Type





With 24V DC, 96W LED driver and universal input voltage - 120 to 277V AC, this driver is dimmable with most Triac and ELV dimmers. PWM dimming method (for best results, minimum load should be 10% of maximum wattage of driver). Can be used in indoor - for dry, damp locations, with cooling by free air convection and short circuit, over temperature and over loading protection. Made with black powder coated aluminum enclosure, its efficiency > 87% and Power Factor > 0.9. Certified with ETL Listed, Class 2 power unit and weights 0.63 kg (1.4 lb).













# Intertek CLASS 2

### **SPECIFICATIONS**

I	N	Р	U	Τ

INPUT VOLTAGE	120 - 277V AC
INPUT FREQUENCY	47-63Hz
INPUT CURRENT (MAX.)	1.1A @120V AC
POWER FACTOR (TYP.) @ FULL LOAD	0.9 @120V AC
EFFICACY (TYP.) @ FULL LOAD	87% @120V AC

#### OUTPUT \_

OUTPUT VOLTAGE	24V DC
RELATED OUTPUT POWER	96W
RATED LOAD CURRENT	4.0A

#### PROTECTION \_

SHORT CIRCUIT	Hiccup mode, recover automatically		
	after fault condition is removed		
OVER LOADING	≤150% constant current limiting		

## ENVIRONMENT \_\_\_\_\_

IP RATINGS	IP20, Indoor/ Dry or Damps locations
OPERATING AMBIENT TEMPERATURE	-25° C to 40° C (-13° F to +104° F)
OPERATING AMBIENT HUMIDITY	20~90% RH, non-condensing
STORAGE TEMPERATURE	-40° C to +60° C (-40° F to +40° F)
STORAGE HUMIDITY	10~95% RH

† See Derating Curve


#### SAFETY & EMC \_\_\_\_\_

CERTIFICATES	ETL Listed
SAFETY STANDARDS	UL8750
WITHSTAND VOLTAGE	I/P-O/P: 1500V AC
ISOLATION RESISTANCE	I/P-O/P: 100MΩ / 500V DC /
	25° C / 70% RH
EMC EMISSION	FCC Part 15 B




## **DL-PS-96/24-JB-DIM-A**

24V DC LED POWER SUPPLIES DRIVERS IN JUNCTION BOX - DIMMING SERIES




#### WIRING DIAGRAM

#### **TYPICAL TRIAC DIMMING WIRING**



#### TYPICAL ELV DIMMING WIRING



#### **RECOMMENDED DIMMERS**

LEVI	TON	LEVITON DECORA				
LUTE	RON	LUTRON DIVA CL,	LUTRON TG600,	LUTRON MAESTRO MCL-153,	LUTRON DIVA 303P,	LUTRON CASETA PD,
		LUTRON SKYLARK	COUNTOR CL			