



Designed to cut and strip the most commonly used stranded and single conductors, this wire stripper is the perfect tool for cutting and stripping solid wires from 10 to 20 AWG (2.60 to 0.81 mm) and stranded wires from 12 to 22 AWG (2.05 to 0.65 mm). This wire stripper features the following:

- 50 HRC stainless steel construction for precision stripping and enhanced durability
- Ergonomic curved handle design is naturally comfortable to hold and reduces hand fatigue
- Coil spring reduces hand fatigue when using the tool for extended periods of time
- Conveniently located bending holes makes wire looping quick and easy
- Includes cutting holes for 8-32 and 10-32 threaded screws
- Lifetime Warranty

SPECIFICATIONS	
CUT TYPE	Cut & Strip
WIRE GAUGE	10-20 AWG (2.6 to 0.81 mm) Solid Copper Wire, 12-22 AWG (2.05 - 0.64 mm), 2 to 3 mm Diameter Fiber Jackets
HANDLE COLOR	Blue, Orange
PRODUCT MATERIAL	Stainless Steel
DIMENSIONS	7.2 in x 2.1 in x 0.51 in (18.29 cm x 5.33 cm x 1.3 cm)
WEIGHT	0.32 lb (145.28 g)
UPC #	810053352007

