

Weather-Resistant 3/8-Inch NPT (M) to 1/2-Inch NPT (M) 1/2-Inch ID 5-Foot Rubber Whip Air Hose with Brass Fittings

STEELMAN[®]

KINK RADIUS - 0.21-Inch kink radius allows hose to bend without obstructing airflow

TEMPERATURE RANGE - Can operate effectively in temperatures ranging from -40 to 180 degrees Fahrenheit

REINFORCED - Contains a reinforcement layer to prevent bursting under pressure

DURABLE MATERIALS - Made with durable reinforced rubber and NPT brass fittings



SPECIFICATIONS

- 099198612638
- 1 Year Limited Warranty
- Comes with a 4:1 safety factor to ensure user safety during operation
- Compliant with RMA IP-2 regulations
- Handles a working pressure of up to 300 PSI
- Capable of withstanding pressure up to 1200 PSI

MATERIALS

- Rubber
- Brass

PRODUCT #: 61263