

Electronic Prog. Thermostat CLEAR TOUCH Series







K312RELAY

- 7 day programmable
- Modern design with clear Acrylic panel
- Touch sensitive buttons
- Large LCD display with blue backlight
- Temperature lock feature: set a min & Max temp limit
- Save up to 28% on your heating costs
- 3 minute cycle rate reduces temperature swings
- Complies with all codes requiring anticipated/electronic thermostats
- System On/Standby switch





The Clear Touch. Electronic 7 Day Programmable Thermostat

King's ClearTouch K302PE combines user-friendly touch sensitive buttons with a sleek modern design, offering unparalleled user comfort control. ClearTouch is an energy-saving fully programmable solution for providing highly accurate temperature control for line voltage electric heaters. It's highly accurate sensing technology saves up to 28% on heating costs. Program a full 7 day schedule with ease for total room control.

Ordering Information

MODEL	UPC	DESCRIPTION
K302PE	10399	Thermostat Programmable DP 120/208/240V 15A
K312RELAY	10400	Thermostat Slave Relay DP 120/208/240V 15A

Engineering Specifications

Temperature Range: 41° - 95°F (5° - 35°C) Accuracy: +1° F

Max Power: 1800W @ 120VAC (15A) Max Power: 3120W @ 208VAC (15A) Max Power: 3600W @ 240VAC (15A) Sensing Element: Electronic



Want To Control Multiple Heaters?


K302PE thermostats are compatible with K312RELAY (Shown Below) to extend the heating zone beyond 15A & control from one master location.











K312RELAY

- Settings controlled by master thermostat
- Receives signal & activates heat when required
- ON/STANBY switch to disable heating independently

