

# High Velocity Outdoor Rated Air Circulator PFO Series



Optional Misting Kit  
(Shown)



**Model Code:**

PFO -24  
A B

A: Series  
B: Fan Diameter  
-24 = 24"  
-30 = 30"



- Outdoor rated for wet locations
- 80 degree oscillating motion
- Heavy duty air circulation
- Available in 24" & 30" models
- Waterproof totally enclosed motor
- 3-speed switch controls airflow output
- Direct drive motor for dependability
- Wall mounted to direct airflow
- Optional misting kit available
- Scratch resistant, powder-coated finish
- 3 aerodynamically balanced blades
- Heavy duty steel fan guards
- Meets OSHA 1910.212(A)(5) requirements
- 9 Ft, 120V grounded cord & plug
- 1-year limited warranty

## The King High Velocity Commercial Air Circulator

**King Commercial High Velocity Outdoor Rated Oscillating Air Circulators** are a powerful commercial-grade solution for cooling workshops, warehouses, factories, gyms and more. This oscillating fan motion distributes airflow in a 80 degree sweeping motion or from a fixed position. The waterproof, totally enclosed motor is outdoor rated for wet locations and offers 3-speeds. Featuring 3 aerodynamically balanced aluminum blades for even, steady airflow and to provide maximum air and motor efficiency. The scratch resistant King green finish looks sharp and is easy to clean. Height adjustable from 57" to 75" to direct the air flow where you need it most.

### Ordering Information

STOCK CODE	UPC #093319	MODEL NUMBER	DESCRIPTION	CFM	WT. (lbs.)
A	33151	PFO-24	24" Outdoor Rated Oscillating Circulator With Pedestal Base	7500/6200/4900	67.2
A	33152	PFO-30	30" Outdoor Rated Oscillating Circulator With Pedestal Base	8200/6800/5300	73.3
A	33153	PFO-MISTKIT	Add-On Accessory For Optional Misting Feature		
A	55376	FO-COVER-30	30" Water Resistant Fan Cover		
A	55377	FO-COVER-36	36" Water Resistant Fan Cover		

### PFO Series

Outdoor Rated for Wet Locations

Oscillating Fan Motion Distributive Airflow in a 80 Degree Sweep or Fixed Position

9 Ft Grounded Three Wire Conductor Cord & GFCI Plug, 120V - For Easy Portability & Safety

(3) Non-Corroding Aluminum Blades for Maximum Airflow

3-Speed Pull Chain Switch Controls Air Flow Output to Match Your Needs

Water Resistant Fan Cover

Optional Misting Kit Available: Adds a Fine Mist of Cool Comfort to Hot Environments

Optional PFO-Mistkit

Scratch Resistant, Powder-Coated Finish for Durability