

High Velocity Outdoor Rated Air Circulator PFO Series



Optional Misting Kit (Shown)



Model Code:

PFO -24
A B

A: Series
B: Fan Diameter
-24 = 24"
-30 = 30"



- 24" & 30" Commercial High Velocity Oscillating Air Circulator
- Outdoor Rated with Pedestal Base
- Optional Misting Kit Available
- Optional Fan-Speed-Controller
- 3-Speed Pull Chain Switch
- Totally Enclosed, Outdoor Rated Motor
- 3 Aerodynamically Balanced Blades
- Heavy Duty Steel Fan Guards
- Meets OSHA 1910.212(A)(5) Requirements
- 9 Ft, 120V Grounded Cord & GFCI Plug
- Scratch Resistant, Powder- Coated Finish
- Adjustable Height from 57" to 75"
- UL Certified for USA & Canada
- 1-Year Limited Warranty

The King High Velocity Commercial Air Circulator

King Commercial High Velocity Outdoor Rated Oscillating Air Circulators are a powerful commercial-grade solution for cooling workshops, warehouses, factories, gyms and more. This oscillating fan motion distributes airflow in a 80 degree sweeping motion or from a fixed position. The waterproof, totally enclosed motor is outdoor rated for wet locations and offers 3-speeds. Featuring 3 aerodynamically balanced aluminum blades for even, steady airflow and to provide maximum air and motor efficiency. The scratch resistant King green finish looks sharp and is easy to clean. Height adjustable from 57" to 75" to direct the air flow where you need it most.

Ordering Information

MODEL NUMBER	UPC #093319	DESCRIPTION	CFM	WT. (lbs.)
PFO-24	33151	24" Outdoor Rated Oscillating Circulator With Pedestal Base	7500/6200/4900	67.2
PFO-30	33152	30" Outdoor Rated Oscillating Circulator With Pedestal Base	8200/6800/5300	73.3

Accessories

MODEL	UPC	DESCRIPTION	SHIP WEIGHT lbs
PFO-MISTKIT	33153	Add-On Accessory For Optional Misting Feature	0.5
FO-COVER-24	55376	24" Water Resistant Fan Cover	0.25
FO-COVER-30	55377	30" Water Resistant Fan Cover	0.25
FAN-SPEED-CONTROLLER	55378	Fan Motor Variable Speed Control Plug-In, 120V 3A Max	0.5



FAN-SPEED-CONTROLLER



FO-COVERS
(Available in 24" & 30")

High Velocity Outdoor Rated Air Circulator PFO Series


PFO Series



Outdoor Rated
for Wet Locations

9 Ft Grounded Three
Wire Conductor Cord
& GFCI Plug, 120V -
For Easy Portability
& Safety

Optional Misting
Kit Available: Adds
a Fine Mist of Cool
Comfort to Hot
Environments



Oscillating Fan Motion
Distributive Airflow in a
80 Degree Sweep or
Fixed Position

(3) Non-Corroding
Aluminum Blades
for Maximum Airflow

3-Speed Pull Chain
Switch Controls Air
Flow Output to
Match Your Needs

Scratch Resistant,
Powder-Coated
Finish for Durability

Optional
PFO-Mistkit

Water Resistant
Fan Cover
(Available in 24" & 30")

