

Product Image



Screw Hooks

Screw hooks are manufactured with an open hook at the non-threaded end and lag threads on the opposing end. They are the ideal fastener for light duty applications or hanging chain when installing light fixtures. It is recommended that a pre-drilled hole slightly smaller than the diameter of the screw hook be used.

Features:

- Zinc plated steel
- Round bend type

Product Dimensions

PN	Overall Length	Thread Length	Thread Diameter	Hook Opening
SH20	4-15/16"	1-3/4"	0.370	1"
SH40	3-7/8"	1"	0.272	3/4"
SH60	3-3/8"	7/8"	0.230	3/4"
SH80	2-9/16"	7/8"	0.200	9/16"
SH100	2-1/16"	11/16"	0.156	3/8"
SH120	1-5/16"	1/2"	0.099	1/4"