



Model: **14-840L** Item #: _____ Date: _____
 Project: _____ Qty: _____ Approved By: _____

8" Center Lavatory Faucet with 5-1/2" Wide Rigid Gooseneck Spout

Royal Series Plumbing



14-840L

DESCRIPTION

8" Center Lavatory Faucet with 5-1/2" Rigid Gooseneck Spout, Polished Chrome Finish, 1.8 GPM Aerator Installed

STANDARD FEATURES

- ¼ Turn High Performance Ceramic Cartridge Valves with Integral Check
- 8" Widespread Concealed Deck Mount
- Rigid Gooseneck Spout
- Wristblade Handles
- Warranty: 3 Years

PRODUCT COMPLIANCE

- ASME A112.18.1/CSA B125.1
- NSF-61
- NSF/ANSI 372
- Meets ANSI A117.1 (ADA)
- California Proposition 65
- CEC Listed
- Massachusetts Approved



WARNING: Plumbing connections should be made by qualified personnel who will observe all applicable plumbing, sanitary and safety codes.

SPECIFICATIONS

Water Inlet	1/2" NPT
Temp. Range	40°F - 180°F
Rough In	1-1/2" Round Holes on 8" Center
Flow Rate	1.8 GPM
Material	Chrome Plated Brass
Weight	6 lbs.

