


















## energy efficient

- 17W replaces up to 40W CFL.
- Four color options to choose from: 3000K, 3500K, 4000K & 5000K.
- Universal mounting style.
- Enclosed fixture safe.
- Instant 'on' no warmup time.
- · Glass lens prevents aging, yellowing and bending











PART #	UPC	REPLACES	WATTAGE	LUMENS	CCT (K)	BASE	LENGTH
LED-7340-30K-G2	844006024314	40W CFL	17W	2100	3000K	2G11	22 IN
LED-7340-35K-G2	844006024321	40W CFL	17W	2100	3500K	2G11	22 IN
LED-7340-40K-G2	844006024338	40W CFL	17W	2200	4000K	2G11	22 IN
LED-7340-50K-G2		40W CFL	17W	2200	5000K	2G11	22 IN





