



Product Specification

Product:

G74 cartridge

Description:

G74 AM/MA/P100 cartridge for use with 9000, 9050, 9900, 9950 series facepiece

Sizes: Small – 9100 Medium – 9200 Large – 9300

Sizes: Medium – 9250 Large – 9350

Full facepiece rubber – 9900

Full Facepiece Silicone-9950

Performance Specification: per NIOSH 42 CFR part 84A

AM – Ammonia

MA – Methlyamine

P100 Particulate filter (99.97% efficiency level):

Sodium Chloride @ 85 lpm maximum penetration 99.97%

DOP (dioctyl phthalate) Oil @ 85 lpm 99.97%

Airflow Resistance:

Initial Inhalation: 35 mm water column height pressure @ 85 lpm

Initial Exhalation: 25 mm water column height pressure @ 85 lpm

Materials:

Filter: ABS

Cartridge Body: Carbon

Approvals:

NIOSH

G74 with 9000 series rubber half mask approval TC-84A-2736

G74 with 9050 series silicone half mask approval TC-84A-6837

G74 with 9900 rubber full facepiece approval TC-84A-5517

G74 with 9950 silicone full facepiece approval TC-84A-6743

January 16, 2017

CMS