



## Product Specification

**Product:**

Gerson replacement filter P95 filter

**Description:**

**Description:**

G95P filter for use with 9000 series facepiece

Sizes: Small – 9100                      Medium – 9200                      Large – 9300

Full facepiece – 9900

**Performance Specification:**                      per NIOSH 42 CFR part 84A

**Particulate Filter P95:**

Sodium Chloride @ 85 lpm maximum penetration                      5%

DOP (dioctyl phthalate) Oil @ 85 lpm maximum penetration – non degrading                      5%

**Airflow Resistance:**

Initial Inhalation:                      50 mm water column height pressure @ 85 lpm

Initial Exhalation:                      20 mm water column height pressure @ 85 lpm

Leakage                      30 milliliters per minute @ 25 mm water column height

**Materials:**

Filter:                      polypropylene

**Approvals:**

G01 with G95P with half mask approval TC -84A-3332

G01 with G95P with full facepiece approval TC -84A-5509

G03 with G95P with half mask approval TC -84A-3334

G03 with G95P with full facepiece approval TC -84A-5511

January 8, 2013

RAB