



## Product Specification

**Product:**

G08 cartridge

**Description:**

G08 Multi-Gas cartridge for use with 9000, 9050, 9900, 9950 series facepiece

Sizes: Small – 9100                      Medium – 9200                      Large – 9300

Sizes:    Medium – 9250                      Large – 9350

Full facepiece rubber – 9900

Full Facepiece Silicone-9950

**Performance Specification:**                      per NIOSH 42 CFR part 84A

AM – ammonia

CD- chlorine dioxide

CL- chlorine

FM- formaldehyde

HC- hydrogen chloride

HF- hydrogen fluoride

HS (escape) - Hydrogen Sulfide (escape)

MA- Methylamine

OV- Organic Vapor

SD- Sulfur Dioxide

**Airflow Resistance:**

Initial Inhalation:

35 mm water column height pressure @ 85 lpm

Initial Exhalation:

25 mm water column height pressure @ 85 lpm

**Materials:**

Filter:                      ABS

Cartridge Body: Carbon

**Approvals:**

NIOSH

G08 with 9000 series rubber half mask approval TC-84A-6760

G08 with 9050 series silicone half mask approval TC-84A-6839

G08 with 9900 rubber full facepiece approval TC-84A-6967

G08 with 9950 silicone full facepiece approval TC-84A-6968

September 15, 2015

CMS