

Blue elastic rubber caster



Elastic rubber caster, rigid or swiveling, available with or without "FULL LOCK" break.



Advantages and benefits

- Low starting effort, rolls easily; tread does not flat-spot.
- Soft and cushioned non-marking ride.
- Protective metal thread guards.
- Grease seal to hold in lubricant.
- Corrosion-resistant zinc finish.
- "Full LOCK" breaking system locks both the wheel and the swivel.

Conditions :

- *Water: Optimal*
- *Solvents: Efficient*
- *Detergents: Efficient*
- *Acids: Not recommended*
- *Extreme cold: Optimal*
- *Extreme heat : Optimal*
- *Petroleum products : Efficient*

Non-marking tread:



Hardwood

Tile / Linoleum / Ceramic

Recommended surfaces:



Product number	Description	Wheel Diameter	Load Capacity	Tread Width	Overall Height
F08335	100mm Swiveling caster	100mm (4")	70 kg (154 lbs)	35mm (1-3/8")	130mm (5-1/8")
F08336	100mm, Swiveling caster w/ "FULL LOCK" break	100mm (4")	70 kg (154 lbs)	35mm (1-3/8")	130mm (5-1/8")
F08334	100mm Rigid caster	100mm (4")	70 kg (154 lbs)	35mm (1-3/8")	130mm (5-1/8")
F08338	125mm Swiveling caster	125mm (5")	100 kg (220lbs)	35mm (1-3/8")	155mm (6-1/8")
F08339	125mm Swiveling caster w/ "FULL LOCK" break	125mm (5")	100 kg (220lbs)	35mm (1-3/8")	155mm (6-1/8")
F08337	125mm Rigid caster	125mm (5")	100 kg (220lbs)	35mm (1-3/8")	155mm (6-1/8")
F24789	160mm Swiveling caster	160mm (6-5/16")	140 kg (309lbs)	50mm (1-15/16")	195mm (7-11/16")
F24800	160mm, Swiveling caster w/ "FULL LOCK" break	160mm (6-5/16")	140 kg (309lbs)	50mm (1-15/16")	195mm (7-11/16")
F24795	160mm Rigid caster	160mm (6-5/16")	140 kg (309lbs)	50mm (1-15/16")	195mm (7-11/16")