

F27458



F26488



Pneumatic caster, swiveling or rigid.



Advantages and benefits

- Designed to absorb shocks and vibrations caused by obstacles or bumpy terrain.
- Lets you move fragile objects safely over rough, uneven surfaces.

Recommended surfaces:



Conditions :

- *Water: Optimal*
- *Solvents: Not recommended*
- *Detergents: Not recommended*
- *Acids: Not recommended*
- *Extreme cold: Efficient*
- *Extreme heat: Not recommended*
- *Petroleum products : Not recommended*

Product number	Description	Wheel Diameter	Load Capacity	Tread Width	Overall Height
F26488	203mm Swiveling caster	203mm (8")	80kg (176lbs)	63,5mm (2-1/2")	254mm (10")
F27458	203mm Rigid caster	203mm (8")	80kg (176lbs)	63,5mm (2-1/2")	254mm (10")
F26552	254mm Swiveling caster	254mm (10")	120kg (265lbs)	89mm (3-1/2")	300mm (11-13/16")
F27358	254mm Rigid caster	254mm (10")	120kg (265lbs)	89mm (3-1/2")	300mm (11-13/16")
F26553	305mm Swiveling caster	305mm (12")	204kg (450lbs)	89mm (3-1/2")	381mm (15")
F27359	305mm Rigid caster	305mm (12")	204kg (450lbs)	89mm (3-1/2")	381mm (15")