



PRODUCT DESCRIPTION

Rugged Brown leather shades are stitched and snugly fit over softly angled conical forms to create a rustic and warm lighting resource. Sturdy bases of cylindrical Distressed Wood adds a natural element with countryside appeal. Adjustable joints on the portable floor lamp and swing arm sconce allows you to direct the lighting where needed for function while the pendants glass-backed shade reveals the leather's delightful natural qualities with a glow from the lamp inside. An additional switch on the sconce provides functional convenience to the design.

MEASUREMENTS

DIMENSION : 6.75" L x 6.75" W x 18.5" H
 MAX OAH : 138" OAH
 CANOPY : 5" W x 0.75" H x 5" L
 HANGING WEIGHT : 4.18 lb

LAMPING

INPUT VOLTAGE : 120V
 LUMENS : 810 Rated (700 Del.)
 BULB : 1 x 9W LED E26 Medium , 9W Total
 BULB INCLUDED : (Included)
 DIMMABLE : Y
 CRI : 90 CRI
 COLOR_TEMP : 3000K

FINISHES OPTION

 Weathered Wood / Tan Leather

GLASS

Frosted FT

MATERIAL

Leather, Steel, Glass

RATINGS

cETLus
 Dry Location



ADDITIONAL

RATED LIFE 25000 Hours
 OPERATING TEMPERATURE:
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com