



#### PRODUCT DESCRIPTION

A simple candle style chandelier is given a modern edge with tall tapered candle covers that sit at the ends of curved arms without a bobèche beneath them. Available in Satin Brass or Matte Black, the collection compliments many architectural interiors and allows for creative styling through the selection of lamp type. Pair with our T6 lamp for more modern, industrial flair or classic candelabra for a clean, transitional look. This series provides a convenient new take on the candle chandelier with subtle and unique design details.

#### MEASUREMENTS

DIMENSION : 5" W x 24" H x 3.75" Ext  
 MAX OAH : 5" W x 5" H  
 HANGING WEIGHT : 1.15 lb

#### LAMPING

INPUT VOLTAGE : 120V  
 BULB : 1 x 60W Incandescent E12 Candelabra , 60W Total  
 BULB INCLUDED : (Not Included)

#### FINISHES OPTION

 Black  
 Satin Brass

#### MATERIAL

Steel

#### RATINGS

Damp Location  
 ADA



#### ADDITIONAL

INSTALL UP/DOWN: Up  
 OPERATING TEMPERATURE:  
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.