



PRODUCT DESCRIPTION

The sinuous form of thin arms outstretch and curve in a classic forged iron chandelier design. It seduces its audience with a wild turn at its center stem that ends with a charming hook detail replacing the conventional top loop. Completed in a Black Oxide finish, this collection combines the best elements of Spanish Revival and French Country design in boldly spanning diameters.

MEASUREMENTS

DIMENSION : 32.5" L x 32.5" W x 27.5" H
 MAX OAH : 70.5" OAH
 CANOPY : 5" W x 0.75" H x 5" L
 HANGING WEIGHT : 6.6 lb

LAMPING

INPUT VOLTAGE : 120V
 BULB : 6 x 60W Incandescent E12 Candelabra , 360W Total
 BULB INCLUDED : (Not Included)

FINISHES OPTION

 Black Oxide

MATERIAL

Iron

RATINGS

Dry Location

ADDITIONAL

OPERATING TEMPERATURE:
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.