



PRODUCT DESCRIPTION

Evocative of the past and modernized for today, the Delos collection features ironwork finished in a textured Anthracite that support hefty glass columns. The glass shades are elongated to accentuate the verticality of the chandelier and the fluted glass shades diffuse the light in an interesting and subtly romantic way, giving the appearance of candlelight.

MEASUREMENTS

DIMENSION : 10.5" W x 17.25" H x 5.75" Ext
 MAX OAH : 4.5" W x 4.5" H
 HANGING WEIGHT : 6.6 lb

LAMPING

INPUT VOLTAGE : 120V
 BULB : 2 x 40W Incandescent E12 Candelabra , 80W Total
 BULB INCLUDED : (Not Included)
 DIMMABLE : Y
 LIGHTING_DIRECTION : Omni

FINISHES OPTION

 Anthracite

GLASS

Clear Ribbed CR

MATERIAL

Steel + Glass

RATINGS

cULus
 Dry Location



ADDITIONAL

INSTALL UP/DOWN: Up
 OPERATING TEMPERATURE:
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com