



PRODUCT DESCRIPTION

Whether in town or countryside, this collection of chandeliers simplifies the classic curved frame with a modern approach. Finished in your choice of Satin Brass or Matte Black, the sharply curved arms extend higher than classic proportions and support ribbed cylinders of opal white glass shades. These Satin White glasses upgrade pleated shades by form of their ribbed details. Available in two sizes of chandelier and a linear 4-light pendant, this collection finds its place at home in a variety of applications and fits in regardless of whether its town or country.

MEASUREMENTS

DIMENSION : 26.75" W x 16.25" H
 MAX OAH : 55.5" OAH
 CANOPY : 5" W x 0.75" H
 HANGING WEIGHT : 13.2 lb

LAMPING

INPUT VOLTAGE : 120V
 BULB : 5 x 40W Incandescent E12 Candelabra , 200W Total
 BULB INCLUDED : (Not Included)

FINISHES OPTION

 Black
 Satin Brass

GLASS

Satin White SW

MATERIAL

Steel, Fluted White Glass

RATINGS

Dry Location

ADDITIONAL

OPERATING TEMPERATURE:
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maxilighting.com