



PRODUCT DESCRIPTION

Inspired by the seaside California home that once belonged to a turn-of-the-century celebrity tycoon, the San Simeon flush mount and wall sconce embrace vintage charms using Satin White globes fastened to modernized columns with stepped details in Black and Aged Brass. The collection is also damp rated and safe for use in covered exterior spaces to add a touch of Hollywood Regency styling to your outdoor space.

MEASUREMENTS

DIMENSION : 6" W x 11.5" H x 8" Ext
 MAX OAH : 4.75" W x 6.25" H
 HANGING WEIGHT : 2.8 lb

LAMPING

INPUT VOLTAGE : 120V
 LUMENS : 600 Rated (450 Del.)
 BULB : 2 x 4W LED AC Integrated , 8W Total
 BULB INCLUDED : (Integrated)
 CRI : 90 CRI
 COLOR_TEMP : 3000K

FINISHES OPTION

 Black / Natural Aged Brass

GLASS

Satin White SW

MATERIAL

Steel, Aluminum, Glass

RATINGS

cETLus
 Damp Location



ADDITIONAL

RATED LIFE 35000 Hours
 OPERATING TEMPERATURE:
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maxilighting.com