





PRODUCT DESCRIPTION

The composition of Clear glass rods are elegantly supported by thin radial arms of staggered lengths to create an iridescent motif that is truly Divine. Finished in Polished Nickel or Heritage Brass, the simplicity of this design delivers a crisp lighting fixture that works in a multitude of interior aesthetics from contemporary to traditional.

FINISHES OPTION

-  Heritage
-  Polished Nickel

GLASS

Clear CL

MATERIAL

Steel, Glass

RATINGS

cETLus
Dry Location



ADDITIONAL


OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

MEASUREMENTS

- DIMENSION : 28.5" L x 28.5" W x 25.5" H
- MAX OAH : 59" OAH
- CANOPY : 5" W x 0.75" H x 5" L
- HANGING WEIGHT : 26.4 lb

LAMPING

- INPUT VOLTAGE : 120V
- BULB : 8 x 60W Incandescent E12 Candelabra , 480W Total
- BULB INCLUDED : (Not Included)
- DIMMABLE : Y



*max overall height

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com