



#### PRODUCT DESCRIPTION

Stately outdoor sconces reference classic lantern shapes and are constructed of Maxim's proprietary Vivex composite, a robust weather-resistant materials guaranteed to withstand harsh weather climates. Available in several sizes and illuminated with clusters of candle sockets, this is a timeless design built to last.

#### MEASUREMENTS

DIMENSION : 11" W x 17" H x 5.75" Ext  
 BACK PLATE : 9.25" W x 11.5" H x 12.75" HCO  
 HANGING WEIGHT : 11.68 lb

#### LAMPING

INPUT VOLTAGE : 120V  
 BULB : 2 x 40W Incandescent E12 Candelabra , 80W Total  
 BULB INCLUDED : (Not Included)  
 DIMMABLE :

#### FINISHES OPTION

 Black

#### GLASS

Clear CL

#### MATERIAL

Vivex, Glass

#### RATINGS

Wet Location



#### ADDITIONAL

INSTALL UP/DOWN: Up  
 OPERATING TEMPERATURE:  
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)  
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER  
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com