



**PRODUCT DESCRIPTION**

This very compact LED flush mount directly installs on any 4" junction box and gives the look of a recessed trim. Constructed of Die Cast Aluminum, the Diverse luminaire is dimmable and also approved for wet or damp locations so it can be used in virtually any ceiling application, including showers.

**MEASUREMENTS**

DIMENSION : 6" L x 6" W x 1.25" H  
 HANGING WEIGHT : 0.29 lb

**LAMPING**

INPUT VOLTAGE : 120V  
 LUMENS : 800 Rated (750 Del.)  
 BULB : 1 x 11W LED PCB Integrated , 11W Total  
 BULB INCLUDED : (Integrated)  
 DIMMABLE : Triac/ELV dimming  
 CRI : 90 CRI  
 COLOR\_TEMP : 2700K  
 LIGHTING\_DIRECTION : Down

**FINISHES OPTION**

 White

**GLASS**

White WT

**MATERIAL**

Aluminum + PC

**RATINGS**

cETLus  
 Wet Location  
 Energy Star  
 CA Title 24  
 ADA



**ADDITIONAL**

INSTALL UP/DOWN: UP  
 RATED LIFE 50000 Hours  
 OPERATING TEMPERATURE:  
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)  
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER  
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com